Reliability Monitoring Results

Quarters: Q1/2022 to Q4/2022
Based on structural similarity

Supplier	**User Part Number**
Nexperia B.V.	74AHCT14BQ-Q100

Part Description: Hex inverter Schmitt-trigger; TTL enabled

Function Family: AHC(T)
Process family: Super micron
Package family: DHVQFN

JESD47 Test		**Test Conditions**	**Duration**	**# Lots**	**# Quantity**	**# Rejects**
# 1	**TEST** Pre- and Post-Stress Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below
# 2	**PC** Preconditioning	JESD22-A113 MSL 1	N/A	386	23019	0
# 5a	**HTOL EFR** High Temperature Operating Life Extrinsic	JESD22-A108 Tj = 150°C $V_{CCMAX} \leq V \leq 1.2*V_{CCMAX}$	48 hours or 168 hours	136	39090	0
# 5b	**HTOL IFR** High Temperature Operating Life Intrinsic	JESD22-A108 Tj = 150°C $V_{CCMAX} \leq V \leq 1.2*V_{CCMAX}$	≥500 hours	84	5695	0
# 7	**TC** Temperature Cycling	JESD22-A104 -65 °C to 150°C	≥500 cycles	208	12655	0
# 9	**uHAST / HAST** unbiased or biased High Accelerated Stress Test	JESD22-A101 Tamb = 130 °C, RH = 85%, V = V_{CCMAX}	96 hours	178	10364	0

Calculation of PPM, FIT and MTTF

Test considered for PPM calculation: High Temperature Operating LifeTest Extrinsic (HTOL EFR, Test # 5a above)
Test considered for FIT and MTTF calculations: High Temperature Operating LifeTest Intrinsic(HTOL IFR, Test # 5b above)
Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Product Family	**Package Family**	**Quantity**	**Rejects**	**Extrinsic Failure Rate (PPM)**	**Intrinsic Failure Rate (FIT)**	**MTTF (hrs)**
AHC(T)	DHVQFN	5695	0	24	0.6	1.74 E+09

© 2022 Nexperia B.V.
All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.