

PSMN075-100MSE

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.32	K/W

Cth1	5.676060E-5	F	Rth1	4.566760E-2	Ω
Cth2	6.309250E-2	F	Rth2	4.095960E-1	Ω
Cth3	3.608400E-3	F	Rth3	1.328840E+0	Ω
Cth4	2.335790E-2	F	Rth4	2.054500E-1	Ω
Cth5	1.419530E-3	F	Rth5	1.654800E-1	Ω
Cth6	1.419530E-3	F	Rth6	1.654800E-1	Ω

Part Name: PSMN075-100MSE
 Date: 23 May 2019

