

PSMN3R8-100BS

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	0.22	-	K/W

Cth1	1.956540E+0	F	Rth1	5.266510E-2	Ω
Cth2	2.890660E-2	F	Rth2	1.387320E-1	Ω
Cth3	1.028770E+0	F	Rth3	5.432620E-3	Ω
Cth4	1.877430E-3	F	Rth4	5.051190E-3	Ω
Cth5	7.181940E-3	F	Rth5	6.041310E-3	Ω
Cth6	7.238020E-3	F	Rth6	6.041770E-3	Ω
Cth7	7.207870E-3	F	Rth7	6.041530E-3	Ω

Part Name: PSMN3R8-100BS
 Date: 19 June 2019

