

GAN190-650EBE

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	1.04	K/W

Cth1	9.983690E-5	F	Rth1	1.286450E-1	Ω
Cth2	5.030230E-4	F	Rth2	4.793780E-1	Ω
Cth3	2.364690E-3	F	Rth3	4.336350E-1	Ω
Cth4	9.832050E+1	F	Rth4	2.236390E-6	Ω

Part Name: GAN190-650EBE
 Date: 27 March 2023

