

GAN7R0-150LBE

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	4.16	K/W

Cth1	3.932410E-4	F	Rth1	2.081110E-1	Ω
Cth2	3.412540E-3	F	Rth2	2.231000E+0	Ω
Cth3	2.448290E-2	F	Rth3	1.717000E+0	Ω
Cth4	1.743030E+3	F	Rth4	4.106520E-6	Ω

Part Name: GAN7R0-150LBE
 Date: 22 March 2023

