

GANB4R8-040CBA

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	7.52	K/W

Cth1	1.144580E-3	F	Rth1	9.330050E-1	Ω
Cth2	3.992740E-3	F	Rth2	2.311090E+0	Ω
Cth3	4.412440E-2	F	Rth3	4.278620E+0	Ω
Cth4	8.601910E+1	F	Rth4	1.255130E-4	Ω

Part Name:

GANB4R8-040CBA

Date:

18 December 2023

