

PSMN011-60HL

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.21	K/W

Cth1	8.873640E-5	F	Rth1	3.176990E-2	Ω
Cth2	5.301350E-4	F	Rth2	1.046350E-1	Ω
Cth3	2.569510E-3	F	Rth3	1.196650E+0	Ω
Cth4	4.197450E-2	F	Rth4	8.724500E-1	Ω

Part Name: PSMN011-60HL
 Date: 19 August 2022

