

PSMN013-40VLD

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	3.23	K/W

Cth1	2.962740E-5	F	Rth1	1.069510E-1	Ω
Cth2	3.033770E-4	F	Rth2	9.115190E-1	Ω
Cth3	1.661470E-3	F	Rth3	1.620950E+0	Ω
Cth4	8.075230E-3	F	Rth4	5.872380E-1	Ω

Part Name: PSMN013-40VLD
 Date: 01 June 2021

