

PSMN013-60HL

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.36	K/W

Cth1	8.019370E-5	F	Rth1	3.528400E-2	Ω
Cth2	4.836850E-4	F	Rth2	1.164750E-1	Ω
Cth3	2.300490E-3	F	Rth3	1.304520E+0	Ω
Cth4	4.000150E-2	F	Rth4	9.030240E-1	Ω

Part Name: PSMN013-60HL
 Date: 19 August 2022

