

PSMN013-60HS

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.36	K/W

Cth1	7.972510E-5	F	Rth1	3.416150E-2	Ω
Cth2	4.385900E-4	F	Rth2	1.088250E-1	Ω
Cth3	2.323740E-3	F	Rth3	1.312320E+0	Ω
Cth4	3.997630E-2	F	Rth4	9.039900E-1	Ω

Part Name: PSMN013-60HS
 Date: 19 August 2022

