

PSMN028-100HS

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.36	K/W

Cth1	8.088610E-5	F	Rth1	3.610650E-2	Ω
Cth2	5.189230E-4	F	Rth2	1.242620E-1	Ω
Cth3	2.340740E-3	F	Rth3	1.307550E+0	Ω
Cth4	4.059740E-2	F	Rth4	8.913770E-1	Ω

Part Name: PSMN028-100HS
 Date: 19 August 2022

