

PSMN038-100HS

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.84	K/W

Cth1	6.015230E-5	F	Rth1	4.571880E-2	Ω
Cth2	3.425820E-4	F	Rth2	1.483080E-1	Ω
Cth3	1.765850E-3	F	Rth3	1.685280E+0	Ω
Cth4	3.581490E-2	F	Rth4	9.644900E-1	Ω

Part Name: PSMN038-100HS
 Date: 19 August 2022

