

PSMN8R5-40HS

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.84	K/W

Cth1	5.965000E-5	F	Rth1	4.372130E-2	Ω
Cth2	3.032170E-4	F	Rth2	1.382110E-1	Ω
Cth3	1.768990E-3	F	Rth3	1.690390E+0	Ω
Cth4	3.552670E-2	F	Rth4	9.714790E-1	Ω

Part Name: PSMN8R5-40HS
 Date: 19 August 2022

