

PSMNR67-30YLE

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	0.45	K/W

Cth1	2.354360E-4	F	Rth1	1.151390E-2	Ω
Cth2	2.362180E-3	F	Rth2	5.797540E-2	Ω
Cth3	1.014910E-2	F	Rth3	1.956940E-1	Ω
Cth4	3.962110E-2	F	Rth3	1.817570E-1	Ω

Part Name:

PSMNR67-30YLE

Date:

11 October 2022

