

PXN011-100QS

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	1.89	K/W

Cth1	3.679180E-4	F	Rth1	2.935610E-2	Ω
Cth2	3.355320E-4	F	Rth2	3.055330E-1	Ω
Cth3	1.158600E-3	F	Rth3	1.024070E+0	Ω
Cth4	4.672170E-2	F	Rth4	5.304830E-1	Ω

Part Name: PXN011-100QS
 Date: 26 September 2023

