

PXN028-100QL

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	4.16	K/W

Cth1	1.534000E-4	F	Rth1	1.432670E-1	Ω
Cth2	1.586850E-4	F	Rth2	1.362380E+0	Ω
Cth3	5.310990E-4	F	Rth3	1.613820E+0	Ω
Cth4	7.393470E-3	F	Rth4	1.037810E+0	Ω

Part Name: PXN028-100QL
Date: 26 September 2023

