

GAN7R0-150LBE

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	4.16	K/W

Cth1	4.394430E-4	F	Rth1	1.668200E-1	Ω
Cth2	2.060000E-2	F	Rth2	2.422960E+0	Ω
Cth3	8.265930E-3	F	Rth3	8.661980E-1	Ω
Cth4	1.022080E-2	F	Rth4	7.001420E-1	Ω

Part Name: GAN7R0-150LBE
 Date: 22 March 2023

