

GANB4R8-040CBA

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	7.52	K/W

Cth1	4.402000E-2	F	Rth1	4.818480E+0	Ω
Cth2	1.540000E-3	F	Rth2	5.275000E-1	Ω
Cth3	1.113950E-2	F	Rth3	9.687960E-1	Ω
Cth4	8.941150E-3	F	Rth4	1.208060E+0	Ω

Part Name:

GANB4R8-040CBA

Date:

18 December 2023

