

PSMN028-100HS

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.36	K/W

Cth1	3.580260E-2	F	Rth1	1.091980E+0	Ω
Cth2	3.092570E-3	F	Rth2	1.155440E+0	Ω
Cth3	6.966000E-4	F	Rth3	8.529650E-2	Ω
Cth4	9.455170E-5	F	Rth4	2.657600E-2	Ω

Part Name: PSMN028-100HS
Date: 19 August 2022

