

PSMNR60-25YLH

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	0.55	K/W

Cth1	5.385920E-2	F	Rth1	2.458330E-1	Ω
Cth2	1.002480E-2	F	Rth2	2.577300E-1	Ω
Cth3	2.374720E-3	F	Rth3	3.794210E-2	Ω
Cth4	8.236340E-5	F	Rth4	2.222710E-3	Ω
Cth5	5.275460E-4	F	Rth5	1.111190E-2	Ω

Part Name: PSMNR60-25YLH
Date: 30 October 2019

