

PSMNR67-30YLE

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	0.45	K/W

Cth1	3.444560E-2	F	Rth1	2.982500E-1	Ω
Cth2	1.731190E-2	F	Rth2	1.023310E-1	Ω
Cth3	3.213960E-3	F	Rth3	3.688540E-2	Ω
Cth4	2.597740E-4	F	Rth4	9.473560E-3	Ω

Part Name: PSMNR67-30YLE
Date: 11 October 2022

