

PXN028-100QL

SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	4.16	K/W

Cth1	5.499410E-3	F	Rth1	1.588090E+0	Ω
Cth2	6.399180E-4	F	Rth2	2.144040E+0	Ω
Cth3	6.127260E-4	F	Rth3	3.909380E-1	Ω
Cth4	3.182380E-4	F	Rth4	3.420790E-2	Ω

Part Name: PXN028-100QL
 Date: 26 September 2023

