

Recovery rectifiers

Hyperfast recovery, space-saving devices


Nexperia's recovery rectifiers deliver high power density while minimizing reverse recovery time and loss. For efficient switching and power conversion applications in automotive, industrial and consumer markets.

Portfolio

- › 200–650 V **Hyperfast** switching parts with optimized recovery time (t_{rr}) of < 30 ns
- › High speed switching capability
- › Low voltage drop ($V_F @ I_{F, max} \sim 1$ V)
- › Low leakage current, also at high temperature
- › AEC-Q101 qualified parts ($175^\circ\text{C } T_{J(max)}$)

Robust & thermally efficient

- › High current pulse capability due to solid copper clip-bond
- › High power density / high efficiency planar technology
- › Low magnetic inductance optimizes switching behavior



Key applications

- › Polarity protection
- › DC/DC conversion
- › AC/DC conversion
- › Freewheeling of inductive load
- › Standard switching application
- › High-speed switching application
- › Onboard charging
- › Solenoid control
- › Piezo injection

Economical use of space



CFP2-HP (SOD323HP)

2.2 x 1.3 x 0.68 mm*
 $R_{th(j-sp)} = 6$ K/W



CFP3 (SOD123W)

2.6 x 1.7 x 1.0 mm*
 $R_{th(j-sp)} = 18$ K/W



CFP5 (SOD128)

3.8 x 2.5 x 1.0 mm*
 $R_{th(j-sp)} = 12$ K/W



CFP15B (SOT1289B)










5.8 x 4.3 x 0.95 mm*
 $R_{th(j-sp)} = 3$ K/W

- › Just 1 mm package height for thin PCB designs
- › More than 50% footprint savings - CFP3 compared to SMA

*Body size (l x w x h)

Recovery rectifiers

Types in **bold** represent new products

							Automotive-qualified					
V_R max (V)	V_F max (V)	I_F (A)	I_R max (μ A)	V_R (V)	t_{rr} max (ns)	Package	CFP2-HP (SOD323HP)	CFP3 (SOD123W)	CFP5 (SOD128)	CFP15B (SOT1289B)		
												
							Size (mm)	2.2 x 1.3 x 0.68	2.6 x 1.7 x 1.0	3.8 x 2.5 x 1.0	5.8 x 4.3 x 0.95	
							P_{tot} (mW) @ 1cm ²	1200	1150	1200	2150	
200	1.05	1	1	200	25	 006aab040	PNE20010EXD (-Q)					
	0.93	1	0.2	200	25			PNE20010ER				
	0.98	2	0.2	200	25			PNE20020ER				
	0.95	2	1	200	25				PNE20020EP			
	0.98	3	1	200	30				PNE20030EP			
	0.9	4	1	200	30				PNE20040EP (-Q)			
	1	5	1	200	30				PNE20050EP (-Q)			
	0.93	4	1	200	30	 aaa-033668				PNE20040EPE (-Q)		
	0.94	6	1	200	30						PNE20060EPE (-Q)	
	0.96	8	1	200	30						PNE20080EPE (-Q)	
	0.97	10	1	200	30						PNE200100EPE (-Q)	
	0.98	2x2	1	200	25		 aaa-030581					PNE20040CPE (-Q)
	0.94	2x3	1	200	30							PNE20060CPE (-Q)
	0.95	2x4	1	200	30							PNE20080CPE (-Q)
	0.95	2x5	1	200	30							PNE200100CPE (-Q)
400	1.1	1	1	400	1800	 006aab040		PNS40010ER				
650	1.25	1	1	650	50	 006aab040		PNU65010ER (-Q)				
	1.25	1	1	650	50				PNU65010EP (-Q)			

© 2022 Nexperia B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Date of release:

November 2022