74AHCT541A

Octal buffer/line driver; 3-state

Rev. 8 — 27 September 2023

Product data sheet

1. General description

The 74AHCT541A is an 8-bit buffer/line driver with 3-state outputs and TTL inputs. The device features two output enables ($\overline{\text{OE}}1$ and $\overline{\text{OE}}2$). A HIGH on $\overline{\text{OE}}$ n causes the associated outputs to assume a high-impedance OFF-state.

Designed to operate over a V_{CC} range from 4.5 V to 5.5 V, the inputs are TTL compatible, which allows the device to be used to translate from 3.3 V to 5 V.

Schmitt-trigger action at all inputs makes the circuit tolerant of slower input rise and fall times.

This device is fully specified for partial Power-down applications using I_{OFF} . The I_{OFF} circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

2. Features and benefits

- · Direct interface with TTL levels
- Supply voltage range from 4.5 V to 5.5 V
- Overvoltage tolerant inputs to 5.5 V
- · High noise immunity
- · CMOS low power dissipation
- Typical t_{pd} of 2.8 ns at 5 V
- Typical $V_{OL(p)}$ < 0.8 V at V_{CC} = 5 V, T_{amb} = 25 °C
- Typical V_{OH(v)} > 2.3 V at V_{CC} = 5 V, T_{amb} = 25 °C
- Supports mixed-mode voltage operation on all ports
- I_{OFF} circuitry provides partial Power-down mode operation
- Latch-up performance exceeds 250 mA per JESD 78 Class II
- · ESD protection:
 - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 3000 V
 - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 2000 V
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

3. Ordering information


Table 1. Ordering information

Type number	Package			
	Temperature range	Name	Description	Version
74AHCT541APW	-40 °C to +125 °C	TSSOP20	plastic thin shrink small outline package; 20 leads; body width 4.4 mm	SOT360-1
74AHCT541ABQ	-40 °C to +125 °C	DHVQFN20	plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 20 terminals; body 2.5 × 4.5 × 0.85 mm	SOT764-1




Octal buffer/line driver; 3-state

4. Functional diagram



5. Pinning information

5.1. Pinning



Octal buffer/line driver; 3-state

5.2. Pin description

Table 2. Pin description

Symbol	Pin	Description
OE1, OE2	1, 19	output enable input (active LOW)
A0, A1, A2, A3, A4, A5, A6, A7	2, 3, 4, 5, 6, 7, 8, 9	data input
GND	10	ground (0 V)
Y0, Y1, Y2, Y3, Y4, Y5, Y6, Y7	18, 17, 16, 15, 14, 13, 12, 11	data output
V _{CC}	20	supply voltage

6. Functional description

Table 3. Functional table

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.

Control		Input	Output
OE1	OE2	An	Yn
L	L	L	L
L	L	Н	Н
X	Н	X	Z
Н	X	X	Z

7. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{CC}	supply voltage		-0.5	+7.0	V
VI	input voltage	[1]	-0.5	+7.0	V
Vo	output voltage	active mode [2] [3]	-0.5	V _{CC} + 0.5	V
		power-down or 3-state mode [2]	-0.5	+7.0	V
I _{IK}	input clamping current	V _I < 0 V	-20	-	mA
I _{OK}	output clamping current	V _O < 0 V	-20	-	mA
Io	output current	$V_O = 0 V \text{ to } V_{CC}$	-	±25	mA
I _{CC}	supply current		-	75	mA
I_{GND}	ground current		-75	-	mA
T _{stg}	storage temperature		-65	+150	°C
P _{tot}	total power dissipation	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}$ [4]	-	500	mW

- [1] The minimum input voltage ratings may be exceeded if the input current ratings are observed.
- [2] The output voltage ratings may be exceeded if the output current ratings are observed.
- [3] This value is limited to 7.0 V maximum.
- [4] For SOT360-1 (TSSOP20) package: P_{tot} derates linearly with 10.0 mW/K above 100 °C. For SOT764-1 (DHVQFN20) package: P_{tot} derates linearly with 12.9 mW/K above 111 °C.

Octal buffer/line driver; 3-state

8. Recommended operating conditions

Table 5. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V _{CC}	supply voltage		4.5	5.5	V
VI	input voltage		0	5.5	V
Vo	output voltage	active mode	0	V _{CC}	V
		power-down or 3-state mode	0	5.5	V
T _{amb}	ambient temperature		-40	+125	°C
Δt/ΔV	input transition rise and fall rate	V _{CC} = 5.0 V ± 0.5 V	-	20	ns/V

9. Static characteristics

Table 6. Static characteristics

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		25 °C	;	-40 °C t	o +85 °C	-40 °C to	+125 °C	Unit
			Min	Тур	Max	Min	Max	Min	Max	
V _{IH}	HIGH-level input voltage	V _{CC} = 4.5 V to 5.5 V	2	-	-	2	-	2	-	V
V_{IL}	LOW-level input voltage	V _{CC} = 4.5 V to 5.5 V	-	-	0.8	-	0.8	-	0.8	V
V _{OH}	HIGH-level	$V_I = V_{IH}$ or V_{IL} ; $V_{CC} = 4.5 \text{ V}$								
	output voltage	I _O = -50 μA	4.4	4.5	-	4.4	-	4.4	-	V
		I _O = -8 mA	3.94	-	-	3.8	-	3.7	-	V
V _{OL}	LOW-level	$V_I = V_{IH}$ or V_{IL} ; $V_{CC} = 4.5 \text{ V}$								
	output voltage	I _O = 50 μA	-	0	0.1	-	0.1	-	0.1	V
		I _O = 8 mA	-	-	0.36	-	0.44	-	0.55	V
I _{OZ}	OFF-state output current	V_{CC} = 5.5 V; V_I = V_{IH} or V_{IL} ; V_O = GND to 5.5 V	-	-	±0.25	-	±2.5	-	±2.5	μA
I _{OFF}	power-off leakage current	V_I or V_O = GND to 5.5 V; V_{CC} = 0 V	-	-	0.5	-	5	-	5	μА
II	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 0$ V to 5.5 V	-	-	±0.1	-	±1	-	±1	μΑ
I _{CC}	supply current	$V_I = V_{CC}$ or GND; $I_O = 0$ A; $V_{CC} = 5.5$ V	-	-	2	-	20	-	20	μΑ
Δl _{CC}	additional supply current	per input pin; $V_I = 3.4 \text{ V}$; $I_O = 0 \text{ A}$; $V_{CC} = 5.5 \text{ V}$; other pins at V_{CC} or GND	-	-	1.35	-	1.5	-	1.5	mA

Octal buffer/line driver; 3-state

10. Dynamic characteristics

Table 7. Dynamic characteristics

GND = 0 V. For test circuit see Fig. 5.

Symbol	Parameter	Conditions			25 °C		-40 °C t	o +85 °C	-40 °C to	+125 °C	Unit
			ľ	Min	Typ[1]	Max	Min	Max	Min	Max	
t _{pd}	propagation	An to Yn; see Fig. 3	[2]								
	delay	V _{CC} = 4.5 V to 5.5 V									
		C _L = 15 pF		-	2.8	6.9	1	8	1	8	ns
		C _L = 50 pF		-	4.4	7.9	1	9	1	9	ns
t _{en}	enable time	OEn to Yn; see Fig. 4	[2]								
		V _{CC} = 4.5 V to 5.5 V									
		C _L = 15 pF		-	3.9	11.3	1	13	1	13	ns
		C _L = 50 pF		-	5.5	12.3	1	14	1	14	ns
t _{dis}	disable time	OEn to Yn; see Fig. 4	[2]								
		V _{CC} = 4.5 V to 5.5 V									
		C _L = 15 pF		-	3.6	7.5	1	8	1	8	ns
		C _L = 50 pF		-	5.4	11.9	1	13.5	1	13.5	ns
t _{sk(o)}	skew	V _{CC} = 4.5 V to 5.5 V; C _L = 50 pF		-	-	1	-	1	-	1	ns
Cı	input capacitance	$V_I = V_{CC}$ or GND; $V_{CC} = 5 \text{ V}$		-	2	6	-	6	-	6	pF
Co	output capacitance	$V_O = V_{CC}$ or GND; $V_{CC} = 5 \text{ V}$		-	5	-	-	-	-	-	pF
C _{PD}	power dissipation capacitance	per buffer; $C_L = 0$ pF; f = 10 MHz; $V_I = GND$ to V_{CC}	[3]	-	9	-	-	-	-	-	pF

^[1] Typical values are measured at T_{amb} = 25 °C and V_{CC} = 5 V.

f_i = input frequency in MHz;

 f_o = output frequency in MHz;

C_L = output load capacitance in pF;

V_{CC} = supply voltage in Volts.

Table 8. Noise characteristics

GND = 0 V. For test circuit see Fig. 5.

Symbol	Parameter	Conditions	7	Unit		
			Min	Тур	Max	
V _{CC} = 5 \	7; C _L = 50 pF					
$V_{OL(p)}$	LOW-level output voltage (peak)		-	0.5	1.5	V
$V_{OL(v)}$	LOW-level output voltage (valley)		-1.5	-0.3	-	V
$V_{OH(v)}$	HIGH-level output voltage (valley)		-	4.5	-	V
V _{IH(AC)}	AC HIGH-level input voltage (dynamic)		2	-	-	V
V _{IL(AC)}	AC LOW-level input voltage (dynamic)		-	-	0.8	V

^[2] t_{pd} is the same as t_{PLH} and t_{PHL} .

 t_{en} is the same as t_{PZL} and $t_{\text{PZH}}.$

 t_{dis} is the same as t_{PLZ} and t_{PHZ} . [3] C_{PD} is used to determine the dynamic power dissipation P_D (μ W). $P_D = C_{PD} \times V_{CC}^2 \times f_i + \Sigma (C_L \times V_{CC}^2 \times f_o)$ where:

Octal buffer/line driver; 3-state

10.1. Waveforms and test circuit




Fig. 3. Propagation delay input (An) to output (Yn)






Table 9. Measurement points

Input	Output	utput							
V_{M}	V _M	V _X	V _Y						
1.5 V	0.5 × V _{CC}	V _{OL} + 0.3 V	V _{OH} - 0.3 V						

Octal buffer/line driver; 3-state





Test data is given in Table 10.

Definitions test circuit:

 R_T = Termination resistance should be equal to output impedance Z_o of the pulse generator;

 C_L = Load capacitance including jig and probe capacitance;

R_L = Load resistance;

S1 = Test selection switch.

Fig. 5. Test circuit for measuring switching times

Table 10. Test data


Inpu	Input		Load		S1 position			
Vı	t _r , t _f C _L		R_L	t _{PHL} , t _{PLH}	t _{PZH} , t _{PHZ}	t_{PZL}, t_{PLZ}		
GND	0 to 3.0 V	3.0 ns	15 pF, 50 pF	1 kΩ	open	GND	V _{CC}	

Octal buffer/line driver; 3-state

11. Package outline

TSSOP20: plastic thin shrink small outline package; 20 leads; body width 4.4 mm

SOT360-1



UNIT	A max.	A ₁	A ₂	Α3	bp	С	D ⁽¹⁾	E (2)	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ
mm	1.1	0.15 0.05	0.95 0.80	0.25	0.30 0.19	0.2 0.1	6.6 6.4	4.5 4.3	0.65	6.6 6.2	1	0.75 0.50	0.4 0.3	0.2	0.13	0.1	0.5 0.2	8° 0°

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT360-1		MO-153				99-12-27 03-02-19

Fig. 6. Package outline SOT360-1 (TSSOP20)

Octal buffer/line driver; 3-state




Fig. 7. Package outline SOT764-1 (DHVQFN20)

Octal buffer/line driver; 3-state

12. Abbreviations

Table 11. Abbreviations

Acronym	Description	
CDM	Charge Device Model	
DUT	Device Under Test	
ESD	ElectroStatic Discharge	
НВМ	Human Body Model	
TTL	Transistor-Transistor Logic	

13. Revision history

Table 12. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes		
74AHCT541A v.8	20230927	Product data sheet	-	74AHCT541A v.7		
Modifications:	guidelines of Legal texts Section 2 u Section 2: E	 The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia. Legal texts have been adapted to the new company name where appropriate. Section 2 updated. Section 2: ESD specification updated according to the latest JEDEC standard. Section 7: Derating values for P_{tot} total power dissipation updated. 				
74AHCT541A v.7	20170317	Product data sheet	-	74AHCT541A v.6		
Modifications:	Added type	Added type number 74AHCT541ABQ (SOT764-1)				
74AHCT541A v.6	20161102	Product data sheet	-	74AHCT541A v.5		
Modifications:	Type number	Type number 74AHCT541ABQ removed.				
74AHCT541A v.5	20160613	Product data sheet	-	74AHCT541A v.4		
Modifications:	• <u>Table 6</u> : I _I li	<u>Table 6</u> : I _I limits corrected (errata).				
74AHCT541A v.4	20160419	Product data sheet	-	74AHCT541A v.3		
Modifications:	• <u>Table 6</u> : cor	 <u>Table 6</u>: conditions for additional supply current (ΔI_{CC}) corrected. 				
74AHCT541A v.3	20160224	Product data sheet	-	74AHCT541A v.2		
Modifications:	• <u>Table 7</u> : C _P	<u>Table 7</u> : C _{PD} value corrected (errata).				
74AHCT541A v.2	20160127	Product data sheet	-	74AHCT541A v.1		
Modifications:	• <u>Table 7</u> : cor	<u>Table 7</u> : conditions C _{PD} corrected (errata).				
74AHCT541A v.1	20151223	Product data sheet	-	-		

Octal buffer/line driver; 3-state

14. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at https://www.nexperia.com.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by sustained.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Octal buffer/line driver; 3-state

Contents

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 27 September 2023

[©] Nexperia B.V. 2023. All rights reserved