

74AHC1G17-Q100; 74AHCT1G17-Q100

Single Schmitt trigger buffer

Rev. 3 — 15 September 2023

Product data sheet

1. General description

The 74AHC1G17-Q100 and 74AHCT1G17-Q100 are single buffers with Schmitt-trigger inputs. Inputs are overvoltage tolerant. This feature allows the use of these devices as translators in mixed voltage environments.

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

2. Features and benefits

- Automotive product qualification in accordance with AEC-Q100 (Grade 1)
 - Specified from -40 °C to +85 °C and from -40 °C to +125 °C
- Wide supply voltage range from 2.0 to 5.5 V
- Overvoltage tolerant inputs to 5.5 V
- · High noise immunity
- · CMOS low power dissipation
- Latch-up performance exceeds 100 mA per JESD 78 Class II Level A
- · Symmetrical output impedance
- Balanced propagation delays
- Input levels:
 - For 74AHC1G17-Q100: CMOS level
 - For 74AHCT1G17-Q100: TTL level
- SOT353-1 package option
- ESD protection:
 - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2000 V
 - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V

3. Applications

- Wave and pulse shapers
- Astable multivibrators
- Monostable multivibrators

4. Ordering information

Table 1. Ordering information

Type number	Package						
	Temperature range	Name	Description	Version			
74AHC1G17GW-Q100 74AHCT1G17GW-Q100	-40 °C to +125 °C	TSSOP5	plastic thin shrink small outline package; 5 leads; body width 1.25 mm	SOT353-1			




5. Marking

Table 2. Marking codes

Type number	Marking code[1]
74AHC1G17GW-Q100	AJ
74AHCT1G17GW-Q100	Cl


^[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.

6. Functional diagram



7. Pinning information

7.1. Pinning



7.2. Pin description

Table 3. Pin description

Symbol	Pin	Description
n.c.	1	not connected
A	2	data input
GND	3	ground (0 V)
Υ	4	data output
V _{CC}	5	supply voltage

8. Functional description

Table 4. Function table

H = HIGH voltage level; L = LOW voltage level

Input	Output
A	Υ
L	L
Н	Н

9. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{CC}	supply voltage			-0.5	+7.0	V
VI	input voltage			-0.5	+7.0	V
I _{IK}	input clamping current	V _I < -0.5 V		-20	-	mA
I _{OK}	output clamping current	$V_{O} < -0.5 \text{ V or } V_{O} > V_{CC} + 0.5 \text{ V}$	[1]	-	±20	mA
Io	output current	$-0.5 \text{ V} < \text{V}_{\text{O}} < \text{V}_{\text{CC}} + 0.5 \text{ V}$		-	±25	mA
I _{CC}	supply current			-	75	mA
I _{GND}	ground current			-75	-	mA
T _{stg}	storage temperature			-65	+150	°C
P _{tot}	total power dissipation	T _{amb} = -40 °C to +125 °C	[2]	-	250	mW

^[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

^[2] For SOT353-1 (TSSOP5) package: Ptot derates linearly with 3.3 mW/K above 74 °C.

10. Recommended operating conditions

Table 6. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	74Al	74AHC1G17-Q100 74AHCT			CT1G17	Γ1G17-Q100		
			Min	Тур	Max	Min	Тур	Max		
V _{CC}	supply voltage		2.0	5.0	5.5	4.5	5.0	5.5	V	
VI	input voltage		0	-	5.5	0	-	5.5	V	
Vo	output voltage		0	-	V _{CC}	0	-	V _{CC}	V	
T _{amb}	ambient temperature		-40	+25	+125	-40	+25	+125	°C	

11. Static characteristics

Table 7. Static characteristics

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		25 °C		-40 °C to +85 °C		-40 °C to +125 °C		Unit
			Min	Тур	Max	Min	Max	Min	Max	
74AHC1	G17-Q100							<u>'</u>	-	
V _{OH}	HIGH-level	$V_I = V_{T+}$ or V_{T-}								
	output voltage	I _O = -50 μA; V _{CC} = 2.0 V	1.9	2.0	-	1.9	-	1.9	-	V
		I _O = -50 μA; V _{CC} = 3.0 V	2.9	3.0	-	2.9	-	2.9	-	V
		I _O = -50 μA; V _{CC} = 4.5 V	4.4	4.5	-	4.4	-	4.4	-	V
		I_{O} = -4.0 mA; V_{CC} = 3.0 V	2.58	-	-	2.48	-	2.40	-	V
		I_{O} = -8.0 mA; V_{CC} = 4.5 V	3.94	-	-	3.8	-	3.70	-	V
V _{OL}	LOW-level	$V_I = V_{T+}$ or V_{T-}								
	output voltage	I _O = 50 μA; V _{CC} = 2.0 V	-	0	0.1	-	0.1	-	0.1	V
		I _O = 50 μA; V _{CC} = 3.0 V	-	0	0.1	-	0.1	-	0.1	V
		I _O = 50 μA; V _{CC} = 4.5 V	-	0	0.1	-	0.1	-	0.1	V
		$I_O = 4.0 \text{ mA}; V_{CC} = 3.0 \text{ V}$	-	-	0.36	-	0.44	-	0.55	V
		$I_O = 8.0 \text{ mA}; V_{CC} = 4.5 \text{ V}$	-	-	0.36	-	0.44	-	0.55	V
l _l	input leakage current	V _I = 5.5 V or GND; V _{CC} = 0 V to 5.5 V	-	-	0.1	-	1.0	-	2.0	μΑ
I _{CC}	supply current	$V_I = V_{CC}$ or GND; $I_O = 0$ A; $V_{CC} = 5.5 \text{ V}$	-	-	1.0	-	10	-	40	μΑ
Cı	input capacitance		-	1.5	10	-	10	-	10	pF
74AHCT	1G17-Q100	I			1					
V _{OH}	HIGH-level	$V_{I} = V_{T+} \text{ or } V_{T-}; V_{CC} = 4.5 \text{ V}$								T
	output voltage	I _O = -50 μA	4.4	4.5	-	4.4	-	4.4	-	V
		I _O = -8.0 mA	3.94	-	-	3.8	-	3.70	-	V
V _{OL}	LOW-level	$V_{I} = V_{T+} \text{ or } V_{T-}; V_{CC} = 4.5 \text{ V}$								
	output voltage	Ι _Ο = 50 μΑ	-	0	0.1	-	0.1	-	0.1	V
		I _O = 8.0 mA	-	-	0.36	-	0.44	-	0.55	V
l _l	input leakage current	V _I = 5.5 V or GND; V _{CC} = 0 V to 5.5 V	-	-	0.1	-	1.0	-	2.0	μA

Symbol	Parameter	Conditions		25 °C		-40 °C to +85 °C		-40 °C to +125 °C		Unit
			Min	Тур	Max	Min	Max	Min	Max	
I _{CC}		$V_I = V_{CC}$ or GND; $I_O = 0$ A; $V_{CC} = 5.5 \text{ V}$	-	-	1.0	-	10	-	40	μA
ΔI _{CC}		per input pin; $V_I = 3.4 \text{ V}$; other inputs at V_{CC} or GND; $I_O = 0 \text{ A}$; $V_{CC} = 5.5 \text{ V}$	-	-	1.35	-	1.5	-	1.5	mA
C _I	input capacitance		-	1.5	10	-	10	-	10	pF


11.1. Transfer characteristics

Table 8. Transfer characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V). See Fig. 4 and Fig. 5.

Symbol	Parameter	Conditions		25 °C		-40 °C to +85 °C		-40 °C to +125 °C		Unit
			Min	Тур	Max	Min	Max	Min	Max	
74AHC1	G17-Q100									
V_{T+}	positive-going	V _{CC} = 3.0 V	-	-	2.2	-	2.2	-	2.2	V
	threshold voltage	V _{CC} = 4.5 V	-	-	3.15	-	3.15	-	3.15	V
	voitage	V _{CC} = 5.5 V	-	-	3.85	-	3.85	-	3.85	V
V _{T-}	negative-	V _{CC} = 3.0 V	0.9	-	-	0.9	-	0.9	-	V
	going threshold	V _{CC} = 4.5 V	1.35	-	-	1.35	-	1.35	-	V
	voltage	V _{CC} = 5.5 V	1.65	-	-	1.65	-	1.65	-	V
V _H	hysteresis	V _{CC} = 3.0 V	0.3	-	1.2	0.3	1.2	0.25	1.2	V
	voltage	V _{CC} = 4.5 V	0.4	-	1.4	0.4	1.4	0.35	1.4	V
		V _{CC} = 5.5 V	0.5	-	1.6	0.5	1.6	0.45	1.6	V
74AHCT	1G17-Q100								•	
V_{T+}	positive-going	V _{CC} = 4.5 V	-	-	2.0	-	2.0	-	2.0	V
	threshold voltage	V _{CC} = 5.5 V	-	-	2.0	-	2.0	-	2.0	V
V _{T-}	negative-	V _{CC} = 4.5 V	0.5	-	-	0.5	-	0.5	-	V
thr	going threshold voltage	V _{CC} = 5.5 V	0.6	-	-	0.6	-	0.6	-	V
V_{H}	hysteresis	V _{CC} = 4.5 V	0.4	-	1.4	0.4	1.4	0.35	1.4	V
	voltage	V _{CC} = 5.5 V	0.4	-	1.6	0.4	1.6	0.35	1.6	V

11.2. Transfer characteristic waveforms






Fig. 6. Typical 74AHC1G17-Q100 transfer characteristics; V_{CC} = 3.0 V






Fig. 7. Typical 74AHC1G17-Q100 transfer characteristics; V_{CC} = 4.5 V





12. Dynamic characteristics

Table 9. Dynamic characteristics

GND = 0 V; $t_r = t_f \le 3.0$ ns. For waveform, see Fig. 11. For test circuit, see Fig. 12.

Symbol	Parameter	Conditions			25 °C		-40 °C to +85 °C		-40 °C to +125 °C		Unit
				Min	Тур	Max	Min	Max	Min	Max	
74AHC1	G17-Q100										
t _{pd}		A to Y	[1]								
	delay	V _{CC} = 3.0 V to 3.6 V	[2]								
		C _L = 15 pF		-	4.2	12.8	1.0	15.0	1.0	16.5	ns
		C _L = 50 pF		-	6.0	16.3	1.0	18.5	1.0	20.5	ns
		V _{CC} = 4.5 V to 5.5 V	[3]								
		C _L = 15 pF		-	3.2	8.6	1.0	10.0	1.0	11.0	ns
		C _L = 50 pF		-	4.6	10.6	1.0	12.0	1.0	13.5	ns
C _{PD}	power dissipation capacitance	per buffer; C _L = 50 pF; f = 1 MHz; V _I = GND to V _{CC}	[4]	-	12	-	-	-	-	-	pF
74AHCT	1G17-Q100					'					
t _{pd}	propagation delay	A to Y V _{CC} = 4.5 V to 5.5 V	[1] [3]								
		C _L = 15 pF		-	4.1	7.0	1.0	8.0	1.0	9.0	ns
		C _L = 50 pF		-	5.9	8.5	1.0	10.0	1.0	11.0	ns
C _{PD}	power dissipation capacitance	per buffer; C _L = 50 pF; f = 1 MHz; V _I = GND to V _{CC}	[4]	-	13	-	-	-	-	-	pF

- t_{pd} is the same as t_{PLH} and t_{PHL} . Typical values are measured at V_{CC} = 3.3 V. [2]
- Typical values are measured at $V_{CC} = 5.0 \text{ V}$. C_{PD} is used to determine the dynamic power dissipation P_D (μ W). $P_D = C_{PD} \times V_{CC}^2 \times f_i + \Sigma (C_L \times V_{CC}^2 \times f_o)$ where:

 f_i = input frequency in MHz; f_o = output frequency in MHz;

 C_L = output load capacitance in pF; V_{CC} = supply voltage in V.

12.1. Waveform and test circuit




Table 10. Test data

Table 101 100t auta						
Type number	Input	Output				
	V _I	V _M	V _M			
74AHC1G17-Q100	GND to V _{CC}	0.5 × V _{CC}	0.5× V _{CC}			
74AHCT1G17-Q100	GND to 3.0 V	1.5 V	0.5 × V _{CC}			

Product data sheet


13. Application information

The slow input rise and fall times cause additional power dissipation, which can be calculated using the following formula:

 $P_{add} = f_i \times (t_r \times \Delta I_{CC(AV)} + t_f \times \Delta I_{CC(AV)}) \times V_{CC}$ where:


- P_{add} = additional power dissipation (μW);
- f_i = input frequency (MHz);
- t_r = input rise time (ns); 10 % to 90 %;
- t_f = input fall time (ns); 90 % to 10 %;
- ΔI_{CC(AV)} = average additional supply current (µA).

Average additional I_{CC} differs with positive or negative input transitions, as shown in <u>Fig. 13</u> and Fig. 14.



Linear change of V_I between $0.1 V_{CC}$ to $0.9 V_{CC}$

Fig. 13. Average additional I_{CC} for 74AHC1G17-Q100 Schmitt trigger devices



Linear change of V_I between 0.1V_{CC} to 0.9V_{CC}

Fig. 14. Average additional I_{CC} for 74AHCT1G17-Q100 Schmitt trigger devices

14. Package outline




Fig. 15. Package outline SOT353-1 (TSSOP5)

15. Abbreviations

Table 11. Abbreviations

Acronym	Description				
CDM	Charged Device Model				
CMOS	Complementary Metal-Oxide Semiconductor				
DUT	Device Under Test				
ESD	ElectroStatic Discharge				
НВМ	Human Body Model				
TTL	Transistor-Transistor Logic				

16. Revision history

Table 12. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes	
74AHC_AHCT1G17_Q100 v.3	20230915	Product data sheet	-	74AHC_AHCT1G17_Q100 v.2	
Modifications:	<u>Section 2</u> : ESD specification updated according to the latest JEDEC standard.				
74AHC_AHCT1G17_Q100 v.2	20220112	Product data sheet	-	74AHC_AHCT1G17_Q100 v.1	
Modifications:	 The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia. Legal texts have been adapted to the new company name where appropriate. Section 2 updated. Fig. 15: Package outline drawing for SOT353-1 (TSSOP5) has changed. Section 9: Derating values for P_{tot} total power dissipation updated. 				
74AHC_AHCT1G17_Q100 v.1	20160308	Product data sheet	-	-	

17. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at https://www.nexperia.com.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own triple.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1.	General description	1
2.	Features and benefits	. 1
3.	Applications	. 1
4.	Ordering information	1
5.	Marking	. 2
6.	Functional diagram	2
7.	Pinning information	2
7.1	. Pinning	2
7.2	. Pin description	. 3
8.	Functional description	. 3
9.	Limiting values	. 3
10.	Recommended operating conditions	4
11.	Static characteristics	4
11.	1. Transfer characteristics	5
11.	2. Transfer characteristic waveforms	. 6
12.	Dynamic characteristics	. 7
12.	Waveform and test circuit	. 8
13.	Application information	. 9
44	Package outline	
14.	Package outline	10
	Abbreviations	
15.	-	11

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 15 September 2023

[©] Nexperia B.V. 2023. All rights reserved