Product data sheet

#### 1 **General description**

The 74ALVT16244 is a high-performance BiCMOS product designed for  $V_{CC}$  operation at 2.5V or 3.3V with I/O compatibility up to 5V.

This device is a 16-bit buffer and line driver featuring non-inverting 3-state bus outputs. The device can be used as four 4-bit buffers, two 8-bit buffers, or one 16-bit buffer.

#### Features and benefits 2

- 16-bit bus interface
- 3-State buffers
- 5V I/O compatible
- Output capability: +64 mA/–32 mA
- TTL input and output switching levels
- Input and output interface capability to systems at 5 V supply
- · Bus-hold data inputs eliminate the need for external pull-up resistors to hold unused inputs
- · Live insertion/extraction permitted
- Power-up 3-State
- No bus current loading when output is tied to 5 V bus
- Latch-up protection:
  - JESD17: exceeds 500 mA
- ESD protection:
  - MIL STD 883 method 3015: exceeds 2000 V
  - MM exceeds 200 V


#### 3 **Ordering information**

Table 1.	Ordering	information
----------	----------	-------------

Type number	Package									
	Temperature range	Name	Description	Version						
74ALVT16244DGG	-40 °C to +85 °C	TSSOP48	plastic thin shrink small outline package; 48 leads; body width 6.1 mm	SOT362-1						

# nexperia


# 4 Functional diagram



2/15

# 5 Pinning information

#### 5.1 Pinning



### 5.2 Pin description

Symbol	Pin	Description
10E, 20E, 30E, 40E	1, 48, 25, 24	output enable inputs (active LOW)
1A0, 1A1, 1A2, 1A3	47, 46, 44, 43	data inputs
2A0, 2A1, 2A2, 2A3	41, 40, 38, 37	data inputs
3A0, 3A1, 3A2, 3A3	36, 35, 33, 32	data inputs
4A0, 4A1, 4A2, 4A3	30, 29, 27, 26	data inputs
1Y0, 1Y1, 1Y2, 1Y3	2, 3, 5, 6	data outputs
2Y0, 2Y1, 2Y2, 2Y3	8, 9, 11, 12	data outputs
3Y0, 3Y1, 3Y2, 3Y3	13, 14, 16, 17	data outputs
4Y0, 4Y1, 4Y2, 4Y3	19, 20, 22, 23	data outputs
GND	4, 10, 15, 21, 28, 34, 39, 45	ground (0 V)
V <sub>CC</sub>	7, 18, 31, 42	supply voltage

## 6 Functional description

#### Table 3. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.

		Output
nŌE	nAn	nYn
L	L	L
L	Н	Н
Н	X	Z

# 7 Limiting values

#### Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC</sub>	supply voltage			-0.5	+4.6	V
VI	input voltage		[1]	-0.5	+7.0	V
Vo	output voltage	output in OFF-state or HIGH-state	[1]	-0.5	+7.0	V
I <sub>IK</sub>	input clamping current	V <sub>1</sub> < 0 V		-50	-	mA
I <sub>ОК</sub>	output clamping current	V <sub>O</sub> < 0 V		-50	-	mA
I <sub>O</sub>	output current	output in LOW-state		-	128	mA
		output in HIGH-state		-64	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
Tj	junction temperature		[2]	-	150	°C

[1] The input and output negative voltage ratings may be exceeded if the input and output clamp current ratings are observed.

[2] The performance capability of a high-performance integrated circuit in conjunction with its thermal environment can create junction temperatures which are detrimental to reliability.

# 8 Recommended operating conditions

#### Table 5. Recommended operating conditions

Symbol	Parameter	Conditions	$V_{CC}$ = 2.5 V ± 0.2 V		V <sub>CC</sub> = 3.3	V ± 0.3 V	Unit
			Min	Max	Min	Мах	
V <sub>CC</sub>	supply voltage		2.3	2.7	3.0	3.6	V
VI	input voltage		0	5.5	0	5.5	V
I <sub>OH</sub>	HIGH-level output current		-	-8	-	-32	mA
I <sub>OL</sub>	LOW-level output current	none	-	8	-	32	mA
		current duty cycle $\leq$ 50 %; f <sub>i</sub> $\geq$ 1 kHz	-	24	-	64	mA
Δt/ΔV	input transition rise and fall rate	outputs enabled	-	10	-	10	ns/V
T <sub>amb</sub>	ambient temperature	free-air	-40	+85	-40	+85	°C

### 9 Static characteristics

#### Table 6. Static characteristics

At recommended operating conditions;  $T_{amb} = -40$  °C to +85 °C; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Typ <sup>[1]</sup>	Мах	Unit				
$V_{CC} = 2.5 V \pm 0.2 V$										
V <sub>IK</sub>	input clamping voltage	V <sub>CC</sub> = 2.3 V; I <sub>IK</sub> = -18 mA	-	-0.85	-1.2	V				
V <sub>IH</sub>	HIGH-level input voltage	$V_{CC} = 2.5 V \pm 0.2 V$	1.7	-	-	V				
V <sub>IL</sub>	LOW-level input voltage	$V_{CC} = 2.5 V \pm 0.2 V$	-	-	0.7	V				

74ALVT16244 Product data sheet

# 74ALVT16244

### 16-bit buffer/line driver; 3-state

Symbol	Parameter	Conditions	Min	Typ <sup>[1]</sup>	Max	Unit
V <sub>OH</sub>	HIGH-level output voltage	tput voltage $V_{CC}$ = 2.5 V ± 0.2 V; I <sub>O</sub> = -100 µA		V <sub>CC</sub>	-	V
		V <sub>CC</sub> = 2.3 V; I <sub>O</sub> = -8 mA	1.8	2.5	-	V
V <sub>OL</sub>	LOW-level output voltage	V <sub>CC</sub> = 2.3 V; I <sub>O</sub> = 100 μA	-	0.07	0.2	V
		V <sub>CC</sub> = 2.3 V; I <sub>O</sub> = 24 mA	-	0.3	0.5	V
l <sub>l</sub>	input leakage current	all input pins	[2]			
		$V_{CC} = 0 V \text{ or } 2.7 V; V_{I} = 5.5 V$	-	0.1	10	μA
		control pins				
		$V_{CC}$ = 2.7 V; $V_{I}$ = $V_{CC}$ or GND	-	0.1	±1	μA
		data pins;	[2]			
		$V_{CC} = 2.7 \text{ V}; \text{ V}_{I} = V_{CC}$	-	0.1	1	μA
		V <sub>CC</sub> = 2.7 V; V <sub>I</sub> = 0 V	-	0.1	-5	μA
I <sub>OFF</sub>	power-off leakage current	$V_{CC}$ = 0 V; V <sub>I</sub> or V <sub>O</sub> = 0 V to 4.5 V	-	0.1	±100	μA
I <sub>BHL</sub>	bus hold LOW current	data inputs; $V_{CC}$ = 2.3 V; $V_{I}$ = 0.7 V	[3] _	115	-	μA
I <sub>BHH</sub>	bus hold HIGH current	data inputs; $V_{CC}$ = 2.3 V; $V_{I}$ = 1.7 V	[3] _	-10	-	μA
I <sub>EX</sub>	external current	output in HIGH-state when $V_O > V_{CC}$ ; $V_O = 5.5 V$ ; $V_{CC} = 2.3 V$	-	10	125	μA
I <sub>O(pu/pd)</sub>	power-up/power-down output current	$V_{CC} \le 1.2 \text{ V}; V_O = 0.5 \text{ V to } V_{CC};$ V <sub>I</sub> = GND or V <sub>CC</sub> ; nOE = don't care	[4] _	1	±100	μA
I <sub>OZ</sub>	OFF-state output current	$V_{CC}$ = 2.7 V; $V_{I}$ = $V_{IL}$ or $V_{IH}$				
l <sub>oz</sub>		output HIGH: V <sub>O</sub> = 2.3V	-	0.5	5	μA
		output LOW: V <sub>O</sub> = 0.5 V	-	0.5	-5	μA
I <sub>CC</sub>	supply current	$V_{CC}$ = 2.7 V; $V_{I}$ = GND or $V_{CC}$ ; $I_{O}$ = 0 A				_
		outputs HIGH	-	0.04	0.1	mA
		outputs LOW	-	2.5	4.5	mA
		outputs disabled	[5] _	0.04	0.1	mA
ΔI <sub>CC</sub>	additional supply current	per input pin; $V_{CC}$ = 2.3 V to 2.7 V; one input at $V_{CC}$ - 0.6 V; other inputs at $V_{CC}$ or GND	[6] _	0.04	0.4	mA
CI	input capacitance	$n\overline{OE}$ ; V <sub>I</sub> = 0 V or V <sub>CC</sub>	-	3	-	pF
Co	output capacitance	$V_{O} = 0 V \text{ or } V_{CC}$	-	9	-	pF
V <sub>CC</sub> = 3.3	V ± 0.3 V	1		<u> </u>	1	
V <sub>IK</sub>	input clamping voltage	V <sub>CC</sub> = 3.0 V; I <sub>IK</sub> = -18 mA	-	-0.85	-1.2	V
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 3.3 V ± 0.3 V	2.0	-	-	V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 3.3 V ± 0.3 V	-	-	0.8	V
V <sub>OH</sub>	HIGH-level output voltage	V <sub>CC</sub> = 3.3 V ± 0.3 V; I <sub>O</sub> = -100 μA	V <sub>CC</sub> - 0.2	V <sub>CC</sub>	-	V
		V <sub>CC</sub> = 3.0 V; I <sub>O</sub> = -32 mA	2.0	2.3	-	V

# 74ALVT16244

#### 16-bit buffer/line driver; 3-state

Symbol	Parameter	Conditions	Min	Typ <sup>[1]</sup>	Max	Unit
V <sub>OL</sub>	LOW-level output voltage	V <sub>CC</sub> = 3.0 V; I <sub>O</sub> = 100 μA	-	0.07	0.2	V
		V <sub>CC</sub> = 3.0 V; I <sub>O</sub> = 16 mA	-	0.25	0.4	V
		V <sub>CC</sub> = 3.0 V; I <sub>O</sub> = 32 mA	-	0.3	0.5	V
		V <sub>CC</sub> = 3.0 V; I <sub>O</sub> = 64 mA	-	0.4	0.55	V
I <sub>I</sub>	input leakage current	all input pins [2]				
		V <sub>CC</sub> = 0 V or 3.6 V; V <sub>I</sub> = 5.5 V	-	0.1	10	μA
		control pins				
		$V_{CC}$ = 3.6 V; $V_{I}$ = $V_{CC}$ or GND	-	0.1	±1	μA
		data pins [2]				
		$V_{CC} = 3.6 V; V_{I} = V_{CC}$	-	0.5	1	μA
		V <sub>CC</sub> = 3.6 V; V <sub>I</sub> = 0 V	-	0.1	-5	μA
I <sub>OFF</sub>	power-off leakage current	$V_{CC}$ = 0 V; V <sub>I</sub> or V <sub>O</sub> = 0 V to 4.5 V	-	0.1	±100	μA
I <sub>BHL</sub>	bus hold LOW current	data inputs; $V_{CC}$ = 3 V; $V_{I}$ = 0.8 V	75	130	-	μA
I <sub>BHH</sub>	bus hold HIGH current	data inputs; $V_{CC}$ = 3 V; $V_{I}$ = 2.0 V	-75	-140	-	μA
I <sub>BHLO</sub>	bus hold LOW overdrive current	data inputs; $V_{CC}$ = 3.6 V; $V_I$ = 0 V to 3.6 V <sup>[7]</sup>	500	-	-	μA
I <sub>BHHO</sub>	bus hold HIGH overdrive current	data inputs; $V_{CC}$ = 3.6 V; $V_I$ = 0 V to 3.6 V <sup>[7]</sup>	-500	-	-	μA
I <sub>EX</sub>	external current	output in HIGH-state when $V_O > V_{CC}$ ; $V_O = 5.5 V$ ; $V_{CC} = 3.0 V$	-	10	125	μA
I <sub>O(pu/pd)</sub>	power-up/power-down output current	$V_{CC} \le 1.2 \text{ V}; V_O = 0.5 \text{ V to } V_{CC};$ $V_I = \text{GND or } V_{CC}; n\overline{\text{OE}} = \text{don't care}$ <sup>[8]</sup>	-	1	±100	μA
I <sub>OZ</sub>	OFF-state output current	$V_{CC}$ = 3.6 V; $V_{I}$ = $V_{IL}$ or $V_{IH}$				
		output HIGH: V <sub>O</sub> = 3.0V	-	0.5	5	μA
		output LOW: $V_0 = 0.5 V$	-	0.5	-5	μA
I <sub>CC</sub>	supply current	$V_{CC}$ = 3.6 V; $V_{I}$ = GND or $V_{CC}$ ; $I_{O}$ = 0 A				
		outputs HIGH	-	0.05	0.1	mA
		outputs LOW	-	3.6	5	mA
		outputs disabled <sup>[5]</sup>	-	0.06	0.1	mA
ΔI <sub>CC</sub>	additional supply current	per input pin; $V_{CC}$ = 3 V to 3.6 V; <sup>[6]</sup> one input at $V_{CC}$ - 0.6 V; other inputs at $V_{CC}$ or GND	-	0.04	0.4	mA
CI	input capacitance	$n\overline{OE}$ ; V <sub>I</sub> = 0 V or V <sub>CC</sub>	-	3	-	pF
Co	output capacitance	$V_{O} = 0 V \text{ or } V_{CC}$		9		pF

[1] Typical values for V<sub>CC</sub> = 2.5 V  $\pm$  0.2 V are measured at V<sub>CC</sub> = 2.5 V and T<sub>amb</sub> = 25 °C.

Typical values for  $V_{CC}$  = 3.3 V ± 0.3 V are measured at  $V_{CC}$  = 3.3 V and  $T_{amb}$  = 25 °C. [2] Unused pins at  $V_{CC}$  or GND.

Not guaranteed.

[3] Not guaranteed.
 [4] This parameter is valid for any V<sub>CC</sub> between 0 V and 1.2 V with a transition time of up to 10 ms.

From  $V_{CC}$  = 1.2 V to  $V_{CC}$  = 2.5 V ± 0.2 V a transition time of 100 µs is permitted. This parameter is valid for  $T_{amb}$  = 25 °C only.

 $I_{CC}$  is measured with outputs pulled to  $V_{CC}$  or GND. [5]

This is the increase in supply current for each input at the specified voltage level other than  $V_{CC}$  or GND. [6]

This is the bus hold overdrive current required to force the input to the opposite logic state. [7]

This parameter is valid for any  $V_{CC}$  between 0 V and 1.2 V with a transition time of up to 10 ms. [8]

From V<sub>CC</sub> = 1.2 V to V<sub>CC</sub> = 3.3 V  $\pm$  0.3 V a transition time of 100  $\mu$ s is permitted. This parameter is valid for T<sub>amb</sub> = 25 °C only.

All information provided in this document is subject to legal disclaimers.

**Product data sheet** 

74ALVT16244

© Nexperia B.V. 2018. All rights reserved.

# **10** Dynamic characteristics


#### Table 7. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V);  $T_{amb} = -40$  °C to +85 °C; for test circuit see Figure 6.

Symbol	Parameter	Conditions	Min	Typ <sup>[1]</sup>	Max	Unit						
V <sub>CC</sub> = 2.5	$V_{\rm CC} = 2.5  \rm V \pm 0.2  \rm V$											
t <sub>PLH</sub>	LOW to HIGH propagation delay	nAn to nYn; see Figure 4	1.0	1.8	3.0	ns						
t <sub>PHL</sub>	HIGH to LOW propagation delay	nAn to nYn; see Figure 4	1.0	1.9	3.5	ns						
t <sub>PZH</sub>	OFF-state to HIGH propagation delay	nOE to nYn; see <u>Figure 5</u>	2.0	3.1	5.9	ns						
t <sub>PZL</sub>	OFF-state to LOW propagation delay	nOE to nYn; see <u>Figure 5</u>	1.5	2.5	4.7	ns						
t <sub>PHZ</sub>	HIGH to OFF-state propagation delay	nOE to nYn; see <u>Figure 5</u>	1.5	2.7	4.4	ns						
t <sub>PLZ</sub>	LOW to OFF-state propagation delay	nOE to nYn; see Figure 5	1.0	2.0	3.4	ns						
V <sub>CC</sub> = 3.3	V ± 0.3 V											
t <sub>PLH</sub>	LOW to HIGH propagation delay	nAn to nYn; see <u>Figure 4</u>	0.8	1.5	2.4	ns						
t <sub>PHL</sub>	HIGH to LOW propagation delay	nAn to nYn; see Figure 4	0.8	1.5	2.5	ns						
t <sub>PZH</sub>	OFF-state to HIGH propagation delay	nOE to nYn; see <u>Figure 5</u>	1.0	2.3	3.8	ns						
t <sub>PZL</sub>	OFF-state to LOW propagation delay	nOE to nYn; see Figure 5	0.5	1.8	2.9	ns						
t <sub>PHZ</sub>	HIGH to OFF-state propagation delay	nOE to nYn; see Figure 5	1.5	2.7	4.2	ns						
t <sub>PLZ</sub>	LOW to OFF-state propagation delay	nOE to nYn; see Figure 5	1.5	2.3	3.6	ns						

[1] Typical values for V<sub>CC</sub> = 2.5 V ± 0.2 V are measured at V<sub>CC</sub> = 2.5 V and T<sub>amb</sub> = 25 °C. Typical values for V<sub>CC</sub> = 3.3 V ± 0.3 V are measured at V<sub>CC</sub> = 3.3 V and T<sub>amb</sub> = 25 °C.

### 10.1 Waveforms and test circuit




Measurement points are given in <u>Table 8</u>.

 $V_{\text{OL}}$  and  $V_{\text{OH}}$  are typical voltage output levels that occur with the output load.

Figure 4. Inputs nAn to output nYn propagation delays

# 74ALVT16244

16-bit buffer/line driver; 3-state



measurement points are given in <u>Table o</u>.

 $V_{\text{OL}}$  and  $V_{\text{OH}}$  are typical voltage output levels that occur with the output load.


Figure 5. OFF-state to HIGH or LOW and HIGH or LOW to OFF-state propagation delays

#### Table 8. Measurement points

V <sub>cc</sub>	Input		Output			
	VI	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>	
$V_{CC} \le 2.7 V$	V <sub>CC</sub>	0.5 x V <sub>CC</sub>	0.5 x V <sub>CC</sub>	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V	
V <sub>CC</sub> ≥ 3.0 V	3.0 V	1.5 V	1.5 V	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V	

# 74ALVT16244

#### 16-bit buffer/line driver; 3-state



#### Table 9. Test data

Input			Load		V <sub>EXT</sub>			
VI	f <sub>i</sub>	tw	t <sub>r</sub> , t <sub>f</sub>	CL	RL	t <sub>PHZ</sub> , t <sub>PZH</sub>	t <sub>PLZ</sub> , t <sub>PZL</sub>	t <sub>PLH</sub> , t <sub>PHL</sub>
3.0 V or $V_{CC}$ whichever is less	≤ 10 MHz	500 ns	≤ 2.5 ns	50 pF	500 Ω	GND	6 V or $V_{CC}$ x 2	open

# 11 Package outline




Figure 7. Package outline SOT362-1 (TSSOP48)

# **12 Abbreviations**

Table 10. Abbreviations		
Acronym	Description	
BiCMOS	Bipolar Complementary Metal Oxide Semiconductor	
DUT	Device Under Test	
ESD	ElectroStatic Discharge	
MIL	Military	
ММ	Machine Model	
TTL	Transistor-Transistor Logic	

# **13 Revision history**

1	Table	11.	Revision	history
Г				

Document ID	Release date	Data sheet status	Change notice	Supersedes		
74ALVT16244 v.5	20180202	Product data sheet	-	74ALVT16244 v.4		
Modifications:	Nexperia. <ul> <li>Legal texts has</li> </ul>	<ul> <li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li>Type number 74ALVT16244DL (SOT370-1 / SSOP48) removed.</li> </ul>				
74ALVT16244 v.4	19981007	Product specification	-	74ALVT16244 v.3		
74ALVT16244 v.3	19980213	Product specification	-	74ALVT16244 v.2		
74ALVT16244 v.2	19980213	Product specification	-	74ALVT16244 v.1		
74ALVT16244 v.1	19960529	Product specification	-	-		

# 14 Legal information

#### 14.1 Data sheet status

Document status <sup>[1][2]</sup>	Product status <sup>[3]</sup>	Definition		
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.		
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.		
Product [short] data sheet	Production	This document contains the product specification.		

Please consult the most recently issued document before initiating or completing a design. [1]

The term 'short data sheet' is explained in section "Definitions".

[2] [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

#### 14.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### 14.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia. In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia

Right to make changes - Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use - Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer

No offer to sell or license - Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

74ALVT16244 **Product data sheet** 

# 74ALVT16244

#### 16-bit buffer/line driver; 3-state

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer

design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### 14.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

# 74ALVT16244

16-bit buffer/line driver; 3-state

#### Contents

1	General description	1
2	Features and benefits	1
3	Ordering information	1
4	Functional diagram	2
5	Pinning information	3
5.1	Pinning	
5.2	Pin description	4
6	Functional description	
7	Limiting values	
8	Recommended operating conditions	5
9	Static characteristics	5
10	Dynamic characteristics	8
10.1	Waveforms and test circuit	
11	Package outline	
12	Abbreviations	12
13	Revision history	12
14	Legal information	13

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© Nexperia B.V. 2018.

All rights reserved.

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com

Date of release: 2 February 2018 Document identifier: 74ALVT16244