74HC3GU04

Triple unbuffered inverter Rev. 6 — 29 January 2019

Product data sheet

1. General description

The 74HC3GU04 is a triple unbuffered inverter. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of V_{CC} .

2. Features and benefits

- Wide supply voltage range from 2.0 V to 6.0 V
- Symmetrical output impedance
- High noise immunity
- Low-power dissipation
- Balanced propagation delays
- Multiple package options
- ESD protection:
 - HBM JESD22-A114F exceeds 2000 V
 - MM JESD22-A115-A exceeds 200 V
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

3. Ordering information

Table 1. Ordering information

Type number	Package						
	Temperature range	Name	Description	Version			
74HC3GU04DP	-40 °C to +125 °C	TSSOP8	plastic thin shrink small outline package; 8 leads; body width 3 mm; lead length 0.5 mm	SOT505-2			
74HC3GU04DC	-40 °C to +125 °C	VSSOP8	plastic very thin shrink small outline package; 8 leads; body width 2.3 mm	SOT765-1			


4. Marking

Table 2. Marking					
Type number	Marking code[1]				
74HC3GU04DP	HU4				
74HC3GU04DC	HU4				

[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.




5. Functional diagram



6. Pinning information

6.1. Pinning



6.2. Pin description

Symbol	Pin	Description	
1A, 2A, 3A	1, 3, 6	data input	
1Y, 2Y, 3Y	7, 5, 2	data output	
GND	4	ground (0 V)	
V _{cc}	8	supply voltage	

7. Functional description

Table 4. Function table

H = *HIGH* voltage level; *L* = *LOW* voltage level.

Input	Output
nA	nY
L	Н
Н	L

74HC3GU04

8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{CC}	supply voltage			-0.5	+7.0	V
I _{IK}	input clamping current	$V_{\rm I}$ < -0.5 V or $V_{\rm I}$ > $V_{\rm CC}$ + 0.5 V	[1]	-	±20	mA
I _{ОК}	output clamping current	$V_{\rm O}$ < -0.5 V or $V_{\rm O}$ > $V_{\rm CC}$ + 0.5 V	[1]	-	±20	mA
lo	output current	$V_{\rm O}$ = -0.5 V to (V _{CC} + 0.5 V)	[1]	-	±25	mA
I _{CC}	quiescent supply current		[1]	-	50	mA
I _{GND}	ground current		[1]	-50	-	mA
T _{stg}	storage temperature			-65	+150	°C
P _{tot}	total power dissipation	T _{amb} = -40 °C to +125 °C	[2]	-	300	mW

[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

[2] For TSSOP8 package: above 55 °C the value of P_{tot} derates linearly with 2.5 mW/K.

For VSSOP8 package: above 110 °C the value of Ptot derates linearly with 8 mW/K.

9. Recommended operating conditions

Table 6. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V _{CC}	supply voltage		2.0	5.0	6.0	V
VI	input voltage		0	-	V _{CC}	V
Vo	output voltage		0	-	V _{CC}	V
T _{amb}	ambient temperature		-40	+25	+125	°C
Δt/ΔV	input transition rise and fall rate	V _{CC} = 2.0 V	-	-	625	ns/V
		V _{CC} = 4.5 V	-	1.67	139	ns/V
		V _{CC} = 6.0 V	-	-	83	ns/V

10. Static characteristics

Table 7. Static characteristics

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40 °C to +85 °C		5 °C	-40 °C t	Unit	
			Min	Typ[1]	Мах	Min	Max	
V _{IH}	HIGH-level input	V _{CC} = 2.0 V	1.7	1.1	-	1.7	-	V
voltage	voltage	V _{CC} = 4.5 V	3.6	2.4	-	3.6	-	V
		V _{CC} = 6.0 V	4.8	3.1	-	4.8	-	V
V _{IL}	LOW-level input voltage	V _{CC} = 2.0 V	-	0.9	0.3	-	0.3	V
		V _{CC} = 4.5 V	-	2.1	0.9	-	0.9	V
		V _{CC} = 6.0 V	-	2.9	1.2	-	1.2	V

74HC3GU04

Triple unbuffered inverter

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C t	Unit	
			Min	Typ[1]	Мах	Min	Max	
V _{OH}	HIGH-level output	$V_{I} = V_{IH} \text{ or } V_{IL}$						
	voltage	I_{O} = -20 µA; V_{CC} = 2.0 V	1.9	2.0	-	1.9	-	V
		I_{O} = -20 µA; V_{CC} = 4.5 V	4.4	4.5	-	4.4	-	V
		I_{O} = -20 µA; V_{CC} = 6.0 V	5.9	6.0	-	5.9	-	V
		I _O = -4.0 mA; V _{CC} = 4.5 V	4.13	4.32	-	3.7	-	V
		I _O = -5.2 mA; V _{CC} = 6.0 V	5.63	5.81	-	5.2	-	V
V _{OL} I	LOW-level output voltage	$V_{I} = V_{IH} \text{ or } V_{IL}$						
		I _O = 20 μA; V _{CC} = 2.0 V	-	0	0.1	-	0.1	V
		I_{O} = 20 µA; V_{CC} = 4.5 V	-	0	0.1	-	0.1	V
		I _O = 20 μA; V _{CC} = 6.0 V	-	0	0.1	-	0.1	V
		I _O = 4.0 mA; V _{CC} = 4.5 V	-	0.15	0.33	-	0.4	V
		I _O = 5.2 mA; V _{CC} = 6.0 V	-	0.16	0.33	-	0.4	V
l _l	input leakage current	$V_1 = V_{CC}$ or GND; $V_{CC} = 6.0 V$	-	-	±1.0	-	±1.0	μA
I _{CC}	supply current	per input pin; $V_I = V_{CC}$ or GND; $I_O = 0A$; $V_{CC} = 6.0 V$	-	-	10	-	20	μA
CI	input capacitance		-	3.0	-	-	-	pF

[1] All typical values are measured at T_{amb} = 25 °C.

11. Dynamic characteristics

Table 8. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 5.

Symbol Parameter		rameter Conditions		-40 °C to +85 °C			-40 °C to +125 °C	
			Min	Typ[1]	Max	Min	Max	
t _{pd}	propagation delay	nA to nY; see Fig. 4 [2]						
		V _{CC} = 2.0 V	-	13	75	-	90	ns
		V _{CC} = 4.5 V	-	6	15	-	18	ns
		V _{CC} = 6.0 V	-	5	13	-	15	ns
t _t	transition time	nY; see <u>Fig. 4</u> [3]						
		V _{CC} = 2.0 V	-	18	95	-	125	ns
		V _{CC} = 4.5 V	-	6	19	-	25	ns
		V _{CC} = 6.0 V	-	5	16	-	20	ns
C _{PD}	power dissipation capacitance	$V_{I} = GND \text{ to } V_{CC}$ [4]	-	5	-	-	-	pF

- All typical values are measured at T_{amb} = 25 °C. [1]
- t_{pd} is the same as t_{PLH} and t_{PHL} . [2]
- [3] t_t is the same as t_{TLH} and t_{THL} . [4] C_{PD} is used to determine the dynamic power dissipation (P_D in μ W).
 - $P_{D} = C_{PD} \times V_{CC}^{2} \times f_{i} \times N + \Sigma (C_{L} \times V_{CC}^{2} \times f_{o}) \text{ where:}$
 - f_i = input frequency in MHz;
 - fo = output frequency in MHz;
 - C_L = output load capacitance in pF;
 - V_{CC} = supply voltage in V;
 - N = number of inputs switching;

 $\Sigma(C_L \times V_{CC}^2 \times f_0)$ = sum of outputs.

11.1. Waveforms and test circuit




Table 9. Measurement points

Туре	Input	Output	
	V _M	V _M	
74HC3GU04	$0.5 \times V_{CC}$	$0.5 \times V_{CC}$	






Table 10. Test data


Туре	Input		Load		S1 position	
	VI	t _r , t _f	CL	R _L	t _{PHL} , t _{PLH}	
74HC3GU04	GND to V _{CC}	≤ 6 ns	50 pF	1 kΩ	open	

74HC3GU04









12. Typical transfer characteristics


74HC3GU04


13. Application information

Some applications for the 74HC3GU04 are:

- Linear amplifier (see Fig. 11)
- Crystal oscillator (see Fig. 13).

All values given are typical values unless otherwise specified.









Table 11. External components for resonator (f < 1 MHz)

Frequency	R1	R2	C1	C2
10 kHz to 15.9 kHz	2.2 ΜΩ	220 kΩ	56 pF	20 pF
16 kHz to 24.9 kHz	2.2 ΜΩ	220 kΩ	56 pF	10 pF
25 kHz to 54.9 kHz	2.2 ΜΩ	100 kΩ	56 pF	10 pF
55 kHz to 129.9 kHz	2.2 ΜΩ	100 kΩ	47 pF	5 pF
130 kHz to 199.9 kHz	2.2 ΜΩ	47 kΩ	47 pF	5 pF
200 kHz to 349.9 kHz	2.2 ΜΩ	47 kΩ	47 pF	5 pF
350 kHz to 600 kHz	2.2 ΜΩ	47 kΩ	47 pF	5 pF

Table 12. Optimum value for R2

Frequency	R2	Optimum	
3 kHz	2.0 kΩ	minimum required I _{CC}	
	8.0 kΩ	minimum influence due to change in V _{CC}	
6 kHz	1.0 kΩ	minimum required I _{CC}	
	4.7 kΩ	minimum influence by V_{CC}	
10 kHz	0.5 kΩ	minimum required I _{CC}	
	2.0 kΩ	minimum influence by V_{CC}	
14 kHz	0.5 kΩ	minimum required I _{CC}	
	2.0 kΩ	minimum influence by V_{CC}	
> 14 kHz	replace R2 by C3 = 35 pF (typical)		

14. Package outline



74HC3GU04

Triple unbuffered inverter




Fig. 15. Package outline SOT765-1 (VSSOP8)

15. Abbreviations

Table 13. Abbreviations			
Acronym	Description		
DUT	Device Under Test		
ESD	ElectroStatic Discharge		
НВМ	Human Body Model		
MM	Machine Model		

16. Revision history

Table 14. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes			
74HC3GU04 v.6	20190129	Product data sheet	-	74HC3GU04 v.5			
Modifications:	Nexperia. Legal texts have 	 The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia. Legal texts have been adapted to the new company name where appropriate. Type number 74HC3GU04GD (SOT996-2/XSON8) removed. 					
74HC3GU04 v.5	20131002	Product data sheet	-	74HC3GU04 v.4			
Modifications:	For type number	For type number 74HC3GU04GD XSON8U has changed to XSON8.					
74HC3GU04 v.4	20100111	Product data sheet	-	74HC3GU04 v.3			
Modifications:	Marking code f	Marking code for 74HC3GU04DP package changed from HU04 to HU4					
74HC3GU04 v.3	20090511	Product data sheet	-	74HC3GU04 v.2			
74HC3GU04 v.2	20031126	Product specification	-	74HC3GU04 v.1			
74HC3GU04 v.1	20030818	Product specification	-	-			

17. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	1
4. Marking	1
5. Functional diagram	2
6. Pinning information	2
6.1. Pinning	2
6.2. Pin description	2
7. Functional description	2
8. Limiting values	3
9. Recommended operating conditions	3
10. Static characteristics	3
11. Dynamic characteristics	
11.1. Waveforms and test circuit	5
11.2. Additional characteristics	6
12. Typical transfer characteristics	7
13. Application information	
14. Package outline	
15. Abbreviations	12
16. Revision history	12
17. Legal information	
-	

© Nexperia B.V. 2019. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 29 January 2019