

# 74HC9114; 74HCT9114

Nine wide Schmitt trigger buffer; open drain outputs; inverting

Rev. 4 — 9 November 2023

**Product data sheet** 

# 1. General description

The 74HC9114; 74HCT9114 is a 9-bit inverter with Schmitt trigger inputs and open drain outputs. This device features reduced input threshold levels to allow interfacing to TTL logic levels. Inputs also include clamp diodes, this enables the use of current limiting resistors to interface inputs to voltages in excess of V<sub>CC</sub>. Schmitt trigger inputs transform slowly changing input signals into sharply defined jitter-free output signals.

# 2. Features and benefits

- Wide operating voltage 2.0 V to 6.0 V
- CMOS low power dissipation
- High noise immunity
- Unlimited input rise and fall times
- Latch-up performance exceeds 100 mA per JESD 78 Class II Level B
- Complies with JEDEC standards:
  - JESD8C (2.7 V to 3.6 V)
  - JESD7A (2.0 V to 6.0 V)
- ESD protection:
  - HBM JESD22-A114F exceeds 2000 V
  - MM JESD22-A115-A exceeds 200 V
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C


# 3. Ordering information

#### Table 1. Ordering information

Type number	Package			
	Temperature range	Name	Description	Version
74HC9114D 74HCT9114D	-40 °C to +125 °C	SO20	plastic small outline package; 20 leads; body width 7.5 mm	<u>SOT163-1</u>




# 4. Functional diagram



# 5. Pinning information

### 5.1. Pinning



### 5.2. Pin description

Table 2. Pin description							
Symbol	Pin	Description					
A0, A1, A2, A3, A4, A5, A6, A7, A8	1, 2, 3, 4, 5, 6, 7, 8, 9	data input					
GND	10	ground (0 V)					
<u>Y0, Y1, Y2, Y3, Y4, Y5, Y6, Y7, Y8</u>	19, 18, 17, 16, 15, 14, 13, 12, 11	data output					
V <sub>CC</sub>	20	supply voltage					

# 6. Functional description

#### Table 3. Function table

*H* = *HIGH* voltage level; *L* = *LOW* voltage level; *Z* = *high-impedance OFF-state*.

Input	Output
An	Yn
L	Z
Н	L

## 7. Limiting values

#### Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC</sub>	supply voltage			-0.5	+7.0	V
I <sub>IK</sub>	input clamping current	$V_{I}$ < -0.5 V or $V_{I}$ > $V_{CC}$ + 0.5 V	[1]	-	±20	mA
I <sub>OK</sub>	output clamping current	$V_{\rm O}$ < -0.5 V or $V_{\rm O}$ > $V_{\rm CC}$ + 0.5 V	[1]	-	±20	mA
lo	output current	$-0.5 V < V_O < V_{CC} + 0.5 V$	[1]	-	±25	mA
I <sub>CC</sub>	supply current			-	50	mA
I <sub>GND</sub>	ground current			-50	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C	[2]	-	500	mW

[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

[2] For SOT163-1 (SO20) package:  $P_{tot}$  derates linearly with 12.3 mW/K above 109 °C.

## 8. Recommended operating conditions

#### Table 5. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	7	74HC9114			74HCT9114			
			Min	Тур	Max	Min	Тур	Мах	1	
V <sub>CC</sub>	supply voltage		2.0	5.0	6.0	4.5	5.0	5.5	V	
VI	input voltage		0	-	V <sub>CC</sub>	0	-	V <sub>CC</sub>	V	
Vo	output voltage		0	-	V <sub>CC</sub>	0	-	V <sub>CC</sub>	V	
T <sub>amb</sub>	ambient temperature		-40	+25	+125	-40	+25	+125	°C	

# 9. Static characteristics

#### Table 6. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		+25 °C	;	-40 °C t	o +85 °C	-40 °C to	o +125 °C	Unit
			Min	Тур	Мах	Min	Max	Min	Max	
74HC91	14		1			I				
V <sub>OH</sub>	HIGH-level	$V_{I} = V_{T+}$ or $V_{T-}$								
	output voltage	I <sub>O</sub> = -20 μA; V <sub>CC</sub> = 2.0 V	1.9	2.0	-	1.9	-	1.9	-	V
		I <sub>O</sub> = -20 μA; V <sub>CC</sub> = 4.5 V	4.4	4.5	-	4.4	-	4.4	-	V
		I <sub>O</sub> = -20 μA; V <sub>CC</sub> = 6.0 V	5.9	6.0	-	5.9	-	5.9	-	V
		I <sub>O</sub> = -4.0 mA; V <sub>CC</sub> = 4.5 V	3.98	4.32	-	3.84	-	3.7	-	V
		I <sub>O</sub> = -5.2 mA; V <sub>CC</sub> = 6.0 V	5.48	5.81	-	5.34	-	5.2	-	V
V <sub>OL</sub>	LOW-level	$V_{I} = V_{T+}$ or $V_{T-}$								
	output voltage	I <sub>O</sub> = 20 μA; V <sub>CC</sub> = 2.0 V	-	0	0.1	-	0.1	-	0.1	V
		I <sub>O</sub> = 20 μA; V <sub>CC</sub> = 4.5 V	-	0	0.1	-	0.1	-	0.1	V
		I <sub>O</sub> = 20 μA; V <sub>CC</sub> = 6.0 V	-	0	0.1	-	0.1	-	0.1	V
		I <sub>O</sub> = 4.0 mA; V <sub>CC</sub> = 4.5 V	-	0.15	0.26	-	0.33	-	0.4	V
		I <sub>O</sub> = 5.2 mA; V <sub>CC</sub> = 6.0 V	-	0.16	0.26	-	0.33	-	0.4	V
lı	input leakage current	$V_{I} = V_{CC}$ or GND; $V_{CC} = 6.0$ V	-	-	±0.1	-	±1.0	-	±1.0	μA
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $I_O = 0$ A; $V_{CC} = 6.0$ V	-	-	8.0	-	80	-	160	μA
CI	input capacitance		-	3.5	-	-	-	-	-	pF
74HCT9	114	1	1		1	I	1	1	1	1
V <sub>OH</sub>	HIGH-level	$V_{I} = V_{T+}$ or $V_{T-}$ ; $V_{CC} = 4.5 V$								
	output voltage	Ι <sub>O</sub> = -20 μΑ	4.4	4.5	-	4.4	-	4.4	-	V
		I <sub>O</sub> = -4.0 mA	3.98	4.32	-	3.84	-	3.7	-	V
V <sub>OL</sub>	LOW-level	$V_{I} = V_{T+}$ or $V_{T-}$ ; $V_{CC} = 4.5 V$								
	output voltage	I <sub>O</sub> = 20 μA;	-	0	0.1	-	0.1	-	0.1	V
		I <sub>O</sub> = 4.0 mA;	-	0.15	0.26	-	0.33	-	0.4	V
lı	input leakage current	$V_{I} = V_{CC}$ or GND; $V_{CC} = 5.5 V$	-	-	±0.1	-	±1.0	-	±1.0	μA
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $I_O = 0$ A; $V_{CC} = 5.5$ V	-	-	8.0	-	80	-	160	μA
ΔI <sub>CC</sub>	additional supply current	per An input pin; $I_O = 0 A$ ; $V_{CC} = 4.5 V \text{ to } 5.5 V$ ; $V_I = V_{CC} - 2.1 V$ ; other inputs at $V_{CC}$ or GND	-	30	108	-	135	-	147	μA
CI	input capacitance		-	3.5	-	-	-	-	-	pF

# **10.** Dynamic characteristics

#### Table 7. Dynamic characteristics

 $GND = 0 V; C_L = 50 pF;$  for test circuit see Fig. 4.

Symbol	Parameter	Conditions		+25 °C	;	-40 °C to +85 °C		-40 °C to	o +125 °C	Unit
			Min	Тур	Max	Min	Мах	Min	Max	
74HC91	14				1			I	1	
t <sub>pd</sub>	propagation	An to $\overline{Yn}$ ; see <u>Fig. 3</u> [1	]							
	delay	V <sub>CC</sub> = 2.0 V	-	36	110	-	140	-	165	ns
		V <sub>CC</sub> = 4.5 V	-	13	22	-	28	-	33	ns
		V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF	-	12	-	-	-	-	-	ns
		V <sub>CC</sub> = 6.0 V	-	10	19	-	24	-	28	ns
t <sub>THL</sub>	HIGH to LOW	Yn; see <u>Fig. 3</u>								
	output transition time	V <sub>CC</sub> = 2.0 V	-	19	75	-	95	-	110	ns
	une	V <sub>CC</sub> = 4.5 V	-	7	15	-	19	-	22	ns
		V <sub>CC</sub> = 6.0 V	-	6	13	-	16	-	19	ns
C <sub>PD</sub>	power dissipation capacitance	per buffer; $V_1$ = GND to $V_{CC}$ [2	] -	5	-	-	-	-	-	pF
74HCT9	114									
t <sub>pd</sub>	propagation	An to Yn; see Fig. 3 [1	]							
	delay	V <sub>CC</sub> = 4.5 V	-	17	31	-	39	-	47	ns
		V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF	-	13	-	-	-	-	-	ns
t <sub>THL</sub>	HIGH to LOW output transition time	<u>Yn;</u> V <sub>CC</sub> = 4.5 V; see <u>Fig. 3</u>	-	7	15	-	19	-	22	ns
C <sub>PD</sub>	power dissipation capacitance	per buffer; [2 $V_I$ = GND to $V_{CC}$ - 1.5 V	] -	5	-	-	-	-	-	pF

f<sub>i</sub> = input frequency in MHz;


fo = output frequency in MHz;

C<sub>L</sub> = output load capacitance in pF;

V<sub>CC</sub> = supply voltage in V;

N = number of inputs switching;  $\sum (C_L \times V_{CC}^2 \times f_o)$  = sum of outputs.

### 10.1. Waveforms and test circuit




### Fig. 3. Input to output propagation delays and HIGH to LOW output transition time

#### Table 8. Measurement points

Туре	Input	Output	
	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>
74HC9114	0.5 × V <sub>CC</sub>	$0.5 \times V_{CC}$	0.1 × V <sub>CC</sub>
74HCT9114	1.3 V	1.3 V	0.1 × V <sub>CC</sub>

# 74HC9114; 74HCT9114

### Nine wide Schmitt trigger buffer; open drain outputs; inverting



#### Table 9. Test data

Туре	Input		Load		S1 position		
	VI	t <sub>r</sub> , t <sub>f</sub>	CL	R <sub>L</sub>	t <sub>PHL</sub> , t <sub>PLH</sub>	t <sub>PZL</sub> , t <sub>PLZ</sub>	
74HC9114	V <sub>CC</sub>	6 ns	15 pF, 50 pF	1 kΩ	open	V <sub>CC</sub>	
74HCT9114	3 V	6 ns	15 pF, 50 pF	1 kΩ	open	V <sub>CC</sub>	


# **11. Transfer characteristics**

#### Table 10. Transfer characteristics


At recommended operating conditions; voltages are referenced to GND (ground = 0 V); see Fig. 5 and Fig. 6.

Symbol	Parameter	Conditions		+25 °C		-40 °C t	o +85 °C	-40 °C to	o +125 °C	Unit
			Min	Тур	Max	Min	Мах	Min	Max	
74HC91	14	I				I			1	-
V <sub>T+</sub>	positive-going threshold	V <sub>CC</sub> = 2.0 V	0.70	1.13	1.50	0.70	1.50	0.70	1.50	V
	voltage	V <sub>CC</sub> = 4.5 V	1.75	2.37	3.15	1.75	3.15	1.75	3.15	V
		V <sub>CC</sub> = 6.0 V	2.30	3.11	4.20	2.30	4.20	2.30	4.20	V
V <sub>T-</sub>	7 <sub>T-</sub> negative-going threshold voltage	V <sub>CC</sub> = 2.0 V	0.30	0.70	1.10	0.30	1.10	0.30	1.10	V
		V <sub>CC</sub> = 4.5 V	1.35	1.80	2.40	1.35	2.40	1.35	2.40	V
		V <sub>CC</sub> = 6.0 V	1.8	2.43	3.30	1.80	3.30	1.80	3.30	V
V <sub>H</sub>	hysteresis voltage	V <sub>CC</sub> = 2.0 V	0.2	0.43	0.80	0.18	0.80	0.15	0.80	V
		V <sub>CC</sub> = 4.5 V	0.4	0.57	1.00	0.40	1.00	0.40	1.00	V
		V <sub>CC</sub> = 6.0 V	0.5	0.68	1.10	0.50	1.10	0.50	1.10	V
74HCT9	114								1	
V <sub>T+</sub>	positive-going threshold	V <sub>CC</sub> = 4.5 V	0.9	1.50	2.0	0.9	2.0	0.9	2.0	V
	voltage	V <sub>CC</sub> = 5.5 V	1.2	1.70	2.1	1.2	2.1	1.2	2.1	V
V <sub>T-</sub>	negative-going	V <sub>CC</sub> = 4.5 V	0.7	1.06	1.4	0.7	1.4	0.7	1.4	V
	threshold voltage	V <sub>CC</sub> = 5.5 V	0.8	1.27	1.7	0.8	1.7	0.8	2.7	V
V <sub>H</sub>	hysteresis voltage	V <sub>CC</sub> = 4.5 V	0.2	0.44	0.8	0.2	0.8	0.2	0.8	V
		V <sub>CC</sub> = 5.5 V	0.2	0.44	0.8	0.2	0.8	0.2	0.8	V

### 11.1. Transfer characteristics waveforms



# 12. Package outline



#### Fig. 7. Package outline SOT163-1 (SO20)

74HC\_HCT9114

# 13. Abbreviations

Table 11. Abbrevi	ations
Acronym	Description
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model
MM	Machine Model

# 14. Revision history

### Table 12. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes					
74HC_HCT9114 v.4	20231109	Product data sheet	-	74HC_HCT9114 v.3					
Modifications:		<u>Section 1</u> and <u>Section 2</u> updated. <u>Section 7</u> : Derating values for P <sub>tot</sub> total power dissipation updated.							
74HC_HCT9114 v.3	20171002	Product data sheet	-	74HC_HCT9114 v.2					
Modifications:	guidelines	t of this data sheet has been of Nexperia. In have been adapted to the	-						
74HC_HCT9114 v.2	19901201	Product specification	-	74HC_HCT9114 v.1					
74HC_HCT9114 v.1	19880301	Product specification	-	-					

# 15. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

# Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	1
4. Functional diagram	2
5. Pinning information	2
5.1. Pinning	2
5.2. Pin description	3
6. Functional description	3
7. Limiting values	3
8. Recommended operating conditions	3
9. Static characteristics	4
10. Dynamic characteristics	5
10.1. Waveforms and test circuit	6
11. Transfer characteristics	8
11.1. Transfer characteristics waveforms	8
12. Package outline	9
13. Abbreviations	10
14. Revision history	10
15. Legal information	

© Nexperia B.V. 2023. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 9 November 2023

74HC\_HCT9114