## 1. General description

The 74LV138 decodes three binary weighted address inputs (A0, A1 and A2) to eight mutually exclusive outputs ( $\overline{Y}0$  to  $\overline{Y}7$ ). The 74LV138 features three enable inputs ( $\overline{Y}1$ ,  $\overline{Y}2$  and E3). Every output will be HIGH unless  $\overline{Y}1$  and  $\overline{Y}2$  are LOW and E3 is HIGH. This multiple enable function allows easy parallel expansion of the 74LV138 to a 1-of-32 (5 to 32 lines) decoder with just four 74LV138 ICs and one inverter. The 74LV138 can be used as an eight output demultiplexer by using one of the active LOW enable inputs as the data input and the remaining enable inputs as strobes. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess  $V_{CC}$ .

## 2. Features and benefits

- Wide supply voltage range from 1.0 to 5.5 V
- Optimized for low voltage applications: 1.0 V to 3.6 V
- · CMOS low power dissipation
- · Direct interface with TTL levels
- Typical output ground bounce < 0.8 V at V<sub>CC</sub> = 3.3 V and T<sub>amb</sub> = 25 °C
- Typical HIGH-level output voltage (V<sub>OH</sub>) undershoot: > 2 V at V<sub>CC</sub> = 3.3 V and T<sub>amb</sub> = 25 °C
- Demultiplexing capability
- · Multiple input enable for easy expansion
- · Ideal for memory chip select decoding
- · Active LOW mutually exclusive outputs
- Latch-up performance exceeds 100 mA per JESD 78 Class II Level B
- Complies with JEDEC standards
  - JESD8-7 (1.65 V to 1.95 V)
  - JESD8-5 (2.3 V to 2.7 V)
  - JESD8C (2.7 V to 3.6 V)
  - JESD36 (4.5 V to 5.5 V)
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2000 V
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V
- Multiple package options
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C




3-to-8 line decoder/demultiplexer; inverting

# 3. Ordering information

**Table 1. Ordering information** 

Type number	Package								
	Temperature range	Name	Description	Version					
74LV138D	-40 °C to +125 °C	SO16	plastic small outline package; 16 leads; body width 3.9 mm	SOT109-1					
74LV138PW	-40 °C to +125 °C	TSSOP16	plastic thin shrink small outline package; 16 leads; body width 4.4 mm	SOT403-1					
74LV138BQ	-40 °C to +125 °C	DHVQFN16	plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 × 3.5 × 0.85 mm	SOT763-1					


# 4. Functional diagram



3-to-8 line decoder/demultiplexer; inverting

# 5. Pinning information

## 5.1. Pinning



## 5.2. Pin description

Table 2. Pin description

Symbol	Pin	Description
A0, A1, A2	1, 2, 3	address input
E1, E2	4, 5	enable input (active LOW)
E3	6	enable input (active HIGH)
GND	8	ground (0 V)
70, 71, 72, 73, 74, 75, 76, 77	15, 14, 13, 12, 11, 10, 9, 7	output
Vcc	16	supply voltage

3-to-8 line decoder/demultiplexer; inverting

# 6. Functional description

#### Table 3. Function table

 $H = HIGH \ voltage \ level; \ L = LOW \ voltage \ level; \ X = don't \ care$ 

Input					Output								
Ē1	E2	E3	A0	A1	A2	<b>∀</b> 0	<b>₹</b> 1	<b>∀</b> 2	<b>∀</b> 3	<b>∀</b> 4	<b> Y</b> 5	<b>∀</b> 6	<b>Y</b> 7
Н	Х	Х	Х	Х	Х	Н	Н	Н	Н	Н	Н	Н	Н
Χ	Н	Х	Х	Х	Х	Н	Н	Н	Н	Н	Н	Н	Н
Χ	Х	L	Х	Х	Х	Н	Н	Н	Н	Н	Н	Н	Н
L	L	Н	L	L	L	L	Н	Н	Н	Н	Н	Н	Н
L	L	Н	Н	L	L	Н	L	Н	Н	Н	Н	Н	Н
L	L	Н	L	Н	L	Н	Н	L	Н	Н	Н	Н	Н
L	L	Н	Н	Н	L	Н	Н	Н	L	Н	Н	Н	Н
L	L	Н	L	L	Н	Н	Н	Н	Н	L	Н	Н	Н
L	L	Н	Н	L	Н	Н	Н	Н	Н	Н	L	Н	Н
L	L	Н	L	Н	Н	Н	Н	Н	Н	Н	Н	L	Н
L	L	Н	Н	Н	Н	Н	Н	Н	Н	Н	Н	Н	L

# 7. Limiting values

#### **Table 4. Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC</sub>	supply voltage		-0.5	+7.0	V
I <sub>IK</sub>	input clamping current	$V_1 < -0.5 \text{ V or } V_1 > V_{CC} + 0.5 \text{ V}$ [1]	-	±20	mA
I <sub>OK</sub>	output clamping current	$V_O < -0.5 \text{ V or } V_O > V_{CC} + 0.5 \text{ V}$ [1]	-	±50	mA
Io	output current	$V_O = -0.5 \text{ V to } (V_{CC} + 0.5 \text{ V})$	-	±25	mA
I <sub>CC</sub>	supply current		-	50	mA
I <sub>GND</sub>	ground current		-50	-	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
P <sub>tot</sub>	total power dissipation	$T_{amb}$ = -40 °C to +125 °C [2]	-	500	mW

<sup>[1]</sup> The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

<sup>[2]</sup> For SOT109-1 (SO16) package: P<sub>tot</sub> derates linearly with 12.4 mW/K above 110 °C. For SOT403-1 (TSSOP16) package: P<sub>tot</sub> derates linearly with 8.5 mW/K above 91 °C. For SOT763-1 (DHVQFN16) package: P<sub>tot</sub> derates linearly with 11.2 mW/K above 106 °C.

3-to-8 line decoder/demultiplexer; inverting

# 8. Recommended operating conditions

#### Table 5. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>CC</sub>	supply voltage	[1]	1.0	3.3	5.5	V
VI	input voltage		0	-	V <sub>CC</sub>	V
Vo	output voltage		0	-	V <sub>CC</sub>	V
T <sub>amb</sub>	ambient temperature		-40	+25	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CC</sub> = 1.0 V to 2.0 V	-	-	500	ns/V
		V <sub>CC</sub> = 2.0 V to 2.7 V	-	-	200	ns/V
		V <sub>CC</sub> = 2.7 V to 3.6 V	-	-	100	ns/V
		V <sub>CC</sub> = 3.6 V to 5.5 V	-	-	50	ns/V

<sup>[1]</sup> The static characteristics are guaranteed from  $V_{CC}$  = 1.2 V to  $V_{CC}$  = 5.5 V, but LV devices are guaranteed to function down to  $V_{CC}$  = 1.0 V (with input levels GND or  $V_{CC}$ ).

## 9. Static characteristics

#### **Table 6. Static characteristics**

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40	-40 °C to +85 °C			-40 °C to +125 °C	
			Min	Typ[1]	Max	Min	Max	
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 1.2 V	0.9	-	-	0.9	-	V
		V <sub>CC</sub> = 2.0 V	1.4	-	-	1.4	-	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	2.0	-	-	2.0	-	V
		V <sub>CC</sub> = 4.5 V to 5.5 V	0.7V <sub>CC</sub>	-	-	0.7V <sub>CC</sub>	-	V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 1.2 V	-	-	0.3	-	0.3	V
		V <sub>CC</sub> = 2.0 V	-	-	0.6	-	0.6	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	-	-	0.8	-	0.8	V
		V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	0.3V <sub>CC</sub>	-	0.3V <sub>CC</sub>	V
$V_{OH}$	HIGH-level output voltage	$V_I = V_{IH}$ or $V_{IL}$						
		$I_{O}$ = -100 $\mu$ A; $V_{CC}$ = 1.2 $V$	-	1.2	-	-	-	V
		$I_{O}$ = -100 $\mu$ A; $V_{CC}$ = 2.0 $V$	1.8	2.0	-	1.8	-	V
		$I_{O}$ = -100 $\mu$ A; $V_{CC}$ = 2.7 $V$	2.5	2.7	-	2.5	-	V
		$I_{O}$ = -100 $\mu$ A; $V_{CC}$ = 3.0 $V$	2.8	3.0	-	2.8	-	V
		$I_{O}$ = -100 $\mu$ A; $V_{CC}$ = 4.5 $V$	4.3	4.5	-	4.3	-	V
		$I_{O}$ = -6 mA; $V_{CC}$ = 3.0 V	2.4	2.82	-	2.2	-	V
		$I_{O}$ = -12 mA; $V_{CC}$ = 4.5 V	3.6	4.2	-	3.5	-	V

### 3-to-8 line decoder/demultiplexer; inverting

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
V <sub>OL</sub>	LOW-level output voltage	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>						
		$I_O = 100 \mu A; V_{CC} = 1.2 V$	-	0	-	-	-	V
		$I_O = 100 \mu A; V_{CC} = 2.0 V$	-	0	0.2	-	0.2	V
		$I_O = 100 \mu A; V_{CC} = 2.7 V$	-	0	0.2	-	0.2	V
		$I_O = 100 \mu A; V_{CC} = 3.0 V$	-	0	0.2	-	0.2	V
		$I_O = 100 \mu A; V_{CC} = 4.5 V$	-	0	0.2	-	0.2	V
		$I_O = 6 \text{ mA}; V_{CC} = 3.0 \text{ V}$	-	0.25	0.40	-	0.50	V
		$I_O = 12 \text{ mA}; V_{CC} = 4.5 \text{ V}$	-	0.35	0.55	-	0.65	V
I <sub>I</sub>	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 5.5 \text{ V}$	-	-	1.0	-	1.0	μA
I <sub>CC</sub>	supply current	$V_1 = V_{CC}$ or GND; $I_0 = 0$ A; $V_{CC} = 5.5 \text{ V}$	-	-	20.0	-	160	μΑ
ΔI <sub>CC</sub>	additional supply current	per input; V <sub>I</sub> = V <sub>CC</sub> - 0.6 V; V <sub>CC</sub> = 2.7 V to 3.6 V	-	-	500	-	850	μA
C <sub>I</sub>	input capacitance		-	3.5	-	-	-	pF

<sup>[1]</sup> Typical values are measured at  $T_{amb}$  = 25 °C.

# 10. Dynamic characteristics

**Table 7. Dynamic characteristics** 

GND = 0 V; For test circuit see Fig. 6.

Symbol	Parameter	rameter Conditions		-40	°C to +8	5 °C	-40 °C to	+125 °C	Unit
				Min	Typ[1]	Max	Min	Max	
t <sub>pd</sub>	propagation	An to ∀n; see Fig. 4	[2]						
	delay	V <sub>CC</sub> = 1.2 V		-	75	-	-	-	ns
		V <sub>CC</sub> = 2.0 V		-	26	44	-	55	ns
		V <sub>CC</sub> = 2.7 V		-	19	31	-	39	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V; C <sub>L</sub> = 15 pF	[3]	-	12	-	-	-	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	[3]	-	15	26	-	32	ns
		V <sub>CC</sub> = 4.5 V to 5.5 V		-	-	17	-	22	ns
		E3, En to Yn; see Fig. 4 and Fig. 5							
		V <sub>CC</sub> = 1.2 V		-	75	-	-	-	ns
		V <sub>CC</sub> = 2.0 V		-	26	43	-	53	ns
		V <sub>CC</sub> = 2.7 V		-	19	30	-	38	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V; C <sub>L</sub> = 15 pF	[3]	-	14	-	-	-	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	[3]	-	15	25	-	31	ns
		V <sub>CC</sub> = 4.5 V to 5.5 V		-	-	19	-	24	ns
C <sub>PD</sub>	power dissipation capacitance	$C_L$ = 50 pF; $f_i$ = 1 MHz; $V_I$ = GND to $V_{CC}$	[4]	-	45	-	-	-	pF

All typical values are measured at  $T_{amb}$  = 25 °C.

 $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ . Typical values are measured at nominal supply voltage ( $V_{CC}$  = 3.3 V).

 $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu$ W).  $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma (C_L \times V_{CC}^2 \times f_o)$  where: f<sub>i</sub> = input frequency in MHz; f<sub>o</sub> = output frequency in MHz;

 $C_L$  = output load capacitance in pF;  $V_{CC}$  = supply voltage in V; N = number of inputs switching;

 $<sup>\</sup>Sigma(C_L \times V_{CC}^2 \times f_0)$  = sum of the outputs.

### 3-to-8 line decoder/demultiplexer; inverting

## 10.1. Waveforms and test circuit




Fig. 4. The inputs An, E3 to outputs  $\overline{Y}$ n propagation delays





Fig. 5. The inputs  $\overline{E}$ n to outputs  $\overline{Y}$ n propagation delays

**Table 8. Measurement points** 

Supply voltage	Input	Output
V <sub>CC</sub>	V <sub>M</sub>	V <sub>M</sub>
< 2.7 V	0.5V <sub>CC</sub>	0.5V <sub>CC</sub>
2.7 V to 3.6 V	1.5 V	1.5 V
≥ 4.5 V	0.5V <sub>CC</sub>	0.5V <sub>CC</sub>

**Product data sheet** 

### 3-to-8 line decoder/demultiplexer; inverting



Test data is given in Table 9.

Definitions test circuit:

 $R_{T}$  = Termination resistance should be equal to output impedance  $Z_{\text{o}}$  of the pulse generator;

R<sub>L</sub> = Load resistance;

 $C_L$  = Load capacitance including jig and probe capacitance.

### Fig. 6. Test circuit for measuring switching times

#### Table 9. Test data

Supply voltage	nput				
V <sub>cc</sub>	t <sub>r</sub> , t <sub>f</sub>				
< 2.7 V	V <sub>CC</sub>	≤ 2.5 ns			
2.7 V to 3.6 V	2.7 V	≤ 2.5 ns			
≥ 4.5 V	V <sub>CC</sub>	≤ 2.5 ns			

### 3-to-8 line decoder/demultiplexer; inverting

# 11. Package outline




Fig. 7. Package outline SOT109-1 (SO16)

#### 3-to-8 line decoder/demultiplexer; inverting




Fig. 8. Package outline SOT403-1 (TSSOP16)

### 3-to-8 line decoder/demultiplexer; inverting

DHVQFN16: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 x 3.5 x 0.85 mm SOT763-1




Fig. 9. Package outline SOT763-1 (DHVQFN16)

3-to-8 line decoder/demultiplexer; inverting

## 12. Abbreviations

#### **Table 10. Abbreviations**

Acronym	Description			
CDM	Charged Device Model			
CMOS	olementary Metal Oxide Semiconductor			
DUT	Device Under Test			
ESD	ElectroStatic Discharge			
НВМ	Human Body Model			
TTL	Transistor-Transistor Logic			

# 13. Revision history

### **Table 11. Revision history**

Document ID	Release date	Data sheet status	Change notice	Supersedes		
74LV138 v.7	20240123	Product data sheet	-	74LV138 v.6		
Modifications:		SD specification updated B: Aligned SO and TSSO	•	atest JEDEC standard. drawings to JEDEC MS-012 and		
74LV138 v.6	20210722	Product data sheet	-	74LV138 v.5		
Modifications:	<ul> <li>Section 1 are</li> <li>Section 5.1:</li> </ul>	er 74LV138DB (SOT338- nd <u>Section 2</u> updated. pin configuration drawing rating values for P <sub>tot</sub> total	g added.			
74LV138 v.5	20180205	Product data sheet	-	74LV138 v.4		
Modifications:	guidelines o	of this data sheet has bee of Nexperia. have been adapted to the	· ·			
74LV138 v.4	20160304	Product data sheet	-	74LV138 v.3		
Modifications:	Type number	er 74LV138N (SOT38-4) r	removed.			
74LV138 v.3	20071115	Product data sheet	-	74LV138 v.2		
Modifications:	guidelines of Legal texts  Section 3: E  Section 7: d	mat of this data sheet has been redesigned to comply with the new identity less of NXP Semiconductors.  exts have been adapted to the new company name where appropriate.  3: DHVQFN16 package added.  7: derating values added for DHVQFN16 package.  butline drawing added for DHVQFN16 package.				
74LV138 v.2	19980428	Product specification	-	74LV138 v.1		
74LV138 v.1	19970203	Product specification	-	-		

# 14. Legal information

#### Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <a href="https://www.nexperia.com">https://www.nexperia.com</a>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

### 3-to-8 line decoder/demultiplexer; inverting

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by sustained.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

74LV138

All information provided in this document is subject to legal disclaimers

© Nexperia B.V. 2024. All rights reserved

### 3-to-8 line decoder/demultiplexer; inverting

# **Contents**

1. General description	1
2. Features and benefits	
3. Ordering information	2
4. Functional diagram	2
5. Pinning information	3
5.1. Pinning	3
5.2. Pin description	3
6. Functional description	4
7. Limiting values	4
8. Recommended operating	conditions5
9. Static characteristics	
10. Dynamic characteristics.	6
10.1. Waveforms and test circ	uit 7
11. Package outline	g
12. Abbreviations	12
13. Revision history	12
14. Legal information	

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 23 January 2024

<sup>©</sup> Nexperia B.V. 2024. All rights reserved