**Product data sheet** 

# 1. General description

Dual high-voltage switching diodes, encapsulated in a small SOT143B Surface-Mounted Device (SMD) plastic package.

## 2. Features and benefits

- High switching speed: t<sub>rr</sub> ≤ 50 ns
- Low leakage current
- Repetitive peak reverse voltage: V<sub>RRM</sub> ≤ 250 V
- Low capacitance: C<sub>d</sub> ≤ 2 pF
- Small SMD plastic package

# 3. Applications

- High-speed switching at high voltage
- · High-voltage general-purpose switching

## 4. Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Per diode					•	
I <sub>R</sub>	reverse current	V <sub>R</sub> = 200 V	-	-	100	nA
V <sub>R</sub>	reverse voltage		-	-	200	V
t <sub>rr</sub>	reverse recovery time	$I_F$ = 10 mA; $I_R$ = 10 mA; $I_{R(meas)}$ = 1 mA; $R_L$ = 100 Ω; $T_{amb}$ = 25 °C	-	-	50	ns

# 5. Pinning information

**Table 2. Pinning information** 

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	K1	cathode (diode 1)	4 0	4 3
2	K2	cathode (diode 2)	<u> </u>	
3	A2	anode (diode 2)		
4	A1	anode (diode 1)	1 2 SOT143B	1 2 006aab100



## **Dual high-voltage switching diodes**

# 6. Ordering information

#### **Table 3. Ordering information**

ype number Package						
	Name	Description	Version			
BAV23		plastic, surface-mounted package; 4 leads; 1.9 mm pitch; 2.9 mm x 1.3 mm x 1 mm body	SOT143B			

## 7. Marking

### Table 4. Marking codes

Type number	Marking code[1]
BAV23	%L3

[1] % = placeholder for manufacturing site code

## 8. Limiting values

#### **Table 5. Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
Per diode			'	<u> </u>	<u>'</u>	<u> </u>
V <sub>R</sub>	reverse voltage			-	200	V
$V_{RRM}$	repetitive peak reverse voltage			-	250	V
I <sub>F</sub>	forward current	Single diode loaded	[1]	-	225	mA
			[2]	-	125	mA
I <sub>FRM</sub>	repetitive peak forward current			-	625	mA
I <sub>FSM</sub>	non-repetitive peak forward current	t <sub>p</sub> = 1 μs; square wave	[3]	-	9	Α
		t <sub>p</sub> = 100 μs; square wave	[3]	-	3	Α
		t <sub>p</sub> = 10 ms; square wave	[3]	-	1.7	Α
Per device	-			'	'	
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> ≤ 25 °C	[4]	-	250	mW
T <sub>j</sub>	junction temperature			-	150	°C
T <sub>amb</sub>	ambient temperature			-65	150	°C
T <sub>stg</sub>	storage temperature			-65	150	°C

- [1] Single diode loaded.
- [2] Double diode loaded.
- [3]  $T_j = 25$  °C prior to surge.
- [4] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

### **Dual high-voltage switching diodes**

## 9. Thermal characteristics

**Table 6. Thermal characteristics** 

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
Per device							
$R_{th(j-a)}$	thermal resistance from junction to ambient	in free air	[1]	-	-	500	K/W
$R_{th(j-sp)}$	thermal resistance from junction to solder point			-	-	360	K/W

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

## 10. Characteristics

### **Table 7. Characteristics**

 $T_{amb}$  = 25 °C unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Per diode				'		
V <sub>F</sub>	forward voltage	I <sub>F</sub> = 100 mA	-	-	1	V
		I <sub>F</sub> = 200 mA	-	-	1.25	V
I <sub>R</sub>	reverse current	V <sub>R</sub> = 200 V	-	-	100	nA
		V <sub>R</sub> = 200 V; T <sub>j</sub> = 150 °C	-	-	100	μΑ
C <sub>d</sub>	diode capacitance	V <sub>R</sub> = 0 V; f = 1 MHz	-	-	2	pF
t <sub>rr</sub>	reverse recovery time	$I_F$ = 10 mA; $I_R$ = 10 mA; $I_{R(meas)}$ = 1 mA; $R_L$ = 100 Ω; $T_{amb}$ = 25 °C	-	-	50	ns





Fig. 1. Forward current as a function of forward voltage; typical values




Based on square wave currents.

T<sub>j(init)</sub> = 25 °C

Fig. 2. Non-repetitive peak forward current as a function of pulse duration; maximum values

**Nexperia** 


### **Dual high-voltage switching diodes**



(2) 
$$T_{amb} = 85^{\circ} C$$


(3) 
$$T_{amb} = 25^{\circ} C$$

Fig. 3. Reverse current as a function of reverse voltage; typical values



f = 1 MHz  $T_i = 25$  °C.

Fig. 4. Diode capacitance as a function of reverse voltage; typical values.




FR4 PCB, standard footprint

- (1) Single diode loaded
- (2) Double diode loaded


Forward current as a function of ambient temperature; derating curves Fig. 5.

## **Dual high-voltage switching diodes**

## 11. Test information




# 12. Package outline



## **Dual high-voltage switching diodes**

# 13. Soldering



## **Dual high-voltage switching diodes**

# 14. Revision history

## **Table 8. Revision history**

Table 6. Revision mistory			,	
Data sheet ID	Release date	Data sheet status	Change notice	Supersedes
BAV23 v.8	20230401	Product data sheet	-	BAV23_SER_7
Modifications:	<ul><li>The format of the of Nexperia.</li><li>Legal texts have</li><li>Product change</li></ul>	e been adapted to the new d to non-automotive qual product alternative(s).	edesigned to com	
BAV23_SER_7	20100319	Product data sheet	-	BAV23_SER_6
BAV23_SER_6	20080303	Product data sheet	-	BAV23S_5 BAV23_2
BAV23S_5	20011012	Product specification	-	BAV23S_4
BAV23_2	19960917	Product specification	-	BAV23_1

## **Dual high-voltage switching diodes**

## 15. Legal information

#### Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <a href="https://www.nexperia.com">https://www.nexperia.com</a>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

BAV23

All information provided in this document is subject to legal disclaimers.

© Nexperia B.V. 2023. All rights reserved

## **Dual high-voltage switching diodes**

## **Contents**

1.	General description	. 1
2.	Features and benefits	. 1
3.	Applications	. 1
4.	Quick reference data	. 1
5.	Pinning information	. 1
6.	Ordering information	. 2
7.	Marking	. 2
8.	Limiting values	2
9.	Thermal characteristics	3
10.	Characteristics	. 3
11.	Test information	. 5
12.	Package outline	. 5
	Soldering	
	Revision history	
	Legal information	

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 1 April 2023

<sup>©</sup> Nexperia B.V. 2023. All rights reserved