

## Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of <http://www.nxp.com>, <http://www.philips.com/> or <http://www.semiconductors.philips.com/>, use **<http://www.nexperia.com>**

Instead of [sales.addresses@www.nxp.com](mailto:sales.addresses@www.nxp.com) or [sales.addresses@www.semiconductors.philips.com](mailto:sales.addresses@www.semiconductors.philips.com), use **[salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)** (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:


- © **Nexperia B.V. (year). All rights reserved.**

If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **[salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia

# DATA SHEET



## **BC857M series** PNP general purpose transistors

Product data sheet  
Supersedes data of 2003 Jul 15

2004 Mar 10

## PNP general purpose transistors

## BC857M series

## FEATURES

- Leadless ultra small plastic package (1 mm × 0.6 mm × 0.5 mm)
- Board space 1.3 × 0.9 mm
- Power dissipation comparable to SOT23.

## APPLICATIONS

- General purpose small signal DC
- Low and medium frequency AC applications
- Mobile communications, digital (still) cameras, PDAs, PCMCIA cards.

## DESCRIPTION

PNP general purpose transistor in a SOT883 leadless ultra small plastic package.

NPN complement: BC847M series.

## MARKING


TYPE NUMBER	MARKING CODE
BC857AM	D1
BC857BM	D2
BC857CM	D3

## QUICK REFERENCE DATA

SYMBOL	PARAMETER	MAX.	UNIT
$V_{CEO}$	collector-emitter voltage	-45	V
$I_C$	collector current (DC)	-100	mA
$I_{CM}$	peak collector current	-200	mA

## PINNING

PIN	DESCRIPTION
1	base
2	emitter
3	collector



## ORDERING INFORMATION

TYPE NUMBER	PACKAGE		
	NAME	DESCRIPTION	VERSION
BC857AM	—	Leadless ultra small plastic package; 3 solder lands; body 1.0 x 0.6 x 0.5 mm	SOT883
BC857BM			
BC857CM			

## PNP general purpose transistors

## BC857M series

**LIMITING VALUES**

In accordance with the Absolute Maximum System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
$V_{CBO}$	collector-base voltage	open emitter	–	–50	V
$V_{CEO}$	collector-emitter voltage	open base	–	–45	V
$V_{EBO}$	emitter-base voltage	open collector	–	–5	V
$I_C$	collector current (DC)		–	–100	mA
$I_{CM}$	peak collector current		–	–200	mA
$I_{BM}$	peak base current		–	–100	mA
$P_{tot}$	total power dissipation	$T_{amb} \leq 25\text{ °C}$			
		note 1	–	250	mW
		note 2	–	430	mW
$T_{stg}$	storage temperature		–65	+150	°C
$T_j$	junction temperature		–	150	°C
$T_{amb}$	operating ambient temperature		–65	+150	°C

**Notes**

1. Refer to SOT883 standard mounting conditions (footprint), FR4 with 60 µm copper strip line.
2. Device mounted on a FR4 printed-circuit board, single-sided copper, mounting pad for collector 1 cm<sup>2</sup>.

**THERMAL CHARACTERISTICS**

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
$R_{th(j-a)}$	thermal resistance from junction to ambient	in free air		
		note 1	500	K/W
		note 2	290	K/W

**Notes**

1. Refer to SOT883 standard mounting conditions (footprint), FR4 with 60 µm copper strip line.
2. Device mounted on a FR4 printed-circuit board, single-sided copper, mounting pad for collector 1 cm<sup>2</sup>.

## PNP general purpose transistors

## BC857M series

**CHARACTERISTICS**

$T_{amb} = 25\text{ }^{\circ}\text{C}$  unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
$I_{CBO}$	collector-base cut-off current	$V_{CB} = -30\text{ V}; I_E = 0$	–	–15	nA
		$V_{CB} = -30\text{ V}; I_E = 0; T_J = 150\text{ }^{\circ}\text{C}$	–	–5	$\mu\text{A}$
$I_{EBO}$	emitter-base cut-off current	$V_{EB} = -5\text{ V}; I_C = 0$	–	–100	nA
$h_{FE}$	DC current gain BC857AM BC857BM BC857CM	$V_{CE} = -5\text{ V}; I_C = -2\text{ mA}$			
			125	250	
			220	475	
			420	800	
$V_{BE}$	base-emitter voltage	$I_C = -2\text{ mA}; V_{CE} = -5\text{ V}$	–600	–750	mV
		$I_C = -10\text{ mA}; V_{CE} = -5\text{ V}$	–	–820	mV
$V_{CEsat}$	collector-emitter saturation voltage	$I_C = -10\text{ mA}; I_B = -0.5\text{ mA}$	–	–200	mV
		$I_C = -100\text{ mA}; I_B = -5\text{ mA}; \text{note 1}$	–	–400	mV
$C_c$	collector capacitance	$I_E = i_e = 0; V_{CB} = -10\text{ V}; f = 1\text{ MHz}$	–	2.5	pF
$f_T$	transition frequency	$V_{CE} = -5\text{ V}; I_C = -10\text{ mA};$ $f = 100\text{ MHz}$	100	–	MHz
F	noise figure	$I_C = -200\text{ }\mu\text{A}; V_{CE} = -5\text{ V};$ $R_S = 2\text{ k}\Omega; f = 1\text{ kHz}; B = 200\text{ Hz}$	–	10	dB


**Note**

1. Pulse test:  $t_p \leq 300\text{ }\mu\text{s}; \delta \leq 0.02$ .

## PNP general purpose transistors

## BC857M series

## GRAPHICAL INFORMATION BC857AM




$V_{CE} = -5 \text{ V.}$

(1)  $T_{amb} = 150 \text{ }^{\circ}\text{C.}$

(2)  $T_{amb} = 25 \text{ }^{\circ}\text{C.}$

(3)  $T_{amb} = -55 \text{ }^{\circ}\text{C.}$

Fig.2 DC current gain; typical values.




$V_{CE} = -5 \text{ V.}$

(1)  $T_{amb} = -55 \text{ }^{\circ}\text{C.}$

(2)  $T_{amb} = 25 \text{ }^{\circ}\text{C.}$

(3)  $T_{amb} = 150 \text{ }^{\circ}\text{C.}$

Fig.3 Base-emitter voltage as a function of collector current; typical values.




$I_C/I_B = 20.$

(1)  $T_{amb} = 150 \text{ }^{\circ}\text{C.}$

(2)  $T_{amb} = 25 \text{ }^{\circ}\text{C.}$

(3)  $T_{amb} = -55 \text{ }^{\circ}\text{C.}$

Fig.4 Collector-emitter saturation voltage as a function of collector current; typical values.



$I_C/I_B = 20.$

(1)  $T_{amb} = -55 \text{ }^{\circ}\text{C.}$

(2)  $T_{amb} = 25 \text{ }^{\circ}\text{C.}$


(3)  $T_{amb} = 150 \text{ }^{\circ}\text{C.}$

Fig.5 Base-emitter saturation voltage as a function of collector current; typical values.

## PNP general purpose transistors

## BC857M series


## GRAPHICAL INFORMATION BC857BM



$V_{CE} = -5 \text{ V.}$

- (1)  $T_{amb} = 150 \text{ }^{\circ}\text{C.}$
- (2)  $T_{amb} = 25 \text{ }^{\circ}\text{C.}$
- (3)  $T_{amb} = -55 \text{ }^{\circ}\text{C.}$


Fig.6 DC current gain; typical values.



$V_{CE} = -5 \text{ V.}$

- (1)  $T_{amb} = -55 \text{ }^{\circ}\text{C.}$
- (2)  $T_{amb} = 25 \text{ }^{\circ}\text{C.}$
- (3)  $T_{amb} = 150 \text{ }^{\circ}\text{C.}$


Fig.7 Base-emitter voltage as a function of collector current; typical values.



$I_C/I_B = 20.$

- (1)  $T_{amb} = 150 \text{ }^{\circ}\text{C.}$
- (2)  $T_{amb} = 25 \text{ }^{\circ}\text{C.}$
- (3)  $T_{amb} = -55 \text{ }^{\circ}\text{C.}$

Fig.8 Collector-emitter saturation voltage as a function of collector current; typical values.



$I_C/I_B = 20.$





- (1)  $T_{amb} = -55 \text{ }^{\circ}\text{C.}$
- (2)  $T_{amb} = 25 \text{ }^{\circ}\text{C.}$
- (3)  $T_{amb} = 150 \text{ }^{\circ}\text{C.}$

Fig.9 Base-emitter saturation voltage as a function of collector current; typical values.

PNP general purpose transistors

BC857M series

GRAPHICAL INFORMATION BC857CM







PNP general purpose transistors

BC857M series

PACKAGE OUTLINE

Leadless ultra small plastic package; 3 solder lands; body 1.0 x 0.6 x 0.5 mm

SOT883



DIMENSIONS (mm are the original dimensions)

UNIT	A <sup>(1)</sup>	A <sub>1</sub> max.	b	b <sub>1</sub>	D	E	e	e <sub>1</sub>	L	L <sub>1</sub>
mm	0.50 0.46	0.03	0.20 0.12	0.55 0.47	0.62 0.55	1.02 0.95	0.35	0.65	0.30 0.22	0.30 0.22

Note

1. Including plating thickness

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT883			SC-101			03-02-05 03-04-03

## PNP general purpose transistors

## BC857M series

## DATA SHEET STATUS

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

## Notes

1. Please consult the most recently issued document before initiating or completing a design.
2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

## DISCLAIMERS

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions

above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

**Terms and conditions of sale** — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

# ***NXP Semiconductors***

## **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors. No changes were made to the content, except for the legal definitions and disclaimers.

## **Contact information**

For additional information please visit: **<http://www.nxp.com>**

For sales offices addresses send e-mail to: **[salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)**

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

R75/02/pp10

Date of release: 2004 Mar 10

Document order number: 9397 750 12839

founded by

**PHILIPS**