

BUK9K35-60RA

Dual N-channel 60 V, 35 mOhm logic level MOSFET in LFPAK56D using Repetitive Avalanche technology

2 December 2020 Product data sheet

1. General description

Dual, logic level N-channel MOSFET in an LFPAK56D package, using Application Specific (ASFET) repetitive avalanche silicon technology. This product has been designed and qualified to AEC-Q101 for use in repetitive avalanche applications.

2. Features and benefits

- Fully automotive qualified to AEC-Q101 at 175 °C
- Repetitive Avalanche rated to 30 °C T_i rise:
 - · Tested to 1 Bn avalanche events
- LFPAK copper clip package technology:
 - · High robustness and reliability
 - Gull wing leads for high manufacturability and AOI

3. Applications

- 12 V, 24 V and 48 V automotive systems
- · Repetitive avalanche topologies
- · Engine control
- Transmission control
- Actuator and auxiliary loads

4. Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V_{DS}	drain-source voltage	25 °C ≤ T _j ≤ 175 °C	-	-	60	V
I _D	drain current	V _{GS} = 5 V; T _{mb} = 25 °C; <u>Fig. 2</u>	-	-	22	А
P _{tot}	total power dissipation	T _{mb} = 25 °C; <u>Fig. 1</u>	-	-	38	W
Static chara	cteristics FET1 and FET2		•	'		
R _{DSon}	drain-source on-state resistance	$V_{GS} = 5 \text{ V}; I_D = 5 \text{ A}; T_j = 25 \text{ °C}; Fig. 15$	17	30.5	35	mΩ
Dynamic cha	aracteristics FET1 and FE	T2	•	<u>'</u>		
Q_{GD}	gate-drain charge	I _D = 5 A; V _{DS} = 48 V; V _{GS} = 5 V; T _j = 25 °C; <u>Fig. 17</u> ; <u>Fig. 18</u>	-	3	-	nC



5. Pinning information

Table 2. Pinning information

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	S1	source1	8 7 6 5	D1 D1 D2 D2
2	G1	gate1	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	
3	S2	source2		
4	G2	gate2		
5	D2	drain2		
6	D2	drain2		S1 G1 S2 G2
7	D1	drain1		mbk725
8	D1	drain1	LFPAK56D; Dual LFPAK (SOT1205)	

6. Ordering information

Table 3. Ordering information

Type number	Package	Package							
	Name	Description	Version						
BUK9K35-60RA	LFPAK56D; Dual LFPAK	plastic, single ended surface mounted package (LFPAK56D); 8 leads	SOT1205						

7. Marking

Table 4. Marking codes

Type number	Marking code
BUK9K35-60RA	93560RA

8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{DS}	drain-source voltage	25 °C ≤ T _j ≤ 175 °C		-	60	V
V_{DGR}	drain-gate voltage	25 °C ≤ T _j ≤ 175 °C; R _{GS} = 20 kΩ		-	60	V
V_{GS}	gate-source voltage	DC; T _j ≤ 175 °C		-10	10	V
		T _j ≤ 175 °C	[1] [2]	-15	15	V
P _{tot}	total power dissipation	T _{mb} = 25 °C; <u>Fig. 1</u>		-	38	W
I _D	drain current	V _{GS} = 5 V; T _{mb} = 25 °C; <u>Fig. 2</u>		-	22	А
		V _{GS} = 5 V; T _{mb} = 100 °C; <u>Fig. 2</u>		-	16	А
I _{DM}	peak drain current	pulsed; $t_p \le 10 \mu s$; $T_{mb} = 25 °C$; Fig. 3		-	90	А
T _{stg}	storage temperature			-55	175	°C
Tj	junction temperature			-55	175	°C
T _{sld(M)}	peak soldering temperature			-	260	°C

Symbol	Parameter	Conditions		Min	Max	Unit
	n diode FET1 and FET2					
Is	source current	T _{mb} = 25 °C		-	22	А
I _{SM}	peak source current	pulsed; t _p ≤ 10 μs; T _{mb} = 25 °C		-	90	А
Avalanche r	uggedness			'	-	
E _{DS(AL)R}	repetitive drain-source avalanche energy	I_D = 0.73 A; V_{sup} ≤ 60 V; R_{GS} = 10 Ω; V_{GS} =10 V; $T_{j(rise)}$ ≤ 30 °C; unclamped; $Fig. 4$; $Fig. 5$; $Fig. 6$	[3] [4] [5]	-	28.6	mJ
Avalanche r	uggedness FET1 and FET2			'	'	
E _{DS(AL)S}	non-repetitive drain- source avalanche energy	I_D = 22 A; $V_{sup} \le 60$ V; V_{GS} = 5 V; $T_{j(init)}$ = 25 °C; Fig. 7	[6] [7]	-	19.5	mJ

- [1] Accumulated Pulse duration up to 50 hours delivers zero defect ppm.
- [2] Significantly longer life times are achieved by lowering T_j and or V_{GS}
- [3] Repetitive avalanche rating is limited by maximum junction temperature of 175 °C and junction rise of 30 °C
- [4] Refer to Fig. 5 for the limiting number of avalanche events
- [5] Refer to Fig. 6 Rdson at Vgs=5V will increase as a function of repetitive avalanche cycles
- 6] Refer to application note AN10273 for further information
- [7] Single-pulse avalanche rating limited by maximum junction temperature of 175 °C




Fig. 1. Normalized total power dissipation as a function of mounting base temperature






Fig. 2. Continuous drain current as a function of mounting base temperature



 T_{mb} = 25 °C; I_{DM} is single pulse

Fig. 3. Safe operating area; continuous and peak drain current as a function of drain-source voltage



 T_i is limited to 175 °C and $T_{i \text{ (rise)}}$ is limited to 30 °C

Fig. 4. Repetitive avalanche rating; avalanche current as a function of avalanche time




Fig. 5. Repetitive avalanche rating; maximum number of avalanche events as a function of avalanche energy






Fig. 6. Percentage Rdson at 5V increase as a function of avalanche cycles



9. Thermal characteristics

Table 6. Thermal characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
R _{th(j-mb)}	thermal resistance from junction to mounting base	Fig. 8	-	-	3.96	K/W
$R_{th(j-a)}$		Minimum footprint; mounted on a printed circuit board	-	95	-	K/W



10. Characteristics

Table 7. Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit	
Static chara	acteristics FET1 and FET2						
V _{(BR)DSS}	drain-source	I _D = 250 μA; V _{GS} = 0 V; T _j = -55 °C	54	-	-	V	
breakd	breakdown voltage	I _D = 250 μA; V _{GS} = 0 V; T _j = 25 °C	60	-	-	V	
V _{GS(th)}	$V_{GS(th)}$	gate-source threshold voltage	I_D = 1 mA; V_{DS} = V_{GS} ; T_j = 25 °C; <u>Fig. 13</u> ; <u>Fig. 14</u>	1.4	1.7	2.1	V
		I _D = 1 mA; V _{DS} =V _{GS} ; T _j = 175 °C; Fig. 13; Fig. 14	0.5	-	-	V	
		I_D = 1 mA; V_{DS} = V_{GS} ; T_j = -55 °C; Fig. 13; Fig. 14	-	-	2.45	V	
I _{DSS}	drain leakage current	V _{DS} = 60 V; V _{GS} = 0 V; T _j = 175 °C	-	-	500	μA	
		V _{DS} = 60 V; V _{GS} = 0 V; T _j = 25 °C	-	0.02	1	μA	
I _{GSS}	gate leakage current	V _{GS} = -10 V; V _{DS} = 0 V; T _j = 25 °C	-	2	100	nA	
		V _{GS} = 10 V; V _{DS} = 0 V; T _j = 25 °C	-	2	100	nA	
R _{DSon}	drain-source on-state resistance	V _{GS} = 5 V; I _D = 5 A; T _j = 25 °C; <u>Fig. 15</u>	17	30.5	35	mΩ	
		V _{GS} = 5 V; I _D = 5 A; T _j = 175 °C; <u>Fig. 15;</u> <u>Fig. 16</u>	-	65.27	79	mΩ	
		V _{GS} = 10 V; I _D = 5 A; T _j = 25 °C; <u>Fig. 15</u>	15.5	26.8	32	mΩ	
Dynamic ch	naracteristics FET1 and FE	T2			'		
Q _{G(tot)}	total gate charge	I _D = 5 A; V _{DS} = 48 V; V _{GS} = 5 V;	-	7.8	-	nC	
Q _{GS}	gate-source charge	T _j = 25 °C; <u>Fig. 17</u> ; <u>Fig. 18</u>	-	1.2	-	nC	
Q_{GD}	gate-drain charge		-	3	-	nC	
C _{iss}	input capacitance	V _{DS} = 25 V; V _{GS} = 0 V; f = 1 MHz;	-	811	1081	pF	
C _{oss}	output capacitance	T _j = 25 °C; <u>Fig. 19</u>	-	98	118	pF	
C _{rss}	reverse transfer capacitance		-	51	70	pF	
t _{d(on)}	turn-on delay time	$V_{DS} = 48 \text{ V}; R_L = 10 \Omega; V_{GS} = 5 \text{ V};$	-	7.1	-	ns	
t _r	rise time	$R_{G(ext)} = 5 \Omega; T_j = 25 ^{\circ}C$	-	11.3	-	ns	
t _{d(off)}	turn-off delay time		-	14.9	-	ns	
t _f	fall time	1	-	10.6	-	ns	
Source-dra	in diode FET1 and FET2		'	1			
V _{SD}	source-drain voltage	I _S = 5 A; V _{GS} = 0 V; T _j = 25 °C; <u>Fig. 20</u>	-	0.78	1.2	V	
t _{rr}	reverse recovery time	$I_S = 5 \text{ A}; dI_S/dt = -100 \text{ A/}\mu\text{s}; V_{GS} = 0 \text{ V};$	-	17.6	-	ns	
Q _r	recovered charge	V _{DS} = 30 V; T _j = 25 °C	-	12.1	-	nC	




Fig. 9. Forward transconductance as a function of drain current; typical values




Fig. 10. Transfer Characteristic: drain current as a function of gate-source voltage; typical values




Fig. 11. Drain-source on-state resistance as a function of gate-source voltage; typical values




Fig. 12. Output characteristics: drain current as a function of drain-source voltage; typical values




Fig. 13. Gate-source threshold voltage as a function of junction temperature




Fig. 14. Sub-threshold drain current as a function of gate-source voltage




Fig. 15. Drain-source on-state resistance as a function of drain current; typical values




Fig. 16. Normalized drain-source on-state resistance factor as a function of junction temperature




Fig. 17. Gate charge waveform definitions




Fig. 18. Gate-source voltage as a function of gate charge; typical values





Fig. 19. Input, output and reverse transfer capacitances | Fig. 20. Source current as a function of source-drain as a function of drain-source voltage; typical values



voltage; typical values

11. Package outline





Fig. 21. Package outline LFPAK56D; Dual LFPAK (SOT1205)

12. Soldering



13. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at https://www.nexperia.com.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own right.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1.	General description	1
2.	Features and benefits	1
3.	Applications	1
4.	Quick reference data	1
5.	Pinning information	2
6.	Ordering information	2
7.	Marking	2
8.	Limiting values	2
9.	Thermal characteristics	5
10	. Characteristics	6
11.	. Package outline	10
12	. Soldering	11
	. Legal information	

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 2 December 2020

[©] Nexperia B.V. 2020. All rights reserved