

Dual voltage regulator diodes Rev. 2 — 10 April 2024

1. General description

General-purpose Zener diodes in a SOT23 small Surface-Mounted Device (SMD) plastic package.

2. Features and benefits

- Non-repetitive peak reverse power dissipation: ≤ 40 W
- Total power dissipation: ≤ 300 mW
- Two tolerance series: B = ±2 % and C = approximately ±5 %
- Working voltage range: nominal 2.4 V to 75 V (E24 range)
- · Small plastic package suitable for surface-mounted design
- Dual common anode configuration
- · Qualified according to AEC-Q101 and recommended for use in automotive applications

3. Applications

General regulation functions

4. Quick reference data

Symbol	Parameter	Conditions	Conditions		Тур	Мах	Unit
V _F	forward voltage	I _F = 10 mA	[1]	-	-	0.9	V
P _{ZSM}	non-repetitive peak reverse power dissipation		[2]	-	-	40	mW

[1] Pulse test: $t_p \le 300 \ \mu s$; $\delta \le 0.02$.

[2] $t_p = 100 \ \mu s$; square wave; $T_j = 25 \ ^\circ C$ prior to surge.



5. Pinning information

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	K1	cathode (diode 1)	□3	CA
2	K2	cathode (diode 2)		
3	CA	common anode		K1 K2 aaa-033766

6. Ordering information

Table 3. Ordering information

Type number	Package				
	Name	Description	Version		
BZB84-B2V4-Q to BZB84-C75- Q[1]	SOT23	plastic, surface-mounted package; 3 terminals; 1.9 mm pitch; 2.9 mm x 1.3 mm x 1 mm body	SOT23		

[1] The series consists of 74 types with nominal working voltages from 2.4 V to 75 V.

BZB84-Q_SER

7. Marking

Type number	Marking code	Type number	Marking code
BZB84-B2V4-Q	V9%	BZB84-C2V4-Q	U9%
BZB84-B2V7-Q	VA%	BZB84-C2V7-Q	UA%
BZB84-B3V0-Q	VB%	BZB84-C3V0-Q	UB%
BZB84-B3V3-Q	VC%	BZB84-C3V3-Q	UC%
BZB84-B3V6-Q	VD%	BZB84-C3V6-Q	UD%
BZB84-B3V9-Q	VE%	BZB84-C3V9-Q	UE%
BZB84-B4V3-Q	VF%	BZB84-C4V3-Q	UF%
BZB84-B4V7-Q	VG%	BZB84-C4V7-Q	UG%
BZB84-B5V1-Q	VH%	BZB84-C5V1-Q	UH%
BZB84-B5V6-Q	VK%	BZB84-C5V6-Q	UK%
BZB84-B6V2-Q	VL%	BZB84-C6V2-Q	UL%
BZB84-B6V8-Q	VM%	BZB84-C6V8-Q	UM%
BZB84-B7V5-Q	VN%	BZB84-C7V5-Q	UN%
BZB84-B8V2-Q	VP%	BZB84-C8V2-Q	UP%
BZB84-B9V1-Q	VR%	BZB84-C9V1-Q	UR%
BZB84-B10-Q	VS%	BZB84-C10-Q	US%
BZB84-B11-Q	VT%	BZB84-C11-Q	UT%
BZB84-B12-Q	VU%	BZB84-C12-Q	UU%
BZB84-B13-Q	VV%	BZB84-C13-Q	UV%
BZB84-B15-Q	VW%	BZB84-C15-Q	UW%
BZB84-B16-Q	PT%	BZB84-C16-Q	PB%
BZB84-B18-Q	PU%	BZB84-C18-Q	PC%
BZB84-B20-Q	RP%	BZB84-C20-Q	RQ%
BZB84-B22-Q	PV%	BZB84-C22-Q	PD%
BZB84-B24-Q	PW%	BZB84-C24-Q	PE%
BZB84-B27-Q	PX%	BZB84-C27-Q	PF%
BZB84-B30-Q	PY%	BZB84-C30-Q	PG%
BZB84-B33-Q	PZ%	BZB84-C33-Q	PH%
BZB84-B36-Q	RA%	BZB84-C36-Q	PJ%
BZB84-B39-Q	RB%	BZB84-C39-Q	PK%
BZB84-B43-Q	RC%	BZB84-C43-Q	PL%
BZB84-B47-Q	RD%	BZB84-C47-Q	PM%
BZB84-B51-Q	RE%	BZB84-C51-Q	PN%
BZB84-B56-Q	RF%	BZB84-C56-Q	PP%
BZB84-B62-Q	RG%	BZB84-C62-Q	PQ%
BZB84-B68-Q	RH%	BZB84-C68-Q	PR%
BZB84-B75-Q	RJ%	BZB84-C75-Q	PS%

8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
Per diode						
l _F	forward current			-	200	mA
I _{ZSM}	non-repetitive peak reverse current		[1]	-	see tables	8 and 9
P _{ZSM}	non-repetitive peak reverse power dissipation		[1]	-	40	W
Per device						
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C	[2]	-	300	mW
Tj	junction temperature			-	150	°C
T _{amb}	ambient temperature			-55	+150	°C
T _{stg}	storage temperature			-65	+150	°C

[1] $t_p = 100 \ \mu s$; square wave; $T_j = 25 \ ^\circ C$ prior to surge.

[2] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

9. Thermal characteristics

Table 6. Thermal characteristics

Symbol	Parameter	Conditions		Min	Тур	Мах	Unit		
Per device; single diode loaded									
R _{th(j-a)}	thermal resistance from junction to ambient	in free air	[1]	-	-	417	K/W		
R _{th(j-sp)}	thermal resistance from junction to solder point		[2]	-	-	100	K/W		

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Soldering point at pins 1 and 2.

10. Characteristics

Table 7. Characteristics

 T_i = 25 °C unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
V _F	forward voltage	I _F = 10 mA [1]	-	-	0.9	V

[1] Pulse test: $t_p \le 300 \ \mu s$; $\delta \le 0.02$

Table 8. Characteristics per type; BZB84-B2V4-Q to BZB84-C24-Q

$T_i = 25$ °C unless otherwise specified.

BZB84 -xxx-Q	Sel	Workin voltag V _Z (V)	ng	Differentia resistance r _{dif} (Ω)		Rever currer I _R (µA	nt	Temp coeffi S _Z (m		Diode capacitance C _d (pF) [1]	Non-repetitive peak reverse current	
		l _Z = 5 ı	mA	I _Z = 1 mA	l _Z = 5 mA			l _Z = 5	mA		I _{ZSM} (A) [2]	
		Min	Max	Max	Max	Мах	V _R (V)	Min	Max	Мах	Мах	
2V4	В	2.35	2.45	600	100	50	1	-3.5	0.0	450	6.0	
	С	2.20	2.60									
2V7	В	2.65	2.75	600	100	20	1	-3.5	0.0	450	6.0	
	С	2.50	2.90									
3V0	В	2.94	3.06	600	95	10	1	-3.5	0.0	450	6.0	
	С	2.80	3.20									
3V3	В	3.23	3.37	600	95	5	1	-3.5	0.0	450	6.0	
	С	3.10	3.50									
3V6	В	3.53	3.67	600	90	5	1	-3.5	0.0	450	6.0	
	С	3.40	3.80									
3V9	В	3.82	3.98	600	90	3	1	-3.5	0.0	450	6.0	
	С	3.70	4.10									
4V3	В	4.21	4.39	600	90	3	1	-3.5	0.0	450	6.0	
	С	4.00	4.60									
4V7	В	4.61	4.79	500	80	3	2	-3.5	0.2	300	6.0	
	С	4.40	5.00									
5V1	В	5.00	5.20	480	60	2	2	-2.7	1.2	300	6.0	
	С	4.80	5.40									
5V6	В	5.49	5.71	400	40	1	2	-2.0	2.5	300	6.0	
	С	5.20	6.00									
6V2	В	6.08	6.32	150	10	3	4	0.4	3.7	200	6.0	
	С	5.80	6.60									
6V8	В	6.66	6.94	80	15	2	4	1.2	4.5	200	6.0	
	С	6.40	7.20	-								
7V5	В	7.35	7.65	80	15	1	5	2.5	5.3	150	4.0	
	С	7.00	7.90									
8V2	В	8.04	8.36	80	15	0.7	5	3.2	6.2	150	4.0	
	С	7.70	8.70	-								
9V1	В	8.92	9.28	100	15	0.5	6	3.8	7.0	150	3.0	
	С	8.50	9.60	1								
10	В	9.80	10.20	150	20	0.2	7	4.5	8.0	90	3.0	
	С	9.40	10.60	1								
11	В	10.80	11.20	150	20	0.1	8	5.4	9.0	85	2.5	
	С	10.40	11.60	1								
12	В	11.80	12.20	150	25	0.1	8	6.0	10.0	85	2.5	
	С	11.40	12.70	1								
13	В	12.70	13.30	170	30	0.1	8	7.0	11.0	80	2.5	
	С	12.40	14.10	1								

5/14

Dual voltage regulator diodes

BZB84 -xxx-Q			ng e	Differential resistance r _{dif} (Ω)		current		Temperature coefficient S _Z (mV/K)		Diode capacitance C _d (pF) [1]	Non-repetitive peak reverse current	
		l _Z = 5 ı	mA	I _Z = 1 mA I _Z = 5 mA				l _Z = 5 mA			I _{ZSM} (A) [2]	
	Min	Max	Max	Max	Max	V _R (V)	Min	Max	Max	Мах		
15	В	14.70	15.30	200	30 0.05 10.5	9.2	13.0	75	2.0			
	С	13.80	15.60									
16	В	15.70	16.30	200	40	0.05	11.2	10.4	14.0	75	1.5	
	С	15.30	17.10									
18	В	17.60	18.40	225	225	45	0.05	12.6	12.4	16.0	70	1.5
	С	16.80	19.10									
20	В	19.60	20.40	225	55	0.05	14	14 14.4	18.0	60	1.5	
	С	18.80	21.20									
22	В	21.60	22.40	250	55	0.05	15.4	16.4	20.0	60	1.25	
	С	20.80	23.30									
24	В	23.50	24.50	250	70	0.05	16.8	18.4	22.0	55	1.25	
	С	22.80	25.60	1								

[1] f = 1 MHz; V_R = 0 V

[2] $t_p = 100 \ \mu s$; square wave; $T_j = 25 \ ^\circ C$ prior to surge

Dual voltage regulator diodes

Table 9. Characteristics per type; BZB84-B27-Q to BZB84-C75-Q


$T_i = 25 \text{ °C}$ unless otherwise specified.

BZB84 -xxx-Q	Sel	Worki voltag V _Z (V)		Differentia r _{dif} (Ω)	Il resistance	Rever currer I _R (µA)	nt	Temp coeffi S _Z (m		Diode capacitance C _d (pF) [1]	Non-repetitive peak reverse current	
		I _Z = 2 mA		I _Z = 0.5 I _Z = 2 mA mA				I _Z = 2	mA		I _{ZSM} (A) [2]	
		Min	Max	Max	Мах	Max	V _R (V)	Min	Max	Мах	Мах	
27	В	26.50	27.50	300	80	0.05	18.9	21.4 25.3	50	1.0		
	С	25.10	28.90									
30	B 29.4	29.40	30.60	300	80	0.05	21	24.4	29.4	50	1.0	
	С	28.00	32.00									
33	В	32.30	33.70	325	80	0.05	23.1	27.4	33.4	45	0.9	
	С	31.00	35.00									
36	B 35.30 36.7	36.70	350	90	0.05	25.2	30.4	37.4	45	0.8		
	С	34.00	38.00									
39	В	38.20	39.80	350	130	0.05	27.3	33.4	41.2	45	0.7	
	С	37.00	41.00									
43	В	42.10	43.90	375 150	375 150	150	0.05	30.1	37.6	46.6	40	0.6
	С	40.00	46.00									
47	В	46.10	47.90	375 170 0	0.05	0.05 32.9	42.0	51.8	40	0.5		
	С	44.00	50.00									
51	В	50.00	52.00	400	180	0.05	35.7	46.6	57.2	40	0.4	
	С	48.00	54.00									
56	В	54.90	57.10	425	200	0.05	39.2	52.2	63.8	40	0.3	
	С	52.00	60.00									
62	В	60.80	63.20	450	215	0.05	43.4	58.8	71.6	35	0.3	
	С	58.00	66.00									
68	В	66.60	69.40	475	240	0.05	47.6	65.6	79.8	35	0.25	
	С	64.00	72.00									
75	В	73.50	76.50	500	255	0.05	52.5	73.4	88.6	35	0.20	
	С	70.00	79.00]								

[1] $f = 1 \text{ MHz}; V_R = 0 \text{ V}$


[2] $t_p = 100 \ \mu s$; square wave; $T_j = 25 \ ^\circ C$ prior to surge

Dual voltage regulator diodes




© Nexperia B.V. 2024. All rights reserved

Dual voltage regulator diodes



Dual voltage regulator diodes




11. Test information


Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard *Q101* - *Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

12. Package outline



13. Soldering



14. Revision history

Table 10. Revision history	Table 10. Revision history								
Document ID	Release date	Data sheet status	Change notice	Supersedes					
BZB84-Q_SER v.2	20240410	Product data sheet	-	BZB84-Q_SER v.1					
Modifications:	Characteristics' Table 8: column width adjusted								
BZB84-Q_SER v.1	20240315	Product data sheet	-	-					

BZB84-Q_SER

15. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

Dual voltage regulator diodes

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description	1
2. Features and benefits	1
3. Applications	1
4. Quick reference data	1
5. Pinning information	2
6. Ordering information	2
7. Marking	3
8. Limiting values	4
9. Thermal characteristics	4
10. Characteristics	4
11. Test information	10
12. Package outline	
13. Soldering	11
14. Revision history	12
15. Legal information	13

© Nexperia B.V. 2024. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 10 April 2024