

#### Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of <a href="http://www.nxp.com">http://www.nxp.com</a>, <a href="http://www.semiconductors.philips.com/">http://www.nxp.com</a>, <a href="http://www.nexperia.com/">http://www.nexperia.com/</a>, <a href="http://www.nexperia.com/">http://www.nexperia.com/</a>, <a href="http://www.nexperia.com/">use http://www.nexperia.com/</a>

Instead of sales.addresses@www.nxp.com or sales.addresses@www.semiconductors.philips.com, use salesaddresses@nexperia.com (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © Nexperia B.V. (year). All rights reserved.


If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **salesaddresses@nexperia.com**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia

# DISCRETE SEMICONDUCTORS

# DATA SHEET



# **BZV90 series**Voltage regulator diodes

Product data sheet Supersedes data of 1996 Oct 25 1999 May 17



# Voltage regulator diodes

#### **BZV90** series

#### **FEATURES**

- Total power dissipation: max. 1500 mW
- Tolerance series: approx. ±5%
- Working voltage range: nom. 2.4 to 75 V (E24 range)
- Non-repetitive peak reverse power dissipation: max. 40 W.

#### **APPLICATIONS**

• General regulation functions.


#### **DESCRIPTION**

Medium-power voltage regulator diodes in SOT223 plastic SMD packages.

The diodes are available in the normalized E24 approx.  $\pm 5\%$  tolerance range. The series consists of 37 types with nominal working voltages from 2.4 to 75 V (BZV90-C2V4 to C75).

#### **PINNING**

PIN	DESCRIPTION			
1	anode			
2, 4	cathode			
3	anode			



#### LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
I <sub>F</sub>	continuous forward current		_	400	mA
I <sub>ZSM</sub>	non-repetitive peak reverse current	$t_p$ = 100 μs; square wave; $T_j$ = 25 °C prior to surge	see Table "Per type"		
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = 25 °C; note 1	_	1500	mW
P <sub>ZSM</sub>	non-repetitive peak reverse power dissipation	$t_p$ = 100 μs; square wave; $T_j$ = 25 °C prior to surge; see Fig.2	_	40	W
T <sub>stg</sub>	storage temperature		-65	+150	°C
Tj	junction temperature		_	150	°C

#### Note

1. Device mounted on an FR4 double-sided copper-clad printed circuit-board; copper area = 2 cm<sup>2</sup>.

#### **ELECTRICAL CHARACTERISTICS**

#### Total series

 $T_i = 25$  °C unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V <sub>F</sub>	forward voltage	I <sub>F</sub> = 50 mA; see Fig.3	I	1.0	V

Voltage regulator diodes

BZV90 series

BZV90- CXXX	VOLT V <sub>Z</sub>	KING FAGE (V) Ztest	RESIS r <sub>di</sub>	RENTIAL STANCE <sub>if</sub> (Ω) I <sub>Ztest</sub>	S	IP. COI z (mV/I at I <sub>Ztest</sub> Figs 4 a	<b>&lt;</b> )	TEST CURRENT I <sub>Ztest</sub> (mA)	DIODE CAP. $C_{d} (pF)$ at $f = 1$ MHz; at $V_{R} = 0$ V	REVERSE CURRENT at REVERSE VOLTAGE		$ \begin{array}{c cccc} C_d \ (pF) & CURRENT \ at \\ t \ f = 1 \ MHz; & REVERSE & I_{ZSM} \ (A) \\ at \ V_R = 0 \ V & VOLTAGE & at \ t_p = 100 \ \mu s; \end{array} $		at t <sub>p</sub> = 100 μs;
										<b>I</b> <sub>R</sub> (μ <b>A</b> )	$V_{R}$	T <sub>amb</sub> = 25 °C		
	MIN.	MAX.	TYP.	MAX.	MIN.	TYP.	MAX.		MAX.	MAX.	(V)	MAX.		
2V4	2.2	2.6	70	100	-3.5	-1.6	0	5	450	50	1.0	6.0		
2V7	2.5	2.9	75	100	-3.5	-2.0	0	5	450	20	1.0	6.0		
3V0	2.8	3.2	80	95	-3.5	-2.1	0	5	450	10	1.0	6.0		
3V3	3.1	3.5	85	95	-3.5	-2.4	0	5	450	5	1.0	6.0		
3V6	3.4	3.8	85	90	-3.5	-2.4	0	5	450	5	1.0	6.0		
3V9	3.7	4.1	85	90	-3.5	-2.5	0	5	450	3	1.0	6.0		
4V3	4.0	4.6	80	90	-3.5	-2.5	0	5	450	3	1.0	6.0		
4V7	4.4	5.0	50	80	-3.5	-1.4	0.2	5	300	3	2.0	6.0		
5V1	4.8	5.4	40	60	-2.7	-0.8	1.2	5	300	2	2.0	6.0		
5V6	5.2	6.0	15	40	-2.0	1.2	2.5	5	300	1	2.0	6.0		
6V2	5.8	6.6	6	10	0.4	2.3	3.7	5	200	3	4.0	6.0		
6V8	6.4	7.2	6	15	1.2	3.0	4.5	5	200	2	4.0	6.0		
7V5	7.0	7.9	6	15	2.5	4.0	5.3	5	150	1	5.0	4.0		
8V2	7.7	8.7	6	15	3.2	4.6	6.2	5	150	0.7	5.0	4.0		
9V1	8.5	9.6	6	15	3.8	5.5	7.0	5	150	0.5	6.0	3.0		
10	9.4	10.6	8	20	4.5	6.4	8.0	5	90	0.2	7.0	3.0		
11	10.4	11.6	10	20	5.4	7.4	9.0	5	85	0.1	8.0	2.5		
12	11.4	12.7	10	25	6.0	8.4	10.0	5	85	0.1	8.0	2.5		
13	12.4	14.1	10	30	7.0	9.4	11.0	5	80	0.1	8.0	2.5		
15	13.8	15.6	10	30	9.2	11.4	13.0	5	75	0.05	10.5	2.0		
16	15.3	17.1	10	40	10.4	12.4	14.0	5	75	0.05	11.2	1.5		
18	16.8	19.1	10	45	12.4	14.4	16.0	5	70	0.05	12.6	1.5		
20	18.8	21.2	15	55	14.4	16.4	18.0	5	60	0.05	14.0	1.5		

**WORKING** 

**DIFFERENTIAL** 

Voltage regulator diodes

Product data sheet

TEST

DIODE CAP.

**REVERSE** 

NON-REPETITIVE PEAK

TEMP. COEFF.

# Voltage regulator diodes

BZV90 series

#### THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
R <sub>th j-a</sub>	thermal resistance from junction to ambient	lead length max.; note 1	83.3	K/W

5

#### Note

1. Device mounted on an FR4 double-sided copper-clad printed circuit-board; copper area = 2 cm<sup>2</sup>.

#### **GRAPHICAL DATA**




Fig.2 Maximum permissible non-repetitive peak reverse power dissipation versus duration.





Fig.3 Forward current as a function of forward voltage; typical values.

1999 May 17

# Voltage regulator diodes

## BZV90 series



MBG924 10 S<sub>Z</sub> (mV/K) 10 9V1 5 8V2 7V5 6V8 6V2 5V6 5V1 8 12 16 <sub>IZ</sub> (mA) 20 **BZV90-C4V7 to C10.**  $T_j = 25$  to 150 °C. Fig.5 Temperature coefficient as a function of working current; typical values.


# Voltage regulator diodes

## BZV90 series

#### **PACKAGE OUTLINE**

Plastic surface mounted package; collector pad for good heat transfer; 4 leads

**SOT223** 



EUROPEAN	ISSUE DATE	
PROJECTION	1930E DATE	
	<del>97-02-28</del> 99-09-13	
_		

1999 May 17 7

#### Voltage regulator diodes

#### **BZV90** series

#### **DATA SHEET STATUS**

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

#### **Notes**

- 1. Please consult the most recently issued document before initiating or completing a design.
- 2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

#### **DISCLAIMERS**

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this

document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

# **NXP Semiconductors**

#### **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors, including new legal definitions and disclaimers. No changes were made to the technical content, except for package outline drawings which were updated to the latest version.

#### **Contact information**

For additional information please visit: http://www.nxp.com
For sales offices addresses send e-mail to: salesaddresses@nxp.com

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands 115002/00/03/pp9 Date of release: 1999 May 17 Document order number: 9397 750 05928

