

GAN039-650NTB

650 V, 33 mOhm Gallium Nitride (GaN) FET in a CCPAK1212i package

5 December 2023

Product data sheet

1. General description

The GAN039-650NTB is a 650 V, 33 m Ω Gallium Nitride (GaN) FET in a CCPAK1212i inverted package. It is a normally-off device that combines Nexperia's latest high-voltage GaN HEMT H2 technology and low-voltage silicon MOSFET technologies — offering superior reliability and performance.

2. Features and benefits

- · Simplified driver design as standard level MOSFET gate drivers can be used:
 - 0 V to 12 V drive voltage
 - Gate threshold voltage V_{GSth} of 4 V
- Robust gate oxide with ±20 V V_{GS} rating
- High gate threshold voltage of 4 V for gate bounce immunity
- Low body diode V_f for reduced losses and simplified dead-time adjustments
- Transient over-voltage capability for increased robustness
- CCPAK package technology:
 - Improved reliability, with reduced $R_{\text{th(j-mb)}}$ for optimal cooling
 - · Lower inductances for lower switching losses and EMI
 - 150 °C maximum junction temperature
 - High Board Level Reliability absorbing mechanical stress during thermal cycling, unlike traditional QFN packages
 - · Visual (AOI) soldering inspection, no need for expensive x-ray equipment
 - Easy solder wetting for good mechanical solder joints

3. Applications

- Hard and soft switching converters for industrial and datacom power
- Bridgeless totempole PFC
- PV and UPS inverters
- Servo motor drives

4. Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V _{DS}	drain-source voltage	-55 °C ≤ T _j ≤ 150 °C		-	-	650	V
I _D	drain current	V _{GS} = 10 V; T _{mb} = 25 °C; <u>Fig. 2</u>	[1]	-	-	58.5	Α
P _{tot}	total power dissipation	T _{mb} = 25 °C; <u>Fig. 1</u>		-	-	250	W
Tj	junction temperature			-55	-	150	°C
Static characteristics							
R _{DSon}	drain-source on-state resistance	V_{GS} = 10 V; I_D = 32 A; T_j = 25 °C; Fig. 10		-	33	39	mΩ



Symbol	Parameter	Conditions		Min	Тур	Max	Unit
		V_{GS} = 10 V; I_D = 32 A; T_j = 150 °C; Fig. 11		-	73	86	mΩ
Dynamic chara	cteristics						
Q_{GD}	gate-drain charge	$I_D = 32 \text{ A}; V_{DS} = 400 \text{ V}; V_{GS} = 10 \text{ V};$		-	5	-	nC
Q _{G(tot)}	total gate charge	T _j = 25 °C; <u>Fig. 12</u> ; <u>Fig. 13</u>		-	26	-	nC
Source-drain d	Source-drain diode						
Q _r	recovered charge	$I_S = 32 \text{ A}; dI_S/dt = -1000 \text{ A/}\mu\text{s};$ $V_{GS} = 0 \text{ V}; V_{DS} = 400 \text{ V}; Fig. 19$	[2]	-	187	-	nC

^[1] The ID value is calculated based on the maximum thermal resistance from junction to mounting base and the RDSon

5. Pinning information

Table 2. Pinning information

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	G	gate		
2	S	source		
3	S	source		
4	S	source	6 5 4 3 2 1	D I
5	S	source		
6	S	source		
7	D	drain		
8	D	drain		
9	D	drain	<u>مُثمثمثم</u>	
10	D	drain	7 8 9 10 11 12 CCPAK1212i (SOT8005)	s
11	D	drain	COPAR 12 121 (SO 10003)	aaa-028116
12	D	drain		
mb	S	mounting base; connected to source		

6. Ordering information

Table 3. Ordering information

able 6. Ordering information						
Type number	Package					
	Name	Description	Version			
GAN039-650NTB	CCPAK1212i	Plastic, surface mounted copper clip package inverted (CCPAK1212i); 13 terminals; 2.0 mm pitch, 12 mm x 9.4 mm x 2.5 mm body	SOT8005			

7. Marking

Table 4. Marking codes

Type number	Marking code
GAN039-650NTB	039INTB

^[2] Qr = Qoss +Qd where Qd is charge associated with minority carriers in the body diode of the Si mosfet of the cascode.

8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{DS}	drain-source voltage	-55 °C ≤ T _j ≤ 150 °C		-	650	V
V _{TDS}	transient drain to source voltage	pulsed; $t_p = 1 \mu s$; $\delta_{factor} = 0.01$		-	725	V
V_{GS}	gate-source voltage			-20	20	V
P _{tot}	total power dissipation	T _{mb} = 25 °C; <u>Fig. 1</u>		-	250	W
I _D	drain current	V _{GS} = 10 V; T _{mb} = 25 °C; <u>Fig. 2</u>	[1]	-	58.5	А
		V _{GS} = 10 V; T _{mb} = 100 °C; <u>Fig. 2</u>		-	37	А
I _{DM}	peak drain current	pulsed; $t_p \le 10 \mu s$; $T_{mb} = 25 °C$; Fig. 3		-	234	А
T _{stg}	storage temperature			-55	150	°C
T _j	junction temperature			-55	150	°C
T _{sld(M)}	peak soldering temperature			-	260	°C
Source-drain	n diode			'		
Is	source current	T _{mb} = 25 °C; V _{GS} = 0 V		-	58.5	Α
I _{SM}	peak source current	pulsed; $t_p \le 10 \mu s$; $T_{mb} = 25 \text{ °C}$		-	234	А

[1] The ID value is calculated based on the maximum thermal resistance from junction to mounting base and the RDSon






Fig. 1. Normalized total power dissipation as a function of mounting base temperature



 $V_{GS} \ge 10 \text{ V}$ (1) 53.5A DC continuous current has been successfully demonstrated during application tests. Practically the current will be limited by PCB, thermal design and operating temperature.


Fig. 2. Continuous drain current as a function of mounting base temperature



9. Thermal characteristics

Table 6. Thermal characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
R _{th(j-mb)}	thermal resistance from junction to mounting base	Fig. 4	-	-	0.5	K/W



10. Characteristics

Table 7. Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Static char	acteristics					
V _{GS(th)}	gate-source threshold	I _D = 1 mA; V _{DS} =V _{GS} ; T _j = 25 °C	3.4	3.9	4.6	V
	voltage	$I_D = 1 \text{ mA}; V_{DS} = V_{GS}; T_j = 150 \text{ °C}; Fig. 9$	2.4	-	-	V
		$I_D = 1 \text{ mA}; V_{DS} = V_{GS}; T_j = -55 \text{ °C}; Fig. 9$	-	-	5.2	V
I _{DSS}	drain leakage current	V _{DS} = 650 V; V _{GS} = 0 V; T _j = 25 °C	-	2.5	20	μA
		V _{DS} = 650 V; V _{GS} = 0 V; T _j = 150 °C	-	6	-	μA
I _{GSS}	gate leakage current	V _{GS} = -20 V; V _{DS} = 0 V; T _j = 25 °C	-	10	400	nA
		V _{GS} = 20 V; V _{DS} = 0 V; T _j = 25 °C	-	10	400	nA
R _{DSon}	drain-source on-state resistance	$V_{GS} = 10 \text{ V}; I_D = 32 \text{ A}; T_j = 25 \text{ °C};$ Fig. 10	-	33	39	mΩ
		V_{GS} = 10 V; I_D = 32 A; T_j = 150 °C; Fig. 11	-	73	86	mΩ
R_{G}	gate resistance	f = 1 MHz	0.2	0.5	1.3	Ω
Dynamic c	haracteristics					
Q _{G(tot)}	total gate charge	I _D = 32 A; V _{DS} = 400 V; V _{GS} = 10 V;	-	26	-	nC
Q _{GS}	gate-source charge	T _j = 25 °C; <u>Fig. 12</u> ; <u>Fig. 13</u>	-	10.2	-	nC
Q _{GD}	gate-drain charge		-	5	-	nC
C _{iss}	input capacitance	$V_{DS} = 400 \text{ V}; V_{GS} = 0 \text{ V}; f = 1 \text{ MHz};$ $T_j = 25 \text{ °C}; Fig. 14$	-	1980	-	pF
C _{oss}	output capacitance		-	144	-	pF
C _{rss}	reverse transfer capacitance		-	1.6	-	pF
C _{o(er)}	effective output capacitance, energy related	$0 \text{ V} \le \text{ V}_{DS} \le 400 \text{ V}; \text{ V}_{GS} = 0 \text{ V};$ f = 1 MHz; T _j = 25 °C; Fig. 15	-	218	-	pF
C _{o(tr)}	effective output capacitance, time related	$0 \text{ V} \le \text{ V}_{DS} \le 400 \text{ V}; \text{ V}_{GS} = 0 \text{ V};$ f = 1 MHz; T _j = 25 °C	-	432	-	pF
t _{d(on)}	turn-on delay time	V_{DS} = 400 V; R_L = 12.5 Ω ; V_{GS} = 12 V;	-	17	-	ns
t _r	rise time	$R_{G(ext)} = 30 \Omega; Fig. 16; Fig. 17$	-	10	-	ns
t _{d(off)}	turn-off delay time		-	28	-	ns
t _f	fall time	1	-	9	-	ns
Q _{oss}	output charge	V _{GS} = 0 V; V _{DS} = 400 V	-	173	-	nC
Source-dra	ain diode		,			,
V _{SD}	source-drain voltage	$I_S = 32 \text{ A}; V_{GS} = 0 \text{ V}; T_j = 25 \text{ °C}; Fig. 18$	-	1.6	-	V
		I _S = 16 A; V _{GS} = 0 V; T _j = 25 °C; <u>Fig. 18</u>	-	1.2	-	V
t _{rr}	reverse recovery time	I _S = 32 A; dI _S /dt = -1000 A/μs;	-	25	-	ns
Q _r	recovered charge	V _{GS} = 0 V; V _{DS} = 400 V; <u>Fig. 19</u>	[1] -	187	-	nC

^[1] Qr = Qoss +Qd where Qd is charge associated with minority carriers in the body diode of the Si mosfet of the cascode.




Fig. 5. Output characteristics; drain current as a function of drain-source voltage; typical values




Fig. 7. Transfer characteristics; drain current as a function of gate-source voltage; typical values




Fig. 6. Output characteristics; drain current as a function of drain-source voltage; typical values




Fig. 8. Drain-source on-state resistance as a function of gate-source voltage; typical values




Fig. 9. Gate-source threshold voltage as a function of junction temperature




Fig. 10. Drain-source on-state resistance as a function of drain current; typical values




Fig. 11. Normalized drain-source on-state resistance factor as a function of junction temperature




Fig. 12. Gate-source voltage as a function of gate charge; typical values




Fig. 13. Gate charge waveform definitions




Fig. 14. Input, output and reverse transfer capacitances as a function of drain-source voltage; typical values




Fig. 15. Typical COSS Stored Energy




Fig. 16. Switching time test circuit




Fig. 17. Switching time waveform






Fig. 18. Source-drain (diode forward) current as a function of source-drain (diode forward) voltage; typical values




11. Application information

A Ferrite bead must be fitted in series with the gate of the GaN FET and should be located as close as possible to the gate pin, (see figure below). Keeping the gate-source loop as compact as possible minimizes the gate loop inductance. The Ferrite bead damps the resonant circuit made up of the gate source loop inductance and the GaN FET input capacitance, thus providing fast switching stability. It is recommended that the impedance of the ferrite bead should be 30 Ω @ 100 MHz, (recommended p/n BLM18PG300SN1D). A series resistance (R $_{\rm G}$) of 10 - 15 Ω is also recommended.




A DC-link resonance damper is recommended in all cases. Optimal is 20 nF in series with 4 Ω , most easily achieved with parallel combination 10 nF and 8 Ω . This resonance damper lowers the Q factor of any resonance in the bus. That resonance will act as a load on the high gain amplifier that is the GaN FET and can lead to instability.

12. Package outline



13. Soldering



14. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at https://www.nexperia.com.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by sustained.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1.	General description	1
2.	Features and benefits	1
3.	Applications	1
4.	Quick reference data	1
5.	Pinning information	2
6.	Ordering information	2
7.	Marking	2
8.	Limiting values	3
9.	Thermal characteristics	4
10.	Characteristics	5
11.	Application information	9
12.	Package outline	11
13.	Soldering	12
14.	Legal information	.13

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 5 December 2023

[©] Nexperia B.V. 2023. All rights reserved