Quad 2-input NAND Schmitt trigger Rev. 2 — 25 February 2022

1. General description

The HEF4093B-Q100 is a quad 2-input NAND gate with Schmitt-trigger inputs. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of V_{DD} . Schmitt trigger inputs transform slowly changing input signals into sharply defined jitter-free output signals.

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

2. Features and benefits

- Automotive product qualification in accordance with AEC-Q100 (Grade 1)
 Specified from -40 °C to +85 °C and from -40 °C to +125 °C
- Schmitt trigger input discrimination
- Fully static operation
- 5 V, 10 V, and 15 V parametric ratings
- Wide supply voltage range from 3.0 V to 15.0 V
- CMOS low power dissipation
- High noise immunity
- Standardized symmetrical output characteristics
- ESD protection:
 - MIL-STD-833, method 3015 exceeds 2000 V
 - HBM JESD22-A114F exceeds 2000 V
 - MM JESD22-A115-A exceeds 200 V (C = 200 pf, R = 0 Ω)
- Complies with JEDEC standard JESD 13-B

3. Applications

- Wave and pulse shapers
- Astable multivibrators
- Monostable multivibrators

4. Ordering information


Table 1. Ordering information

Type number	Package				
	Temperature range	Name	Description	Version	
HEF4093BT-Q100	-40 °C to +125 °C		plastic small outline package; 14 leads; body width 3.9 mm	SOT108-1	

ne<mark>x</mark>peria


Quad 2-input NAND Schmitt trigger

5. Functional diagram



6. Pinning information

6.1. Pinning



6.2. Pin description

Table 2. Pin description				
Symbol	Pin	Description		
1A, 2A, 3A, 4A	1, 5, 8, 12	input		
1B, 2B, 3B, 4B	2, 6, 9, 13	input		
1Y, 2Y, 3Y, 4Y	3, 4, 10, 11	output		
V _{DD}	14	supply voltage		
V _{SS}	7	ground (0 V)		

7. Functional description

Table 3. Function table

H = HIGH voltage level; L = LOW voltage level.

Input	Output	
nA	nB	nY
L	L	Н
L	Н	Н
н	L	Н
Н	Н	L

8. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to V_{SS} = 0 V (ground).

Symbol	Parameter	Conditions	Min	Max	Unit
V _{DD}	supply voltage		-0.5	+18	V
I _{IK}	input clamping current	V_{l} < -0.5 V or V_{l} > V_{DD} + 0.5 V	-	±10	mA
VI	input voltage		-0.5	V _{DD} + 0.5	V
I _{OK}	output clamping current	V_{O} < -0.5 V or V_{O} > V_{DD} + 0.5 V	-	±10	mA
I _{I/O}	input/output current		-	±10	mA
I _{DD}	supply current		-	50	mA
T _{stg}	storage temperature		-65	+150	°C
T _{amb}	ambient temperature		-40	+125	°C
P _{tot}	total power dissipation	T _{amb} = -40 °C to +125 °C [1]	-	500	mW
Р	power dissipation	per output	-	100	mW

[1] For SOT108-1 (SO14) package: Ptot derates linearly with 10.1 mW/K above 100 °C.

9. Recommended operating conditions

Table 5. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Max	Unit
V _{DD}	supply voltage		3	15	V
VI	input voltage		0	V _{DD}	V
T _{amb}	ambient temperature	in free air	-40	+125	°C

10. Static characteristics

Table 6. Static characteristics

 $V_{SS} = 0 V$; $V_{I} = V_{SS}$ or V_{DD} ; unless otherwise specified.

Symbol	Parameter	Conditions	V _{DD}	T _{amb} =	-40 °C	T _{amb} =	+25 °C	T _{amb} =	+85 °C	T _{amb} = -	+125 °C	Unit
				Min	Мах	Min	Мах	Min	Мах	Min	Max	
V _{OH}	HIGH-level output	I _O < 1 μΑ	5 V	4.95	-	4.95	-	4.95	-	4.95	-	V
	voltage		10 V	9.95	-	9.95	-	9.95	-	9.95	-	V
			15 V	14.95	-	14.95	-	14.95	-	14.95	-	V

Symbol Parameter Conditions T_{amb} = -40 °C V_{DD} T_{amb} = +25 °C | T_{amb} = +85 °C T_{amb} = +125 °C Unit Min Max Min Min Max Min Max Max V VOL LOW-level output $|I_0| < 1 \mu A$ 5 V 0.05 0.05 0.05 0.05 -_ -voltage V 10 V 0.05 0.05 0.05 0.05 --_ -V 15 V 0.05 0.05 0.05 0.05 -_ _ -HIGH-level output Vo = 2.5 V -1.7 -1.4 5 V -1.1 -1.1 mΑ I_{OH} -_ -current V_O = 4.6 V 5 V --0.64 _ -0.5 --0.36 _ -0.36 mΑ V_O = 9.5 V 10 V -1.6 -1.3 -0.9 -0.9 mΑ -_ --V_O = 13.5 V -4.2 -3.4 -2.4 15 V -2.4 mΑ ----LOW-level output V_O = 0.4 V I_{OL} 5 V 0.64 _ 0.5 -0.36 0.36 mΑ _ current V_O = 0.5 V 10 V 1.6 _ 1.3 _ 0.9 0.9 _ mΑ _ V_O = 1.5 V 15 V 4.2 _ 3.4 _ 2.4 -2.4 mA I_L input leakage 15 V ±0.1 ±0.1 ±1.0 ±1.0 μA -_ _ current all valid input 5 V 0.25 0.25 7.5 7.5 supply current μΑ I_{DD} --_ _ combinations; 10 V 0.5 0.5 15.0 15.0 μA --_ -I_O = 0 A 15 V 1.0 1.0 30.0 30.0 μA --_ pF C input capacitance 7.5 _ _ ---_ -

Quad 2-input NAND Schmitt trigger

11. Dynamic characteristics

Table 7. Dynamic characteristics

 T_{amb} = 25 °C; C_L = 50 pF; t_r = $t_f \le$ 20 ns; unless otherwise specified. For waveforms see Fig. 4; for test circuit see Fig. 5.

Symbol	Parameter	Conditions	V _{DD}	Extrapolation formula [1]	Min	Тур	Max	Unit
t _{PHL}	HIGH to LOW	nA or nB to nY	5 V	63 ns + (0.55 ns/pF)C _L	-	90	185	ns
	propagation delay		10 V	29 ns + (0.23 ns/pF)C _L	-	40	80	ns
			15 V	22 ns + (0.16 ns/pF)C _L	-	30	60	ns
t _{PLH}	LOW to HIGH	nA or nB to nY	5 V	58 ns + (0.55 ns/pF)C _L	-	85	170	ns
	propagation delay	opagation delay	10 V	29 ns + (0.23 ns/pF)C _L	-	40	80	ns
			15 V	22 ns + (0.16 ns/pF)C _L	-	30	60	ns
t _{THL}	HIGH to LOW output	nY to LOW	5 V	10 ns + (1.00 ns/pF)C _L	-	60	120	ns
	transition time		10 V	9 ns + (0.42 ns/pF)C _L	-	30	60	ns
			15 V	6 ns + (0.28 ns/pF)C _L	-	20	40	ns
t _{TLH}	LOW to HIGH output	nA or nB to	5 V	10 ns + (1.00 ns/pF)C _L	-	60	120	ns
	transition time	HIGH	10 V	9 ns + (0.42 ns/pF)C _L	-	30	60	ns
			15 V	6 ns + (0.28 ns/pF)C _L	-	20	40	ns


[1] Typical value of the propagation delay and output transition time can be calculated with the extrapolation formula (C_L in pF).

Table 8. Dynamic power dissipation

 $V_{SS} = 0 V; t_r = t_f \le 20 ns; T_{amb} = 25 \ ^{\circ}C.$

Symbol	Parameter	V _{DD}	Typical formula	where:
P _D	dynamic power	5 V		f _i = input frequency in MHz;
	dissipation	10 V	$P_{D} = 6400 \times f_{i} + \Sigma (f_{o} \times C_{L}) \times V_{DD}^{2} (\mu W)$	$f_o =$ output frequency in MHz; C _L = output load capacitance in pF;
		15 V	$P_{D} = 18700 \times f_{i} + \Sigma (f_{o} \times C_{L}) \times V_{DD}^{2} (\mu W)$	$\Sigma(f_o \times C_L)$ = sum of the outputs; V_{DD} = supply voltage in V.

11.1. Waveforms and test circuit




Logic levels: V_{OL} and V_{OH} are typical output voltage levels that occur with the output load. t_r , t_f = input rise and fall times.

Fig. 4. Propagation delay and output transition time

Table 9. Measurement points

Supply voltage	Input	Output
V _{DD}	V _M	V _M
5 V to 15 V	$0.5 \times V_{DD}$	$0.5 \times V_{DD}$



 R_T = termination resistance should be equal to the output impedance Z_o of the pulse generator.

Fig. 5. Test circuit for measuring switching times

Table 10. Test data


Supply voltage	Input L		Load
V _{DD}	VI	t _r , t _f	CL
5 V to 15 V	V_{SS} or V_{DD}	≤ 20 ns	50 pF

12. Transfer characteristics


Table 11. Transfer characteristics


 $V_{SS} = 0 V$; $T_{amb} = 25 \text{ °C}$; see Fig. 6 and Fig. 7.

Symbol	Parameter	Conditions	V _{DD}	Min	Тур	Max	Unit
V _{T+}	positive-going threshold voltage		5 V	1.9	2.9	3.5	V
			10 V	3.6	5.2	7	V
			15 V	4.7	7.3	11	V
V _{T-}	V _{T-} negative-going threshold voltage		5 V	1.5	2.2	3.1	V
			10 V	3	4.2	6.4	V
			15 V	4	6.0	10.3	V
V _H	hysteresis voltage		5 V	0.4	0.7	-	V
			10 V	0.6	1.0	-	V
			15 V	0.7	1.3	-	V



Quad 2-input NAND Schmitt trigger





HEF4093B_Q100


All information provided in this document is subject to legal disclaimers.

© Nexperia B.V. 2022. All rights reserved

13. Application information

Some examples of applications for the HEF4093B-Q100 are:

- Wave and pulse shapers
- Astable multivibrators
- Monostable multivibrators



If a Schmitt trigger is driven via a high-impedance (R > 1 k Ω), then it is necessary to incorporate a capacitor C with a value of $\frac{C}{C_P} > \frac{V_{\text{DD}} - V_{\text{SS}}}{V_H}$; otherwise oscillation can occur on the edges of a pulse.

 C_p is the external parasitic capacitance between inputs and output; the value depends on the circuit board layout.

Remark: The two inputs may be connected together, but this will result in a larger through-current at the moment of switching.

14. Package outline




Fig. 12. Package outline SOT108-1 (SO14)

15. Abbreviations

DUT Device Under Test ESD ElectroStatic Discharge HBM Human Body Model MIL Military	Acronym	Description
ESD ElectroStatic Discharge HBM Human Body Model MIL Military	CDM	Charged Device Model
HBM Human Body Model MIL Military	DUT	Device Under Test
MIL Military	ESD	ElectroStatic Discharge
	НВМ	Human Body Model
MM Machine Model	MIL	Military
	MM	Machine Model

16. Revision history

Table 13. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
HEF4093B_Q100 v.2	20220225	Product specification	-	HEF4093B_Q100 v.1
Modifications	Nexperia. • Legal texts hav • <u>Table 4</u> : Derati • <u>Section 1, Sec</u>	this data sheet has been redes we been adapted to the new co ing values for P _{tot} total power o <u>tion 2</u> , and <u>Section 15</u> updated inimum values changed to max	ompany name where lissipation updated. d.	
HEF4093B_Q100 v.1	20120712	Product specification	-	-

17. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

Quad 2-input NAND Schmitt trigger

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description	1
2. Features and benefits	1
3. Applications	1
4. Ordering information	1
5. Functional diagram	2
6. Pinning information	2
6.1. Pinning	2
6.2. Pin description	2
7. Functional description	3
8. Limiting values	3
9. Recommended operating conditions	3
10. Static characteristics	3
11. Dynamic characteristics	4
11.1. Waveforms and test circuit	5
12. Transfer characteristics	6
13. Application information	8
14. Package outline	
15. Abbreviations	10
16. Revision history	
17. Legal information	

© Nexperia B.V. 2022. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 25 February 2022