8-stage shift-and-store register LED driver Rev. 2 — 7 November 2018

**Product data sheet** 

nexperia

## 1. General description

The HEF4794B-Q100 is an 8-stage serial shift register. It has a storage latch associated with each stage for strobing data from the serial input (D) to the parallel LED driver outputs (QP0 to QP7). Data is shifted on the positive-going clock (CP) transitions. The data in each shift register stage is transferred to the storage register when the strobe input (STR) is HIGH. Data in the storage register appears at the outputs whenever the output enable input (OE) signal is HIGH.

Two serial outputs (QS1 and QS2) are available for cascading a number of HEF4794B-Q100 devices. Serial data is available at QS1 on positive-going clock edges to allow high-speed operation in cascaded systems with a fast clock rise time. The same serial data is available at QS2 on the next negative going clock edge. This is used for cascading HEF4794B-Q100 devices when the clock has a slow rise time.

It operates over a recommended  $V_{DD}$  power supply range of 3 V to 15 V referenced to  $V_{SS}$  (usually ground). Unused inputs must be connected to  $V_{DD}$ ,  $V_{SS}$ , or another input.

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

## 2. Features and benefits

- Automotive product qualification in accordance with AEC-Q100 (Grade 1)
  - Specified from -40 °C to +85 °C and from -40 °C to +125 °C
- Fully static operation
- 5 V, 10 V, and 15 V parametric ratings
- Standardized symmetrical output characteristics
- ESD protection:
  - MIL-STD-883, method 3015 exceeds 2000 V
  - HBM JESD22-A114F exceeds 2000 V
  - MM JESD22-A115-A exceeds 200 V (C = 200 pF; R = 0 Ω)
- Complies with JEDEC standard JESD 13-B


## 3. Ordering information

### Table 1. Ordering information

All types operate from -40 °C to +125 °C.


Type number	Package	Package					
	Name	Description	Version				
HEF4794BT-Q100	SO16	plastic small outline package; 16 leads; body width 3.9 mm	SOT109-1				

# 4. Functional diagram



# 5. Pinning information

## 5.1. Pinning



## 5.2. Pin description

### Table 2. Pin description

Symbol	Pin	Description
D	2	serial input
QP0 to QP7	4, 5, 6, 7, 14, 13, 12, 11	parallel output (open-drain)
QS1	9	serial output
QS2	10	serial output
СР	3	clock input
STR	1	strobe input
OE	15	output enable input
V <sub>DD</sub>	16	supply voltage
V <sub>SS</sub>	8 ground (0 V)	

## 6. Functional description


### Table 3. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state;  $\uparrow = LOW-to-HIGH$  clock transition;  $\downarrow = HIGH-to-LOW$  clock transition.

Input				Parallel outp	out	Serial outpu	Serial output	
СР	OE	STR	D	QP0	QPn	QS1[1]	QS2[2]	
1	L	Х	Х	Z	Z	Q6S	no change	
$\downarrow$	L	Х	Х	Z	Z	n.c.	Q7S	
1	Н	L	Х	no change	no change	Q6S	no change	
1	Н	Н	L	Z	QPn - 1	Q6S	no change	
↑	Н	Н	Н	L	QPn - 1	Q6S	no change	
Ļ	Н	Н	Н	no change	no change	no change	Q7S	

[1] Q6S = the data in register stage 6 before the LOW to HIGH clock transition.

[2] Q7S = the data in register stage 7 before the HIGH to LOW clock transition.



# 7. Limiting values

### Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>DD</sub>	supply voltage		-0.5	+18	V
l <sub>IK</sub>	input clamping current	$V_{I}$ < -0.5 V or $V_{I}$ > $V_{DD}$ + 0.5 V	-	±10	mA
VI	input voltage		-0.5	V <sub>DD</sub> + 0.5	V
I <sub>OK</sub> output clamping current		QSn outputs; V <sub>O</sub> < -0.5 V or V <sub>O</sub> > V <sub>DD</sub> + 0.5 V	-	±10	mA
		QPn outputs; V <sub>O</sub> < -0.5 V	-	40	mA
l <sub>l</sub>	input leakage current		-	±10	mA
I <sub>O</sub>	output current	QSn outputs	-	±10	mA
		QPn outputs	-	40	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
T <sub>amb</sub>	ambient temperature		-40	+125	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C			
		SO16 package [*	- 1	500	mW
Р	power dissipation	per output	-	100	mW

[1] For SO16 package:  $P_{tot}$  derates linearly with 8 mW/K above 70  $^\circ\text{C}.$ 

# 8. Recommended operating conditions

### Table 5. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>DD</sub>	supply voltage		3	15	V
VI	input voltage		0	V <sub>DD</sub>	V
T <sub>amb</sub>	ambient temperature	in free air	-40	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>DD</sub> = 5 V	-	3.75	µs/V
		V <sub>DD</sub> = 10 V	-	0.5	µs/V
		V <sub>DD</sub> = 15 V	-	0.08	µs/V

# 9. Static characteristics

### Table 6. Static characteristics

 $V_{SS} = 0 V$ ;  $V_{I} = V_{SS}$  or  $V_{DD}$ ; unless otherwise specified.

Symbol	Parameter	Conditions	V <sub>DD</sub>	T <sub>amb</sub> =	-40 °C	T <sub>amb</sub> =	25 °C	T <sub>amb</sub> =	85 °C	T <sub>amb</sub> =	125 °C	Unit
				Min	Мах	Min	Max	Min	Max	Min	Max	
VIH	HIGH-level	I <sub>O</sub>   < 1 μΑ	5 V	3.5	-	3.5	-	3.5	-	3.5	-	V
	input voltage		10 V	7.0	-	7.0	-	7.0	-	7.0	-	V
			15 V	11.0	-	11.0	-	11.0	-	11.0	-	V
V <sub>IL</sub>	LOW-level input	I <sub>O</sub>   < 1 μΑ	5 V	-	1.5	-	1.5	-	1.5	-	1.5	V
	voltage		10 V	-	3.0	-	3.0	-	3.0	-	3.0	V
			15 V	-	4.0	-	4.0	-	4.0	-	4.0	V
V <sub>OH</sub>	HIGH-level	QSn outputs;	5 V	4.95	-	4.95	-	4.95	-	4.95	-	V
	output voltage	I <sub>O</sub>   < 1 μΑ	10 V	9.95	-	9.95	-	9.95	-	9.95	-	V
			15 V	14.95	-	14.95	-	14.95	-	14.95	-	V
V <sub>OL</sub>	LOW-level		5 V	-	0.05	-	0.05	-	0.05	-	0.05	V
	output voltage	I <sub>O</sub>   < 1 μΑ	10 V	-	0.05	-	0.05	-	0.05	-	0.05	V
			15 V	-	0.05	-	0.05	-	0.05	-	0.05	V
		QPn outputs;  I <sub>O</sub>   < 20 mA	5 V	-	0.75	-	0.75	-	1.5	-	1.5	V
			10 V	-	0.75	-	0.75	-	1.5	-	1.5	V
		15 V	-	0.75	-	0.75	-	1.5	-	1.5	V	
I <sub>OH</sub>	HIGH-level	QSn outputs										
	output current	V <sub>O</sub> = 2.5 V	5 V	-	-1.7	-	-1.4	-	-1.1	-	-1.1	mA
		V <sub>O</sub> = 4.6 V	5 V	-	-0.64	-	-0.5	-	-0.36	-	-0.36	mA
		V <sub>O</sub> = 9.5 V	10 V	-	-1.6	-	-1.3	-	-0.9	-	-0.9	mA
		V <sub>O</sub> = 13.5 V	15 V	-	-4.2	-	-3.4	-	-2.4	-	-2.4	mA
I <sub>OL</sub>	LOW-level	QSn outputs										
	output current	V <sub>O</sub> = 0.4 V	5 V	0.64	-	0.5	-	0.36	-	0.36	-	mA
		V <sub>O</sub> = 0.5 V	10 V	1.6	-	1.3	-	0.9	-	0.9	-	mA
		V <sub>O</sub> = 1.5 V	15 V	4.2	-	3.4	-	2.4	-	2.4	-	mA
l <sub>l</sub>	input leakage current		15 V	-	±0.1	-	±0.1	-	±1.0	-	±1.0	μA
I <sub>OZ</sub>	OFF-state	QPn output	5 V	-	2	-	2	-	15	-	15	μA
	output current	is HIGH; V <sub>O</sub> = 15 V	10 V	-	2	-	2	-	15	-	15	μA
		v0 - 10 v	15 V	-	2	-	2	-	15	-	15	μA
I <sub>DD</sub>	supply current	I <sub>O</sub> = 0 A	5 V	-	5	-	5	-	150	-	150	μA
			10 V	-	10	-	10	-	300	-	300	μA
			15 V	-	20	-	20	-	600	-	600	μA
CI	input capacitance		-	-	-	-	-	7.5	-	-	-	pF

# **10.** Dynamic characteristics

### Table 7. Dynamic characteristics

 $V_{SS} = 0 V$ ;  $T_{amb} = 25 \degree C$  unless otherwise specified. For test circuit, see Fig. 10.

Symbol	Parameter	Conditions	V <sub>DD</sub>	Extrapolation formula	Min	Тур	Мах	Unit
t <sub>PHL</sub>	HIGH to LOW	CP to QS1;	5 V [1]	132 ns + (0.55 ns/pF)C <sub>L</sub>	-	160	320	ns
	propagation delay	see <u>Fig. 6</u>	10 V	53 ns + (0.23 ns/pF)C <sub>L</sub>	-	65	130	ns
			15 V	37 ns + (0.16 ns/pF)C <sub>L</sub>	-	45	90	ns
		CP to QS2;	5 V	92 ns + (0.55 ns/pF)C <sub>L</sub>	-	120	240	ns
		see <u>Fig. 6</u>	10 V	39 ns + (0.23 ns/pF)C <sub>L</sub>	-	50	100	ns
			15 V	32 ns + (0.16 ns/pF)C <sub>L</sub>	-	40	80	ns
t <sub>PLH</sub>	LOW to HIGH	CP to QS1;	5 V [1]	102 ns + (0.55 ns/pF)C <sub>L</sub>	-	130	260	ns
	propagation delay	see <u>Fig. 6</u>	10 V	44 ns + (0.23 ns/pF)C <sub>L</sub>	-	55	110	ns
			15 V	32 ns + (0.16 ns/pF)C <sub>L</sub>	-	40	80	ns
		CP to QS2;	5 V	102 ns + (0.55 ns/pF)C <sub>L</sub>	-	130	260	ns
		see <u>Fig. 6</u>	10 V	49 ns + (0.23 ns/pF)C <sub>L</sub>	-	60	120	ns
			15 V	37 ns + (0.16 ns/pF)C <sub>L</sub>	-	45	90	ns
t <sub>PZL</sub>	OFF-state to LOW	CP to QPn;	5 V		-	240	480	ns
	propagation delay	see <u>Fig. 6</u>	10 V		-	80	160	ns
			15 V		-	55	110	ns
		STR to QPn;	5 V		-	140	280	ns
		see <u>Fig. 7</u>	10 V		-	70	140	ns
			15 V		-	55	110	ns
t <sub>PLZ</sub> LOW to OFF-state	CP to QPn;	5 V		-	170	340	ns	
	propagation delay	see <u>Fig. 6</u>	10 V		-	75	150	ns
			15 V		-	60	120	ns
		STR to QPn;	5 V		-	100	200	ns
		see <u>Fig. 7</u>	10 V		-	40	100	ns
			15 V		-	35	70	ns
t <sub>en</sub>	enable time	OE to QPn;	5 V [2]		-	100	200	ns
		see <u>Fig. 8</u>	10 V		-	55	110	ns
			15 V		-	50	100	ns
t <sub>dis</sub>	disable time	OE to QPn;	5 V [2]		-	80	160	ns
		see <u>Fig. 8</u>	10 V		-	40	80	ns
			15 V		-	30	60	ns
t <sub>t</sub>	transition time	QS1, QS2;	5 V [1][3]	35 ns + (1.00 ns/pF)C <sub>L</sub>	-	85	170	ns
		see <u>Fig. 6</u>	10 V	19 ns + (0.42 ns/pF)C <sub>L</sub>	-	40	80	ns
			15 V	16 ns + (0.28 ns/pF)C <sub>L</sub>	-	30	60	ns
t <sub>W</sub>	pulse width	CP LOW and	5 V		60	30	-	ns
		HIGH; see Fig. 6	10 V		30	15	-	ns
			15 V		24	12	-	ns
		STR HIGH;	5 V		80	40	-	ns
		see <u>Fig. 7</u>	10 V		60	30	-	ns
		15 V		24	12	_	ns	

### 8-stage shift-and-store register LED driver

Symbol	Parameter	Conditions	V <sub>DD</sub>	Extrapolation formula	Min	Тур	Мах	Unit
t <sub>su</sub>	set-up time	D to CP; see Fig. 9	5 V		60	30	-	ns
			10 V		20	10	-	ns
		15 V		15	5	-	ns	
t <sub>h</sub>	hold time	D to CP; see Fig. 9	5 V		+5	-15	-	ns
			10 V		20	5	-	ns
			15 V		20	5	-	ns
f <sub>clk(max)</sub>	maximum clock	CP; see Fig. 6	5 V		5	10	-	MHz
frequency	frequency		10 V		11	22	-	MHz
			15 V		14	28	-	MHz

[1] The typical values of the propagation delay and transition times are calculated from the extrapolation formulas shown (C<sub>L</sub> in pF).

[2]  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{dis}$  is the same as  $t_{PLZ}$ 


[3]  $t_t$  is the same as  $t_{TLH}$  and  $t_{THL}$ 

### Table 8. Dynamic power dissipation

 $P_D$  can be calculated from the formulas shown.  $V_{SS} = 0$  V;  $t_r = t_f \le 20$  ns;  $T_{amb} = 25$  °C.

Symbol	Parameter	$V_{DD}$	Typical formula	Where
PD	dynamic power dissipation	5 V		$f_i$ = input frequency in MHz;
		10 V	$P_D = 5 550 \text{ x } f_i + \Sigma (f_o \text{ x } C_L) \text{ x } V_{DD}^2 \mu W$	f <sub>o</sub> = output frequency in MHz; C <sub>1</sub> = output load capacitance in pF;
		15 V	$P_D$ = 15 000 x f <sub>i</sub> + Σ(f <sub>o</sub> x C <sub>L</sub> ) x V <sub>DD</sub> <sup>2</sup> μW	$\Sigma(f_o \times C_L)$ = sum of the outputs; $V_{DD}$ = supply voltage in V.


## 10.1. Waveforms and test circuit



### 8-stage shift-and-store register LED driver

#### Table 9. Measurement points


Supply	Input	Output		
V <sub>DD</sub>	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>
5 V to 15 V	0.5V <sub>DD</sub>	0.5V <sub>DD</sub>	0.1V <sub>0</sub>	0.9V <sub>O</sub>




Measurement points are given in <u>Table 9</u>.

 $V_{\text{OL}}$  is the typical output voltage level that occurs with the output load.

### Fig. 7. Strobe (STR) to output (QPn) propagation delays and the strobe pulse width




### Fig. 8. Enable and disable times for input OE




### Fig. 9. Set-up and hold times for the data input (D)

## 8-stage shift-and-store register LED driver




Supply	Input		V <sub>EXT</sub>		Load		
V <sub>DD</sub>	VI	t <sub>r</sub> , t <sub>f</sub>	t <sub>PLZ</sub> , t <sub>PZL</sub>	t <sub>PLH</sub> , t <sub>PHL</sub>	CL	RL	
5 V to 15 V	V <sub>DD</sub>	≤ 20 ns	V <sub>DD</sub>	open	50 pF	1 kΩ	

## **11. Application information**



## 12. Package outline



### Fig. 12. Package outline SOT109-1 (SO16)

# **13. Revision history**

Table 11. Revision history							
Document ID	Release date	Data sheet status	Change notice	Supersedes			
HEF4794B_Q100 v.2	20181107	Product data sheet	-	HEF4794B _Q100 v.1			
Modifications:	<ul> <li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li>Fig. 5 corrected.</li> </ul>						
HEF4794B _Q100 v.1	20120807	Product data sheet	-	-			

## 14. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

#### 8-stage shift-and-store register LED driver

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

## Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	1
4. Functional diagram	2
5. Pinning information	3
5.1. Pinning	3
5.2. Pin description	3
6. Functional description	4
7. Limiting values	5
8. Recommended operating conditions	5
9. Static characteristics	6
10. Dynamic characteristics	7
10.1. Waveforms and test circuit	
11. Application information	10
12. Package outline	11
13. Revision history	12
14. Legal information	13

#### © Nexperia B.V. 2018. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 7 November 2018