

MMBZ27VUA-Q

TVS device for surge protection of interface and supply lines2 June 2023Product data sheet

## 1. General description

Protection device in a small SOD323 Surface-Mounted Device (SMD) plastic package designed to protect one line from the damage caused by transient overvoltages (TVS).

### 2. Features and benefits

- Reverse stand-off voltage: V<sub>RWM</sub> = 24 V
- Low clamping voltage:  $V_{CL}$  = 60 V at I<sub>PPM</sub>= 4.5 A
- ESD protection up to 30 kV (IEC61000-4-2)
- Ultra low leakage current: I<sub>RM</sub> = 1 nA
- · Qualified according to AEC-Q101 and recommended for use in automotive applications

### 3. Applications

ESD protection for supply and interface lines with high signal levels.

- Industrial
- Consumer
- Computing

## 4. Quick reference data

#### Table 1. Quick reference data

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V <sub>RWM</sub>	reverse standoff voltage	T <sub>amb</sub> = 25 °C		-	-	24	V
I <sub>PPM</sub>	rated peak pulse current	t <sub>p</sub> = 8/20 μs	[1] [2]	-	-	4.5	A
V <sub>CL</sub>	clamping voltage	$I_{PPM}$ = 4.5 A; t <sub>p</sub> = 8/20 µs; T <sub>amb</sub> = 25 °C	[2] [1]	-	-	70	V

[1] Device stressed with 8/20 µs exponential decay waveform according to IEC 61000-4-5.

[2] Measured from pin 1 to 2.



# 5. Pinning information

Table 2. F	Table 2. Pinning information					
Pin	Symbol	Description	Simplified outline	Graphic symbol		
1	К	cathode	1 2			
2	A	anode				
			SOD323	006aaa152		

## 6. Ordering information

Table 3. Ordering information						
Type number	Package	ckage				
	Name	Description	Version			
MMBZ27VUA-Q	SOD323	plastic, surface-mounted package; 2 leads; 1.3 mm pitch; 1.7 mm x 1.25 mm x 0.95 mm body	SOD323			

# 7. Marking

Table 4. Marking codes				
Type number	Marking code			
MMBZ27VUA-Q	V4			

## 8. Limiting values

#### Table 5. Limiting values


In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Мах	Unit
I <sub>PPM</sub>	rated peak pulse current	t <sub>p</sub> = 8/20 μs	[1] [2]	-	4.5	А
Tj	junction temperature			-	150	°C
T <sub>amb</sub>	ambient temperature			-55	150	°C
T <sub>stg</sub>	storage temperature			-65	150	°C
ESD maximu	ım ratings	·				
V <sub>ESD</sub>	electrostatic discharge	IEC 61000-4-2; contact discharge	[2] [3]	-	30	kV
	voltage	ISO 10605: contact discharge; C = 330 pF, R = 330 $\Omega$	[2] [3]	-	19	kV
		ISO 10605: contact discharge; C = 150 pF, R = 330 $\Omega$	[2] [3]	-	30	kV

[1] Device stressed with 8/20  $\mu$ s exponential decay waveform according to IEC 61000-4-5.

[2] Measured from pin 1 to 2.

[3] Device stressed with ten non-repetitive ESD pulses.




## 9. Characteristics

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V <sub>RWM</sub>	reverse standoff voltage	T <sub>amb</sub> = 25 °C		-	-	24	V
V <sub>BR</sub>	breakdown voltage	I <sub>R</sub> = 10 mA; T <sub>amb</sub> = 25 °C	[1]	26.2	27	27.5	V
I <sub>RM</sub>	reverse leakage current	V <sub>R</sub> = 24 V; T <sub>amb</sub> = 25 °C	[1]	-	1	50	nA
C <sub>d</sub>	diode capacitance	f = 1 MHz; V <sub>R</sub> = 0 V; T <sub>amb</sub> = 25 °C		-	23	50	pF
V <sub>CL</sub>	clamping voltage	I <sub>PPM</sub> = 1 A; t <sub>p</sub> = 8/20 μs; T <sub>amb</sub> = 25 °C	[1] [2]	-	30	36	V
		I <sub>PPM</sub> = 4.5 A; t <sub>p</sub> = 8/20 μs; T <sub>amb</sub> = 25 °C	[1] [2]	-	-	70	V
		I <sub>PP</sub> = 16 A; t <sub>p</sub> = 100 ns; T <sub>amb</sub> = 25 °C	[1] [3]	-	67.5	-	V
R <sub>dyn</sub>	dynamic resistance	I <sub>R</sub> = 10 A; t <sub>p</sub> = 100 ns; T <sub>amb</sub> = 25 °C	[1] [3]	-	1.6	-	Ω

[1] Measured from pin 1 to 2.

[2] Device stressed with 8/20 µs exponential decay waveform according to IEC 61000-4-5.


[3] Non-repetitive current pulse, Transmission Line Pulse (TLP); square pulse; ANSI / ESD STM5.5.1-2008.



MMBZ27VUA-Q

# MMBZ27VUA-Q


### TVS device for surge protection of interface and supply lines



**Product data sheet** 

## **10.** Application information

The device is designed for protection of one unidirectional data or signal line from surge pulses and ESD damage. The device is suitable on lines where the signal polarities are either positive or negative with respect to ground.



#### Circuit board layout and protection device placement

Circuit board layout is critical for the suppression of ESD, Electrical Fast Transient (EFT) and surge transients. The following guidelines are recommended:


- 1. Place the device as close to the input terminal or connector as possible.
- 2. Minimize the path length between the device and the protected line.
- 3. Keep parallel signal paths to a minimum.
- 4. Avoid running protected conductors in parallel with unprotected conductors.
- 5. Minimize all Printed-Circuit Board (PCB) conductive loops including power and ground loops.
- **6.** Minimize the length of the transient return path to ground.
- 7. Avoid using shared transient return paths to a common ground point.
- 8. Use ground planes whenever possible. For multilayer PCBs, use ground vias.

## **11. Test information**


### **Quality information**

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q101 - *Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

## 12. Package outline



# 13. Soldering



# 14. Revision history

Table 7. Revision history					
Data sheet ID	Release date	Data sheet status	Change notice	Supersedes	
MMBZ27VUA-Q v.1	20230602	Product data sheet	-	-	

MMBZ27VUA-Q

## 15. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

# Contents

1.	General description	.1
2.	Features and benefits	. 1
3.	Applications	. 1
4.	Quick reference data	.1
5.	Pinning information	.2
6.	Ordering information	.2
7.	Marking	. 2
8.	Limiting values	3
9.	Characteristics	.4
10.	Application information	6
11.	Test information	.6
12.	Package outline	. 7
	Soldering	
14.	Revision history	.9
	Legal information1	
	-	

© Nexperia B.V. 2023. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 2 June 2023