PESD3V3L1UA; PESD3V3L1UB; PESD3V3L1UL

Low capacitance unidirectional ESD protection diodes

Rev. 01 — 17 June 2009

Product data sheet

1. Product profile

1.1 General description

Low capacitance unidirectional ElectroStatic Discharge (ESD) protection diodes in small Surface-Mounted Device (SMD) plastic packages designed to protect one signal line from the damage caused by ESD and other transients.

Table 1.Product overview

Type number	Package F		Package configuration
	Nexperia	JEITA	
PESD3V3L1UA	SOD323	SC-76	very small
PESD3V3L1UB	SOD523	SC-79	ultra small and flat lead
PESD3V3L1UL	SOD882	-	leadless ultra small

1.2 Features

- Unidirectional ESD protection of one line
- Low diode capacitance: C_d = 34 pF
- Low clamping voltage: V_{CL} = 11 V
- Very low leakage current: I_{RM} = 100 nA

1.3 Applications

- Computers and peripherals
- Audio and video equipment
- Cellular handsets and accessories
- Communication systems

1.4 Quick reference data

Table 2.Quick reference data

 $T_{amb} = 25 \circ C$ unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
V _{RWM}	reverse standoff voltage		-	-	3.3	V
C _d	diode capacitance	$f = 1 \text{ MHz}; V_R = 0 \text{ V}$	-	34	40	pF

- ESD protection up to 30 kV
- IEC 61000-4-2; level 4 (ESD)
- AEC-Q101 qualified
- Subscriber Identity Module (SIM) card protection
- Portable electronics
- FireWire
- High-speed data lines

nexperia

Low capacitance unidirectional ESD protection diodes

2. Pinning information

Table 3.	Pinning		
Pin	Description	Simplified outline	Graphic symbol
PESD3V3	3L1UA; PESD3V3L1UB		
1	cathode	[1]	
2	anode	1 2 001aab540	1 2 006aaa152
PESD3V3	3L1UL		
1	cathode	[1]	
2	anode	1 2 Transparent top view	1 2 006aaa152

[1] The marking bar indicates the cathode.

3. Ordering information

Table 4. Ordering information			
Type number	Package		
	Name	Description	Version
PESD3V3L1UA	SC-76	plastic surface-mounted package; 2 leads	SOD323
PESD3V3L1UB	SC-79	plastic surface-mounted package; 2 leads	SOD523
PESD3V3L1UL	-	leadless ultra small plastic package; 2 terminals; body $1.0 \times 0.6 \times 0.5$ mm	SOD882

4. Marking

Table 5. Marking codes

Type number	Marking code
PESD3V3L1UA	1H
PESD3V3L1UB	Ζ7
PESD3V3L1UL	XW

PESD3V3L1UA_UB_UL_1

Low capacitance unidirectional ESD protection diodes

5. Limiting values

Table 6.Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
P _{PP}	peak pulse power	$t_p = 8/20 \ \mu s$	<u>[1][2]</u> _	45	W
I _{PP}	peak pulse current	$t_p = 8/20 \ \mu s$	<u>[1][2]</u> _	4.5	А
Tj	junction temperature		-	150	°C
T _{amb}	ambient temperature		-55	+150	°C
T _{stg}	storage temperature		-65	+150	°C

[1] Non-repetitive current pulse 8/20 µs exponential decay waveform according to IEC 61000-4-5.

[2] Measured from pin 1 to pin 2.

Table 7.ESD maximum ratings

 $T_{amb} = 25 \circ C$ unless otherwise specified.

Symbol	Parameter	Conditions		Min	Max	Unit
V_{ESD}	electrostatic discharge voltage	IEC 61000-4-2 (contact discharge)	<u>[1]</u>	-	30	kV
		machine model		-	400	V
		MIL-STD-883 (human body model)		-	10	kV

[1] Device stressed with ten non-repetitive ESD pulses.


Table 8. ESD standards compliance

Standard	Conditions
IEC 61000-4-2; level 4 (ESD)	> 15 kV (air); > 8 kV (contact)
MIL-STD-883; class 3 (human body model)	> 4 kV

Nexperia

PESD3V3L1UA/UB/UL

Low capacitance unidirectional ESD protection diodes



6. Characteristics

Table 9.Characteristics

 $T_{amb} = 25 \circ C$ unless otherwise specified.

' amb - 20	e unicos ourier moc specifi	icu.				
Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
V _{RWM}	reverse standoff voltage		-	-	3.3	V
I _{RM}	reverse leakage current	$V_{RWM} = 3.3 V$	-	100	300	nA
V _{BR}	breakdown voltage	$I_R = 5 \text{ mA}$	5.3	5.6	6.0	V
C _d	diode capacitance	f = 1 MHz; V _R = 0 V	-	34	40	pF
V _{CL}	clamping voltage		[1][2]			
		I _{PP} = 1 A	-	-	8	V
		I _{PP} = 4.5 A	-	-	11	V
r _{dif}	differential resistance	$I_R = 5 \text{ mA}$	-	-	30	Ω
VF	forward voltage	I _F = 200 mA	-	-	1.2	V


[1] Non-repetitive current pulse 8/20 µs exponential decay waveform according to IEC 61000-4-5.

[2] Measured from pin 1 to pin 2.


Nexperia

PESD3V3L1UA/UB/UL

Low capacitance unidirectional ESD protection diodes




Low capacitance unidirectional ESD protection diodes



Low capacitance unidirectional ESD protection diodes

7. Application information

The PESD3V3L1Ux series is designed for the protection of one unidirectional data or signal line from the damage caused by ESD and surge pulses. The devices may be used on lines where the signal polarities are either positive or negative with respect to ground. The PESD3V3L1Ux series provides a surge capability up to 45 W per line for an 8/20 μ s waveform.



Circuit board layout and protection device placement

Circuit board layout is critical for the suppression of ESD and Electrical Fast Transient (EFT). The following guidelines are recommended:

- 1. Place the device as close to the input terminal or connector as possible.
- 2. The path length between the device and the protected line should be minimized.
- 3. Keep parallel signal paths to a minimum.
- 4. Avoid running protected conductors in parallel with unprotected conductors.
- 5. Minimize all Printed-Circuit Board (PCB) conductive loops including power and ground loops.
- 6. Minimize the length of the transient return path to ground.
- 7. Avoid using shared transient return paths to a common ground point.
- 8. Ground planes should be used whenever possible. For multilayer PCBs, use ground vias.


8. Test information

8.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard *Q101* - *Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

Low capacitance unidirectional ESD protection diodes

9. Package outline



10. Packing information

Table 10. Packing methods


The indicated -xxx are the last three digits of the 12NC ordering code.[1]

Type number	Package	Package Description		Packing quantity		
			3000	8000	10000	
PESD3V3L1UA	SOD323	4 mm pitch, 8 mm tape and reel	-115	-	-135	
PESD3V3L1UB	SOD523	2 mm pitch, 8 mm tape and reel	-	-315	-	
		4 mm pitch, 8 mm tape and reel	-115	-	-135	
PESD3V3L1UL	SOD882	2 mm pitch, 8 mm tape and reel	-	-	-315	


[1] For further information and the availability of packing methods, see Section 14.

Low capacitance unidirectional ESD protection diodes

11. Soldering



Low capacitance unidirectional ESD protection diodes



PESD3V3L1UA_UB_UL_1

Low capacitance unidirectional ESD protection diodes

12. Revision history

Table 11. Revision history	y			
Document ID	Release date	Data sheet status	Change notice	Supersedes
PESD3V3L1UA_UB_UL_1	20090617	Product data sheet	-	-

13. Legal information

13.1 Data sheet status

Document status[1][2]	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

13.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

13.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia accepts no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by Nexperia. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

13.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

14. Contact information

For more information, please visit: http://www.nexperia.com

For sales office addresses, please send an email to: salesaddresses@nexperia.com

PESD3V3L1UA_UB_UL_1

Low capacitance unidirectional ESD protection diodes

15. Contents

1	Product profile 1
1.1	General description
1.2	Features
1.3	Applications 1
1.4	Quick reference data
2	Pinning information 2
3	Ordering information 2
4	Marking
5	Limiting values 3
6	Characteristics 4
7	Application information 7
8	Test information 7
8.1	Quality information 7
9	Package outline 8
10	Packing information 8
11	Soldering 9
12	Revision history 11
13	Legal information 12
13.1	Data sheet status 12
13.2	Definitions 12
13.3	Disclaimers
13.4	Trademarks 12
14	Contact information 12
15	Contents 13