

Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of http://www.nxp.com, http://www.nxp.com, http://www.nexperia.com/, http://www.nexperia.com/, use http://www.nexperia.com/

Instead of sales.addresses@www.nxp.com or sales.addresses@www.semiconductors.philips.com, use salesaddresses@nexperia.com (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © Nexperia B.V. (year). All rights reserved.

If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **salesaddresses@nexperia.com**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia



PMBT3906M

40 V, 200 mA PNP switching transistor

Rev. 01 — 22 July 2009

Product data sheet

1. Product profile

1.1 General description

PNP single switching transistor in a SOT883 (SC-101) leadless ultra small Surface-Mounted Device (SMD) plastic package.

NPN complement: PMBT3904M.

1.2 Features

- Single general-purpose switching transistor
- Board-space reduction
- AEC-Q101 qualified
- Ultra small SMD plastic package

1.3 Applications

■ General-purpose switching and amplification

1.4 Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V_{CEO}	collector-emitter voltage	open base	-	-	-40	V
I_{C}	collector current		-	-	-200	mA
h _{FE}	DC current gain	$V_{CE} = -1 \text{ V};$ $I_{C} = -10 \text{ mA}$	100	180	300	

2. Pinning information

Table 2. Pinning

Simplified outline	Graphic symbol
1 3	3
2	1—
Transparent top view	'*
	2
	sym013
	1 3



3. Ordering information

Table 3. Ordering information

Type number	Package	age					
	Name	Description	Version				
PMBT3906M	SC-101	leadless ultra small plastic package; 3 solder lands; body 1.0 \times 0.6 \times 0.5 mm	SOT883				

4. Marking

Table 4. Marking codes

Type number	Marking code
PMBT3906M	6Q

5. Limiting values

Table 5. Limiting values


In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{CBO}	collector-base voltage	open emitter	-	-40	V
V_{CEO}	collector-emitter voltage	open base	-	-40	V
V_{EBO}	emitter-base voltage	open collector	-	-6	V
I_{C}	collector current		-	-200	mA
I_{CM}	peak collector current	single pulse; $t_p \le 1 \text{ ms}$	-	-200	mA
I _{BM}	peak base current	single pulse; $t_p \le 1 \text{ ms}$	-	-100	mA
P _{tot}	total power dissipation	$T_{amb} \le 25 ^{\circ}C$	[1][2]	260	mW
			[1][3]	590	mW
T _j	junction temperature		-	150	°C
T _{amb}	ambient temperature		-55	+150	°C
T _{stg}	storage temperature		-65	+150	°C

^[1] Reflow soldering is the only recommended soldering method.

^[2] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

^[3] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for collector 1 cm².



6. Thermal characteristics


Table 6. Thermal characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
$R_{th(j-a)}$	thermal resistance from	in free air	[1][2]	-	481	K/W
	junction to ambient		[1][3]	-	212	K/W

^[1] Reflow soldering is the only recommended soldering method.

^[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

^[3] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for collector 1 cm².



7. Characteristics

Table 7. Characteristics

 $T_{amb} = 25 \,^{\circ}C$ unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
I_{CBO}	collector-base cut-off current	$V_{CB} = -30 \text{ V}; I_E = 0 \text{ A}$	-	-	-50	nA
I _{EBO}	emitter-base cut-off current	$V_{EB} = -6 \text{ V}; I_C = 0 \text{ A}$	-	-	-50	nA
h _{FE}	DC current gain	$V_{CE} = -1 V$				
		$I_C = -0.1 \text{ mA}$	60	180	-	
		$I_C = -1 \text{ mA}$	80	180	-	
		$I_C = -10 \text{ mA}$	100	180	300	
		$I_C = -50 \text{ mA}$	60	130	-	
		$I_C = -100 \text{ mA}$	30	50	-	
V _{CEsat}	collector-emitter saturation voltage	$I_C = -10 \text{ mA}; I_B = -1 \text{ mA}$	-	-100	-250	mV
		$I_C = -50 \text{ mA}; I_B = -5 \text{ mA}$	-	-165	-400	mV
V _{BEsat}	base-emitter	$I_C = -10 \text{ mA}; I_B = -1 \text{ mA}$	-	-750	-850	mV
	saturation voltage	$I_C = -50 \text{ mA}; I_B = -5 \text{ mA}$	-	-850	-950	mV
t _d	delay time	$V_{CC} = -3 \text{ V};$	-	-	35	ns
t _r	rise time	$I_C = -10 \text{ mA};$ $I_{Bon} = -1 \text{ mA};$	-	-	35	ns
t _{on}	turn-on time	$I_{Boff} = 1 \text{ mA}$	-	-	70	ns
ts	storage time		-	-	225	ns
t _f	fall time		-	-	75	ns
t _{off}	turn-off time		-	-	300	ns
C _c	collector capacitance	$V_{CB} = -5 \text{ V}; I_E = i_e = 0 \text{ A};$ f = 1 MHz	-	-	4.5	pF


PMBT3906M

40 V, 200 mA PNP switching transistor

 Table 7.
 Characteristics ... continued

 T_{amb} = 25 °C unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
C _e	emitter capacitance	$V_{EB} = -500 \text{ mV};$ $I_C = i_c = 0 \text{ A}; f = 1 \text{ MHz}$	-	-	10	pF
f _T	transition frequency	$V_{CE} = -20 \text{ V};$ $I_{C} = -10 \text{ mA};$ f = 100 MHz	250	-	-	MHz
NF	noise figure	$V_{CE} = -5 \text{ V};$ $I_{C} = -100 \mu\text{A}; R_{S} = 1 k\Omega;$ f = 10 Hz to 15.7 kHz	-	-	4	dB






⁽¹⁾ $T_{amb} = 150 \, ^{\circ}C$

(2)
$$T_{amb} = 25 \, ^{\circ}C$$


(3) $T_{amb} = -55 \, ^{\circ}C$

Fig 3. DC current gain as a function of collector current; typical values



 $T_{amb} = 25 \, ^{\circ}C$


Fig 4. Collector current as a function of collector-emitter voltage; typical values



$$V_{CE} = -1 V$$

- (1) $T_{amb} = -55 \,^{\circ}C$
- (2) $T_{amb} = 25 \, ^{\circ}C$
- (3) $T_{amb} = 150 \, ^{\circ}C$


Fig 5. Base-emitter voltage as a function of collector current; typical values



$$I_{\rm C}/I_{\rm B} = 10$$

- (1) $T_{amb} = -55 \, ^{\circ}C$
- (2) $T_{amb} = 25 \, ^{\circ}C$
- (3) $T_{amb} = 150 \, ^{\circ}C$

Fig 6. Base-emitter saturation voltage as a function of collector current; typical values




$$I_{\rm C}/I_{\rm B}=10$$

- (1) $T_{amb} = 150 \, ^{\circ}C$
- (2) $T_{amb} = 25 \, ^{\circ}C$
- (3) $T_{amb} = -55 \, ^{\circ}C$

Fig 7. Collector-emitter saturation voltage as a function of collector current; typical values


8. Test information



8.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard *Q101 - Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

9. Package outline



10. Packing information


Table 8. Packing methods

The indicated -xxx are the last three digits of the 12NC ordering code.[1]

Type number Package		Description	Packing quantity
			10000
PMBT3906M	SOT883	2 mm pitch, 8 mm tape and reel	-315

^[1] For further information and the availability of packing methods, see Section 14.

11. Soldering





12. Revision history

Table 9. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
PMBT3906M_1	20090722	Product data sheet	-	-

13. Legal information

13.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

13.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

13.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental

damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

13.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

14. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

PMBT3906M_1 © NXP B.V. 2009. All rights reserved.

PMBT3906M

40 V, 200 mA PNP switching transistor

15. Contents

1	Product profile
1.1	General description
1.2	Features
1.3	Applications 1
1.4	Quick reference data
2	Pinning information 1
3	Ordering information
4	Marking 2
5	Limiting values
6	Thermal characteristics
7	Characteristics 4
8	Test information 7
8.1	Quality information
9	Package outline
10	Packing information 8
11	Soldering 8
12	Revision history9
13	Legal information
13.1	Data sheet status
13.2	Definitions
13.3	Disclaimers
13.4	Trademarks10
14	Contact information 10
15	Contents

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

