

30 V, dual N-channel Trench MOSFET 25 March 2015

Product data sheet

1. General description

Dual N-channel enhancement mode Field-Effect Transistor (FET) in a leadless ultra small DFN1010B-6 (SOT1216) Surface-Mounted Device (SMD) plastic package using Trench MOSFET technology.

2. Features and benefits

- Low threshold voltage
- Leadless ultra small and ultra thin SMD plastic package: 1.1 × 1.0 × 0.37 mm
- Trench MOSFET technology
- ElectroStatic Discharge (ESD) protection > 2 kV HBM
- Exposed drain pad for excellent thermal conduction

3. Applications

- Relay driver
- High-speed line driver
- Low-side load switch
- Switching circuits

4. Quick reference data

Table 1. Quick reference data							
Symbol	Parameter	Conditions		Min	Тур	Max	Unit
Per transistor	Per transistor						
V _{DS}	drain-source voltage	T _j = 25 °C		-	-	30	V
V _{GS}	gate-source voltage			-8	-	8	V
I _D	drain current	V _{GS} = 4.5 V; T _{amb} = 25 °C	[1]	-	-	590	mA
Static characteristics (per transistor)							
R _{DSon}	drain-source on-state resistance	V _{GS} = 4.5 V; I _D = 590 mA; T _j = 25 °C		-	550	670	mΩ

[1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated, mounting pad for drain 1 cm².



30 V, dual N-channel Trench MOSFET

5. Pinning information

Table 2.	Pinning	information		
Pin	Symbol	Description	Simplified outline	Graphic symbol
1	S1	source TR1		D1 D2
2	G1	gate TR1		
3	D2	drain TR2	2 5	
4	S2	source TR2		
5	G2	gate TR2	3 4	
6	D1	drain TR1	Transparent top view	S1 S2 017aaa256
7	D1	drain TR1	DFN1010B-6 (SOT1216)	
8	D2	drain TR2		


6. Ordering information

Table 3. Ordering information						
Type number	Package					
	Name	Description	Version			
PMDXB550UNE	DFN1010B-6	DFN1010B-6: plastic thermal enhanced ultra thin small outline package; no leads; 6 terminals	SOT1216			

7. Marking

Table 4.Marking codes

Type number	Marking code
PMDXB550UNE	01 10 00



8. Limiting values

Table 5.Limiting values


In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
Per transis	tor	· · · · · · · · · · · · · · · · · · ·				
V _{DS}	drain-source voltage	T _j = 25 °C		-	30	V
V _{GS}	gate-source voltage			-8	8	V
I _D	drain current	V_{GS} = 4.5 V; T_{amb} = 25 °C	[1]	-	590	mA
		V_{GS} = 4.5 V; T_{amb} = 100 °C	[1]	-	370	mA
I _{DM}	peak drain current	T_{amb} = 25 °C; single pulse; $t_p \le 10 \ \mu s$		-	2.3	А
P _{tot} t	total power dissipation	T _{amb} = 25 °C	[2]	-	285	mW
			[1]	-	410	mW
		T _{sp} = 25 °C		-	4030	mW
Source-dra	in diode		1			
I _S	source current	T _{amb} = 25 °C		-	380	mA
Per device		· · · · · · · · · · · · · · · · · · ·				
Tj	junction temperature			-55	150	°C
T _{amb}	ambient temperature			-55	150	°C
T _{stg}	storage temperature			-65	150	°C

[1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated, mounting pad for drain 1 cm².

[2] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

30 V, dual N-channel Trench MOSFET



9. Thermal characteristics

Table 6. Thermal characteristics							
Symbol	Parameter	Conditions		Min	Тур	Max	Unit
Per transist	or		÷	·			
R _{th(j-a)} tł	thermal resistance	in free air	[1]	-	380	440	K/W
from junction to ambient			[2]	-	275	305	K/W


Nexperia

30 V, dual N-channel Trench MOSFET

Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
R _{th(j-sp)}	thermal resistance from junction to solder point		-	27	31	K/W

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for drain 1 cm².



10. Characteristics


Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
Static chara	cteristics (per transistor)	· · · ·				
V _{(BR)DSS}	drain-source breakdown voltage	I _D = 250 μA; V _{GS} = 0 V; T _j = 25 °C	30	-	-	V
V _{GSth}	gate-source threshold voltage	I_D = 250 µA; V_{DS} = V_{GS} ; T_j = 25 °C	0.45	0.7	0.95	V
I _{DSS}	drain leakage current	V_{DS} = 30 V; V_{GS} = 0 V; T_j = 25 °C	-	-	1	μA
I _{GSS}	gate leakage current	V _{GS} = 8 V; V _{DS} = 0 V; T _j = 25 °C	-	-	5	μA
		V _{GS} = -8 V; V _{DS} = 0 V; T _j = 25 °C	-	-	-5	μA
		V_{GS} = 4.5 V; V_{DS} = 0 V; T_j = 25 °C	-	-	1	μA
		V_{GS} = -4.5 V; V_{DS} = 0 V; T_j = 25 °C	-	-	-1	μA
		V_{GS} = 2.5 V; V_{DS} = 0 V; T_j = 25 °C	-	-	100	nA
		V_{GS} = -2.5 V; V_{DS} = 0 V; T_j = 25 °C	-	-	-100	nA
R _{DSon}	drain-source on-state	V_{GS} = 4.5 V; I _D = 590 mA; T _j = 25 °C	-	550	670	mΩ
	resistance	V _{GS} = 4.5 V; I _D = 590 mA; T _j = 150 °C	-	960	1170	mΩ
		V_{GS} = 2.5 V; I _D = 590 mA; T _j = 25 °C	-	660	900	mΩ
		V _{GS} = 1.8 V; I _D = 80 mA; T _j = 25 °C	-	770	1120	mΩ
		V _{GS} = 1.5 V; I _D = 10 mA; T _j = 25 °C	-	890	1500	mΩ
9 _{fs}	forward transconductance	V _{DS} = 10 V; I _D = 590 mA; T _j = 25 °C	-	600	-	mS
Dynamic ch	aracteristics (per transist	or)				
Q _{G(tot)}	total gate charge	V_{DS} = 15 V; I _D = 590 mA; V _{GS} = 4.5 V;	-	0.6	1.05	nC
Q _{GS}	gate-source charge	T _j = 25 °C	-	0.1	-	nC
Q _{GD}	gate-drain charge		-	0.1	-	nC
C _{iss}	input capacitance	V_{DS} = 15 V; f = 1 MHz; V_{GS} = 0 V;	-	30.3	-	pF
C _{oss}	output capacitance	T _j = 25 °C	-	5.8	-	pF
C _{rss}	reverse transfer capacitance		-	4.2	-	pF
t _{d(on)}	turn-on delay time	V_{DS} = 15 V; I _D = 590 mA; V _{GS} = 4.5 V;	-	4	-	ns
t _r	rise time	R _{G(ext)} = 6 Ω; T _j = 25 °C	-	7	-	ns
t _{d(off)}	turn-off delay time	1	-	12	-	ns
t _f	fall time		-	3	-	ns
Source-drai	n diode (per transistor)		I			
V _{SD}	source-drain voltage	I _S = 380 mA; V _{GS} = 0 V; T _i = 25 °C	-	0.86	1.2	V

PMDXB550UNE

All information provided in this document is subject to legal disclaimers.

© Nexperia B.V. 2017. All rights reserved


30 V, dual N-channel Trench MOSFET



Nexperia

PMDXB550UNE

30 V, dual N-channel Trench MOSFET




PMDXB550UNE

All information provided in this document is subject to legal disclaimers.


Nexperia

PMDXB550UNE

30 V, dual N-channel Trench MOSFET




11. Test information



30 V, dual N-channel Trench MOSFET


12. Package outline



PMDXB550UNE

All information provided in this document is subject to legal disclaimers.

13. Soldering



14. Revision history

Table 8. Revision history				
Data sheet ID	Release date	Data sheet status	Change notice	Supersedes
PMDXB550UNE v.1	20150325	Product data sheet	-	-

30 V, dual N-channel Trench MOSFET

15. Legal information

15.1 Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <u>http://www.nexperia.com</u>.

15.2 Definitions

Preview — The document is a preview version only. The document is still subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and

customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - Nexperia

products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

30 V, dual N-channel Trench MOSFET

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

30 V, dual N-channel Trench MOSFET

16. Contents

1	General description1
2	Features and benefits1
3	Applications1
4	Quick reference data1
5	Pinning information2
6	Ordering information2
7	Marking2
8	Limiting values3
9	Thermal characteristics4
10	Characteristics6
11	Test information9
12	Package outline 10
13	Soldering11
14	Revision history12
15	Legal information13
15.1	Data sheet status 13
15.2	Definitions13
15.3	Disclaimers13
15.4	Trademarks 14

© Nexperia B.V. 2017. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 25 March 2015