

#### Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of <a href="http://www.nxp.com">http://www.nxp.com</a>, <a href="http://www.semiconductors.philips.com/">http://www.nxp.com</a>, <a href="http://www.nexperia.com">http://www.nexperia.com</a>, <a href="http://www.nexperia.com">http://www.nexperia.com</a>)

Instead of sales.addresses@www.nxp.com or sales.addresses@www.semiconductors.philips.com, use salesaddresses@nexperia.com (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © Nexperia B.V. (year). All rights reserved.


If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **salesaddresses@nexperia.com**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia

## DISCRETE SEMICONDUCTORS

## DATA SHEET



# PMSS3906 PNP switching transistor

Product data sheet Supersedes data of 1999 Apr 22 2004 Jan 09



## **PNP** switching transistor

**PMSS3906** 

#### **FEATURES**

• Low current (max. 100 mA)

• Low voltage (max. 40 V).

#### **APPLICATIONS**

• Switching, e.g. telephony and professional communication equipment.

#### **QUICK REFERENCE DATA**

SYMBOL	PARAMETER	TYP.	MAX.	UNIT
$V_{CEO}$	collector-emitter voltage	_	-40	V
I <sub>C</sub>	collector current	_	-100	mA
h <sub>FE</sub>	DC current gain	100	300	

#### **DESCRIPTION**

PNP switching transistor in an SOT323 (SC-70) plastic package. NPN complement: PMSS3904.

#### **PRODUCT OVERVIEW**

TYPE NUMBER	PAC	KAGE	MARKING CODE <sup>(1)</sup>	NPN COMPLEMENT
TIPE NUMBER	PHILIPS	EIAJ	WARKING CODE	NPN COMPLEMENT
PMSS3906	SOT323	SC-70	06*	PMSS3904

#### Note

- 1. \* = p: Made in Hong Kong.
  - \* = t: Made in Malaysia.
  - \* = W: Made in China.

#### SIMPLIFIED OUTLINE, SYMBOL AND PINNING

TYPE NUMBER	SIMPLIFIED OUTLINE AND SYMBOL		PINNING		
ITPE NUMBER			DESCRIPTION		
PMSS3906	☐ 3	1	base		
	3	2	emitter		
	Top view MAM048	3	collector		

## PNP switching transistor

PMSS3906

#### **ORDERING INFORMATION**

TYPE NUMBER	PACKAGE			
ITPE NUMBER	NAME	DESCRIPTION	VERSION	
PMSS3906	_	plastic surface mounted package; 3 leads		

#### **LIMITING VALUES**

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V <sub>CBO</sub>	collector-base voltage	open emitter	_	-40	V
V <sub>CEO</sub>	collector-emitter voltage	open base	-	-40	V
V <sub>EBO</sub>	emitter-base voltage	open collector	_	-5	V
I <sub>C</sub>	collector current (DC)		_	-100	mA
I <sub>CM</sub>	peak collector current		-	-200	mA
I <sub>BM</sub>	peak base current		_	-100	mA
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> ≤ 25 °C; notes 1 and 2	_	200	mW
T <sub>stg</sub>	storage temperature		-65	+150	°C
T <sub>j</sub>	junction temperature		_	150	°C
T <sub>amb</sub>	operating ambient temperature		-65	+150	°C

#### **Notes**

- 1. Refer to standard mounting conditions.
- 2. Transistor mounted on an FR4 printed-circuit board, single-sided copper, tinplated, standard footprint.

#### THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
R <sub>th(j-a)</sub>	thermal resistance from junction to ambient	notes 1 and 2	625	K/W

#### **Notes**

- 1. Refer to standard mounting conditions.
- 2. Transistor mounted on an FR4 printed-circuit board, single-sided copper, tinplated, standard footprint.

## PNP switching transistor

PMSS3906

#### **CHARACTERISTICS**

 $T_{amb}$  = 25 °C unless otherwise specified.


SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
I <sub>CBO</sub>	collector-base cut-off current	I <sub>E</sub> = 0; V <sub>CB</sub> = -30 V	_	-50	nA
		I <sub>E</sub> = 0; V <sub>CB</sub> = -30 V; T <sub>j</sub> = 150 °C	_	-10	μΑ
I <sub>EBO</sub>	emitter-base cut-off current	I <sub>C</sub> = 0; V <sub>EB</sub> = -5 V	_	-50	nA
h <sub>FE</sub>	DC current gain	V <sub>CE</sub> = -1 V			
		$I_{C} = -0.1 \text{ mA}$	60	_	
		$I_C = -1 \text{ mA}$	80	_	
		$I_C = -10 \text{ mA}$	100	300	
		$I_C = -50$ mA; note 1	60	_	
		$I_{C} = -100 \text{ mA}$ ; note 1	30	_	
V <sub>CEsat</sub>	collector-emitter saturation	$I_C = -10 \text{ mA}; I_B = -1 \text{ mA}$	_	-250	mV
	voltage	$I_C = -50 \text{ mA}$ ; $I_B = -5 \text{ mA}$ ; note 1	_	-400	mV
V <sub>BEsat</sub>	base-emitter saturation voltage	$I_C = -10 \text{ mA}; I_B = -1 \text{ mA}$	_	-850	mV
		$I_C = -50 \text{ mA}$ ; $I_B = -5 \text{ mA}$ ; note 1	_	-950	mV
C <sub>c</sub>	collector capacitance	$I_E = i_e = 0$ ; $V_{CB} = -5 \text{ V}$ ; $f = 1 \text{ MHz}$	_	4.5	pF
C <sub>e</sub>	emitter capacitance	$I_C = I_c = 0$ ; $V_{EB} = -0.5 \text{ V}$ ; $f = 1 \text{ MHz}$	_	14	pF
f <sub>T</sub>	transition frequency	$I_E = -10 \text{ mA}; V_{CB} = -20 \text{ V}; f = 100 \text{ MHz}$	150	_	MHz
F	noise figure	$I_C$ = -100 μA; $V_{CE}$ = -5 V; $R_S$ = 1 kΩ; $f$ = 10 Hz to 15.7 kHz	_	4	dB
Switching t	imes (between 10% and 90% lev	rels); see Fig.1			
t <sub>on</sub>	turn-on time	$I_{Con} = -10 \text{ mA}; I_{Bon} = -1 \text{ mA}; I_{Boff} = 1 \text{ mA}$	_	100	ns
t <sub>d</sub>	delay time		_	50	ns
t <sub>r</sub>	rise time		_	50	ns
t <sub>off</sub>	turn-off time		_	700	ns
t <sub>s</sub>	storage time		_	600	ns
t <sub>f</sub>	fall time		_	100	ns

#### Note

1. Pulse test:  $t_p \leq 300~\mu s;~\delta \leq 0.02.$ 

## PNP switching transistor

PMSS3906




## PNP switching transistor

PMSS3906

#### **PACKAGE OUTLINE**

#### Plastic surface-mounted package; 3 leads

**SOT323** 



OUTLINE	REFERENCES			EUROPEAN	ISSUE DATE	
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT323			SC-70			<del>04-11-04</del> 06-03-16

2004 Jan 09 6

0.3

### PNP switching transistor

PMSS3906

#### **DATA SHEET STATUS**

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

#### **Notes**

- 1. Please consult the most recently issued document before initiating or completing a design.
- 2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

#### **DISCLAIMERS**

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions

above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

## **NXP Semiconductors**

#### **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors, including new legal definitions and disclaimers. No changes were made to the technical content, except for package outline drawings which were updated to the latest version.

#### **Contact information**

For additional information please visit: http://www.nxp.com
For sales offices addresses send e-mail to: salesaddresses@nxp.com

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands R75/04/pp8 Date of release: 2004 Jan 09 Document order number: 9397 750 12329

