

## Reliability Monitoring Results

**Quarters:** Q1/2022 to Q4/2022

Based on structural similarity

| Supplier  |  | User Part Number                                      |                             |           |            |           |
|---|--|---|-----------------------------|-----------|------------|-----------|
| Nexperia B.V.   |  | 74AHCT123ABQ-Q100                                     |                             |           |            |           |
| Part Description: Dual retriggerable monostable multivibrator with reset; TTL enabled |  |   |                             |           |            |           |
| Function Family: AHC(T)<br>Process family: Super micron<br>Package family: DHVQFN     |  |   |                             |           |            |           |
| JESD47 Test   |  | Test Conditions                                       | Duration                    | # Lots    | # Quantity | # Rejects |
| # 1   | TEST<br>Pre- and Post-Stress<br>Electrical Test                    | Tamb = 25 °C  | N/A                         | see below | all parts  | see below |
| # 2   | PC<br>Preconditioning  | JESD22-A113<br>MSL 1                                  | N/A                         | 386       | 23019      | 0         |
| # 5a  | HTOL EFR<br>High Temperature<br>Operating Life Extrinsic           | JESD22-A108<br>Tj = 150°C<br>VCCMAX ≤ V ≤ 1.2*VCCMAX  | 48 hours<br>or<br>168 hours | 136       | 39090      | 0         |
| # 5b  | HTOL IFR<br>High Temperature<br>Operating Life Intrinsic           | JESD22-A108<br>Tj = 150°C<br>VCCMAX ≤ V ≤ 1.2*VCCMAX  | ≥500 hours                  | 84        | 5695       | 0         |
| # 7   | TC<br>Temperature Cycling  | JESD22-A104<br>-65 °C to 150°C                        | ≥500 cycles                 | 208       | 12655      | 0         |
| # 9   | uHAST / HAST<br>unbiased or biased High<br>Accelerated Stress Test | JESD22-A101<br>Tamb = 130 °C,<br>RH = 85%, V = VCCMAX | 96 hours                    | 178       | 10364      | 0         |

### Calculation of PPM, FIT and MTTF

Test considered for PPM calculation: High Temperature Operating LifeTest Extrinsic (HTOL EFR, Test # 5a above)

Test considered for FIT and MTTF calculations: High Temperature Operating LifeTest Intrinsic (HTOL IFR, Test # 5b above)

Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

| Product Family | Package Family | Quantity | Rejects | Extrinsic Failure Rate (PPM) | Intrinsic Failure Rate (FIT) | MTTF (hrs) |
|----------------|----------------|----------|---------|------------------------------|------------------------------|------------|
| AHC(T)         | DHVQFN         | 5695     | 0       | 24                           | 0.6                          | 1.74 E+09  |