

## Reliability Monitoring Results

Quarters: Q1/2023 to Q4/2023

Based on structural similarity

| Supplier   |  | User Part Number            |           |            |           |  |
|--|--|-----------------------------|-----------|------------|-----------|--|
| Nexperia B.V.  |  | 74AUP2G04GM                 |           |            |           |  |
| <b>Part Description:</b> Dual inverter   |  |                             |           |            |           |  |
| Function Family: AUP<br>Process family: C075<br>Package family: XSON             |  |                             |           |            |           |  |
| JESD47 Test  | Test Conditions  | Duration                    | # Lots    | # Quantity | # Rejects |  |
| # 1<br><b>TEST</b><br>Pre- and Post-Stress<br>Electrical Test                    | Tamb = 25 °C   | N/A                         | see below | all parts  | see below |  |
| # 2<br><b>PC</b><br>Preconditioning  | JESD22-A113<br>MSL 1   | N/A                         | 1197      | 35627      | 0         |  |
| # 5a<br><b>HTOL EFR</b><br>High Temperature<br>Operating Life Extrinsic          | JESD22-A108<br>Tj = 150°C<br>V <sub>CCMAX</sub> ≤ V ≤ 1.2*V <sub>CCMAX</sub> | 48 hours<br>or<br>168 hours | 252       | 46656      | 0         |  |
| # 5b<br><b>HTOL IFR</b><br>High Temperature<br>Operating Life Intrinsic          | JESD22-A108<br>Tj = 150°C<br>V <sub>CCMAX</sub> ≤ V ≤ 1.2*V <sub>CCMAX</sub> | ≥500 hours                  | 111       | 8362       | 0         |  |
| # 7<br><b>TC</b><br>Temperature Cycling  | JESD22-A104<br>-65 °C to 150°C   | ≥500 cycles                 | 625       | 19434      | 0         |  |
| # 9<br><b>uHAST / HAST</b><br>unbiased or biased High<br>Accelerated Stress Test | JESD22-A101<br>Tamb = 130 °C,<br>RH = 85%, V = V <sub>CCMAX</sub>            | 96 hours                    | 579       | 16193      | 0         |  |

### Calculation of PPM, FIT and MTTF

Test considered for PPM calculation: High Temperature Operating LifeTest Extrinsic (HTOL EFR, Test # 5a above)

Test considered for FIT and MTTF calculations: High Temperature Operating LifeTest Intrinsic (HTOL IFR, Test # 5b above)

Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

| Product Family | Package Family | Quantity | Rejects | Extrinsic Failure Rate (PPM) | Intrinsic Failure Rate (FIT) | MTTF (hrs) |
|----------------|----------------|----------|---------|------------------------------|------------------------------|------------|
| AUP            | XSON           | 8362     | 0       | 20                           | 0.5                          | 2.07 E+09  |