

Reliability Monitoring Results

Quarters: Q1/2024 to Q4/2024

Based on structural similarity

| Supplier | | User Part Number | | | | |
|---|---|---|-----------------------------|-----------|------------|-----------|
| Nexperia B.V. | | 74AXP1G14GX | | | | |
| Part Description: Single inverter Schmitt-trigger | | | | | | |
| Function Family: AXP Process family: C050 Package family: X2SON | | | | | | |
| JESD47 Test | | Test Conditions | Duration | # Lots | # Quantity | # Rejects |
| # 1 | TEST Pre- and Post-Stress Electrical Test | Tamb = 25 °C | N/A | see below | all parts | see below |
| # 2 | PC Preconditioning | JESD22-A113 MSL 1 | N/A | 1940 | 68809 | 0 |
| # 5a | HTOL EFR High Temperature Operating Life Extrinsic | JESD22-A108 Tj = 150°C VCCMAX ≤ V ≤ 1.2*VCCMAX | 48 hours or 168 hours | 59 | 13806 | 0 |
| # 5b | HTOL IFR High Temperature Operating Life Intrinsic | JESD22-A108 Tj = 150°C VCCMAX ≤ V ≤ 1.2*VCCMAX | ≥500 hours | 38 | 3294 | 0 |
| # 7 | TC Temperature Cycling | JESD22-A104 -65 °C to 150°C | ≥500 cycles | 977 | 34915 | 0 |
| # 9 | uHAST / HAST unbiased or biased High Accelerated Stress Test | JESD22-A101 Tamb = 130 °C, RH = 85%, V = VCCMAX | 96 hours | 967 | 33894 | 0 |

Calculation of PPM, FIT and MTTF

Test considered for PPM calculation: High Temperature Operating LifeTest Extrinsic (HTOL EFR, Test # 5a above)

Test considered for FIT and MTTF calculations: High Temperature Operating LifeTest Intrinsic (HTOL IFR, Test # 5b above)

Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

| Product Family | Package Family | Quantity | Rejects | Extrinsic Failure Rate (PPM) | Intrinsic Failure Rate (FIT) | MTTF (hrs) |
|----------------|----------------|----------|---------|------------------------------|------------------------------|------------|
| AXP | X2SON | 3294 | 0 | 67 | 1.2 | 8.93 E+08 |