

Quarterly Reliability Monitoring Results

Quarters: Q3/2021 to Q4/2022

Based on structural similarity

Supplier	User Part Number					
Nexperia B.V.	BZT52H-A9V1-Q					
Name of Laboratory	Part Description					
Assembly reliability labs	Nexperia DHAM	Zener				
	SMD package					
Based on AEC-Q101 Test	Test Conditions	Duration	# Lots	# Quantity	# Rejects	
# E1	TEST Pre- and Post-Stress Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below
# A1	PC Preconditioning	JESD22-A113 Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85% Reflow soldering	24 hours 168 hours 3 cycles	1168	66640	0
# B1	HTRB High Temperature Reverse Bias	MIL-STD-750-1 M1038 Method A Tj = Tjmax, VR = 80 % of rated reverse voltage	1000 hours	198	11960	0
# B1b	SSOP Steady State Operational	MIL-STD-750-1 M1038 Method B Tj = Tjmax, Iz = 100% of max. datasheet reverse current	1000 hours	24	1760	0
# A4	TC Temperature Cycling	JESD22-A104 -65 °C to Tjmax, not to exceed 150°C	1000 cycles	240	14800	0
# A3 or	UHASt Unbiased HAST	JESD22-A118 Tamb = 130 °C, RH = 85 %	96 hours	240	14800	0
# A3 alt	AC Autoclave	JESD22-A102 Tamb = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia)				
# A2 alt	H3TRB High Humidity High Temperature Reverse Bias	JESD22-A101 Tamb = 85 °C, RH = 85%, VR = 80 % of rated reverse voltage ^[1]	1000 hours	240	14800	0
# A5	IOL Intermittent Operating Life	MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔTj = 100 °C for 15000 cycles	1000 hours	264	16720	0
# C8	RSH Resistance to Solder Heat	JESD22-A111 260 °C ± 5 °C	10 s	184	5520	0
# C10	SD Solderability	J-STD-002		501	5010	0

[1] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1)

Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
Nexperia DHAM	Zener	11960	0	0,36	2,82E+09

© 2023 Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.

nexperia.com