

## Quarterly Reliability Monitoring Results

Quarters: Q1/2022 to Q4/2023

Based on structural similarity

Supplier		User Part Number				
Nexperia B.V.		BZX384-C56-Q				
Name of Laboratory		Part Description				
Assembly reliability labs		Nexperia DHAM Zener SMD package				
Based on AEC-Q101 Test		Test Conditions	Duration	# Lots	# Quantity	# Rejects
<b>TEST</b> Pre- and Post-Stress Electrical Test		Tamb = 25 °C	N/A	see below	all parts	see below
# E1						
<b>PC</b> Preconditioning		JESD22-A113 Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85% Reflow soldering	24 hours 168 hours 3 cycles	1514	64430	0
# A1						
<b>HTRB</b> High Temperature Reverse Bias		MIL-STD-750-1 M1038 Method A Tj = Tjmax, VR = 80 % of rated reverse voltage	1000 hours	250	11400	0
# B1						
<b>SSOP</b> Steady State Operational		MIL-STD-750-1 M1038 Method B Tj = Tjmax, Iz = 100% of max. datasheet reverse current	1000 hours	44	1920	0
# B1b						
<b>TC</b> Temperature Cycling		JESD22-A104 -65 °C to Tjmax, not to exceed 150°C	1000 cycles	311	14080	0
# A4						
<b>UHAST</b> Unbiased HAST		JESD22-A118 Tamb = 130 °C, RH = 85 %	96 hours	311	14080	0
# A3 or						
<b>AC</b> Autoclave		JESD22-A102 Tamb = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia)				
# A3 alt						
<b>H3TRB</b> High Humidity High Temperature Reverse Bias		JESD22-A101 Tamb = 85 °C, RH = 85%, VR = 80 % of rated reverse voltage <sup>[1]</sup>	1000 hours	311	14080	0
# A2 alt						
<b>IOL</b> Intermittent Operating Life		MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔTj = 100 °C for 15000 cycles	1000 hours	312	14120	0
# A5						
<b>RSB</b> Resistance to Solder Heat		JESD22-A111 260 °C ± 5 °C	10 s	269	8070	0
# C8						
<b>SD</b> Solderability		J-STD-002		19	6660	0
# C10						

[1] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

### Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1)

Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
Nexperia DHAM	Zener	11400	0	0,37	2,68E+09

© 2024 Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.

[nexperia.com](https://www.nexperia.com)