



## Reliability Investigation Results for Product Type MMBZ9V1AL

Time period: Q4/2013 to Q3/2014

### Test Results

AEC-Q101 Test	Conditions	Duration	Quantity	Rejects
<b>TEST</b>				
# 1 Pre- and Post-Stress Electrical Test	$T_{amb} = 25\text{ }^{\circ}\text{C}$	N/A	all parts	see below
# 2 <b>PC</b> Preconditioning	JESD22-A113 Bake $T_{amb} = 125\text{ }^{\circ}\text{C}$ Soak $T_{amb} = 85\text{ }^{\circ}\text{C}$ , RH = 85% Reflow soldering	24 hours 168 hours 3 cycles	43440	0
# 5 <b>HTRB</b> High Temperature Reverse Bias	JESD22-A108 $T_j = T_{jmax}$ , $V_R > 80\%$ of max. breakdown voltage	1000 hours	5760	0
# 7 <b>TC</b> Temperature Cycling	JESD22-A104 -55 $^{\circ}\text{C}$ to $T_{jmax}$	1000 cycles	11360	0
# 8 <b>AC</b> Autoclave	JESD22-A102 $T_{amb} = 121\text{ }^{\circ}\text{C}$ , RH = 100 % Pressure = 205 kPa (29.7 psia)	96 hours	11360	0
# 9 <b>H3TRB</b> High Humidity High Temperature Reverse Bias	JESD22-A101 $T_{amb} = 85\text{ }^{\circ}\text{C}$ , RH = 85%, $V_R > 80\%$ of rated breakdown voltage	1000 hours	11360	0
# 10 <b>IOL</b> Intermittent Operating Life	MIL-STD-750 Method 1037 $t_{on} = t_{off}$ , devices powered to insure $\Delta T_j = 125\text{ }^{\circ}\text{C}$ for 7500 cycles or $\Delta T_j = 100\text{ }^{\circ}\text{C}$ for 15000 cycles	1000 hours	9360	0
# 20 <b>RSH</b> Resistance to Solder Heat	JESD22-A111 / JESD22-B106 260 $^{\circ}\text{C} \pm 5\text{ }^{\circ}\text{C}$	10 s	2700	0
# 21 <b>SD</b> Solderability	J-STD-002 245 $^{\circ}\text{C} \pm 5\text{ }^{\circ}\text{C}$	3 s	2790	0

### Calculation of FIT and MTBF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, AEC-Q101 Test # 5)

Confidence level 60%, derated to 55  $^{\circ}\text{C}$ , activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate	MTBF
NXP DHAM	Zener / Protection	5760	0	0.74 FIT	154731 years