nexperia

Product Reliability Information

| | Conditions | Duration | Quantity | Rejects |
|---|--|-------------|-----------|-----------|
| #1 TEST Pre and Post stress electrical test | T _{amb} = 25°C | N/A | All parts | See below |
| #2 PC Preconditioning | JESD22-A11324 hoursBake $T_{amb} = 125^{\circ}C$ 168 hoursSoak $T_{amb} = 85^{\circ}C$, RH = 85%3 cycles | | 960 | 0 |
| #5 HTRB High temperature reverse bias | $ \begin{array}{c c} \text{MIL-STD-750-1} \\ \text{T}_{j} = \text{T}_{j} \text{ max}, \text{V}_{\text{DS}} = 80\% \text{ of rated} \\ \text{voltage} \\ \text{M1039 Method A} \end{array} \begin{array}{c} 1000 \text{ hours} \\ 2870 \end{array} $ | | 2870 | 0 |
| #6 HTGB High temperature gate bias | JESD22-A108 $T_j = T_j \max, V_{GS} = 16V$ 1000 hours 3540 | | 3540 | 0 |
| #7 TC Temperature Cycling | JESD22-A104 -55°C to 150°C 500 cycles | | 240 | 0 |
| #8 UHAST Unbiased highly accelerated stress test | JESD22-A118 T _{amb} = 130°C, RH = 85% Pressure = $+2.27$ atm | | | 0 |
| #9 HAST Highly accelerated stress test | JESD22-A110 $T_{amb} = 130$ °C, RH = 85% $V_{DS} = 80\%$ of rated voltage | 96 hours | | 0 |
| #10 IOL Intermittent operating life | MIL-STD-750 method 1037 ΔTj = 80°C | 5000 cycles | 240 | 0 |
| #20 RSH Resistance to solder heat | JESD22-A111 (SMD) 260°C ± 5°C | 10s | 180 | 0 |

| #21 SD Solderability | IPC/ECA J-STD-002 Method A dip and look No aging, solder Ta = 245°C | 3 sec dip | 180 | 0 |
|-------------------------|--|-----------------------|-----|---|
| | IPC/ECA J-STD-002 Method B dip and look No aging Solder Ta = 245°C >95% lead coverage required Steam Aging: condition C Steam Ta = 93°C, 8 hours Solder Ta = 245°C, 3 sec dip | 8 hours 3 sec dip | 180 | 0 |
| | Dry Bake: Ta = 150°C Solder Ta = 245°C >95% lead coverage required | 16 hours 3 sec dip | 180 | 0 |

Calculation of FIT and MTBF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB) and High temperature Gate Bias (HTGB). Confidence level 60%, derated to 55°C, activation energy 0.7Ev test time 168 to 1000 hours.

| Wafer Fab | Technology | Quantity | Failure rate | MTBF |
|-----------|------------|----------|--------------|----------|
| VIS | TrenchMOS | 6410 | 0.19 | 5.23E+09 |

© 2022 Nexperia B.V.