

Quarterly Reliability Monitoring Results

Quarters: Q1/2023 to Q4/2024

Based on structural similarity

Supplier		User Part Number				
Nexperia B.V.		PESD5V0HS-SF				
Name of Laboratory		Part Description				
Assembly reliability labs		NXP ICN8 BD package Protection INDI				
Test	Test Conditions	Duration	# Lots	# Quantity	# Rejects	
# 1	TEST Pre- and Post-Stress Electrical Test Tamb = 25 °C	N/A	see below	all parts	see below	
# 5	HTRB High Temperature Reverse Bias MIL-STD-750-1 M1038 Method A Tj = Tjmax, Vr = 100% of max. datasheet reverse voltage	1000 hours	96	3840	0	
# 7	TC Temperature Cycling JESD22-A104 -40 °C to 125°C	1000 cycles	175	7000	0	
# 8 or	UHAST Unbiased HAST JESD22-A118 Tamb = 130 °C, RH = 85 %	96 hours	n.a.	n.a.	n.a.	
# 8a	AC Autoclave JESD22-A102 Tamb = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia)					
# 9	HAST Highly Accelerated Stress Test JESD22-A110 Tamb = 130 °C, RH = 85%, VR = 80 % of rated reverse voltage ^[1]	96 hours	175	7000	0	
# 10	IOL Intermittent Operating Life MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔTj = 100 °C for 15000 cycles	1000 hours	n.a.	n.a.	n.a.	
# 20	RSH Resistance to Solder Heat JESD22-A111 260 °C ± 5 °C	10 s	n.a.	n.a.	n.a.	
# 21	SD Solderability J-STD-002		6	180	0	

[1] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test # 5)
Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
NXP ICN8	Protection INDI	3840	0	1,1	9,04E+08